

Aluminum Capacitors 105 °C, Miniature, Radial Lead


FEATURES

- Improved SMPS output capacitors
- Highest ripple current ratings per case size
- High CV
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



| QUICK REFERENCE DATA | |
|---|--|
| DESCRIPTION | VALUE |
| Nominal case size Ø D x L in inches [mm] | 0.394 x 0.472 [10.0 x 12.0] to 0.709 x 1.575 [18.0 x 40.0] |
| Operating temperature | -55 °C to +105 °C |
| Rated capacitance range, C _R | 33 µF to 6800 µF |
| Tolerance on C _R | ± 20 % |
| Rated voltage range, U _R | 6.3 WV _{DC} to 63 WV _{DC} |
| Termination | 2 and 3 radial leads and axial mount. |
| Life validation test at 105 °C | 4000 h (≥ 0.512" [13.0] diameter): 3000 h (0.394" [10.0] diameter): ΔCAP ≤ 20 % (6.3 WV _{DC} to 25 WV _{DC}), ≤ 15 % (40 WV _{DC} to 63 WV _{DC}) from initial measurement. ΔESR ≤ 1.3 x initial specified limit. ΔDCL ≤ 2 x initial specified limit. |
| Shelf life at 105 °C | 1000 h: ΔCAP ≤ 20 % (6.3 WV _{DC} to 25 WV _{DC}), ≤ 15 % (40 WV _{DC} to 63 WV _{DC}) from initial measurements. ΔESR ≤ 1.3 x initial specified limit. |
| DC leakage current | I = 0.01 CV (2 min charge time) I = 0.03 CV (1 min charge time) I in µA, C in µF, V in Volts |

| RIPPLE CURRENT MULTIPLIERS | | | | | |
|----------------------------|----------|-------------|------------|-----------|-------------|
| TEMPERATURE | | | | | |
| AMBIENT TEMPERATURE | | MULTIPLIERS | | | |
| +105 °C | | 1.0 | | | |
| +85 °C | | 2.2 | | | |
| +75 °C | | 2.7 | | | |
| ≤ +65 °C | | 3.0 | | | |
| FREQUENCY (Hz) | | | | | |
| WV _{DC} | 50 TO 60 | 100 TO 120 | 300 TO 400 | 1K TO 19K | 20K TO 200K |
| 6.3 to 63 | 0.60 | 0.70 | 0.75 | 0.82 | 1.0 |

| LOW TEMPERATURE PERFORMANCE | | | | |
|---|---------------|--------------|--------------|--------------|
| CAPACITANCE RATIO C ^{-55 °C} / C ^{+25 °C} MINIMUM AT 120 Hz | | | | |
| MAXIMUM CAPACITANCE CHANGE | VOLTAGE | MULTIPLIER | | |
| | 6.3 V to 16 V | 0.75 | | |
| 25 V to 63 V | 0.85 | | | |
| MAXIMUM IMPEDANCE CHANGE | VOLTAGE | MULTIPLIER | | |
| | 6.3 V to 16 V | 2.0 | | |
| 25 V to 63 V | 1.5 | | | |
| ESL (TYPICAL VALUES AT 1 MHz TO 10 MHz) | | | | |
| NOMINAL DIAMETER | 0.394 [10.0] | 0.512 [13.0] | 0.630 [16.0] | 0.709 [18.0] |
| TYPICAL ESL (nH) | 4.0 | 7.0 | 10.0 | 12.0 |

BULK SPECIFICATIONS in millimeters

TERMINAL CODE C

TERMINAL CODE D

TERMINAL CODE J (1)

TERMINAL CODE O (2)

Notes

- ⊕ Positive terminal
- ⊖ Negative terminal
- Ⓝ No charge potential
- (1) Available for 12.5 mm, 16 mm, and 18 mm diameter units
- (2) Available for 12.5 mm, 16 mm, and 18 mm diameter units with epoxy end-seal

| DIMENSIONS in inches [millimeters] | | | | | | | | | | |
|---|--------------|--------------|----------------|--------------|----------------|--------------|------------------|------------------|---------------|-----|
| CASE CODE | NOMINAL | | STYLES 2 AND 4 | | STYLES 3 AND 5 | | LEAD SPACING | | LEAD DIAMETER | |
| | D | L | D (max.) | L (max.) | D (max.) | L (max.) | S ± 0.024 [0.60] | T ± 0.020 [0.50] | NOMINAL | AWG |
| CC | 0.394 [10.0] | 0.512 [13.0] | 0.413 [10.5] | 0.563 [14.3] | 0.413 [10.5] | 0.630 [16.0] | 0.197 [5.0] | n/a | 0.025 [0.63] | 22 |
| CD | 0.394 [10.0] | 0.630 [16.0] | 0.413 [10.5] | 0.669 [17.0] | 0.413 [10.5] | 0.740 [18.8] | 0.197 [5.0] | n/a | 0.025 [0.63] | 22 |
| CG | 0.394 [10.0] | 0.787 [20.0] | 0.413 [10.5] | 0.846 [21.5] | 0.413 [10.5] | 0.906 [23.0] | 0.197 [5.0] | n/a | 0.025 [0.63] | 22 |
| DG | 0.492 [12.5] | 0.787 [20.0] | 0.512 [13.0] | 0.846 [21.5] | 0.512 [13.0] | 0.906 [23.0] | 0.197 [5.0] | 0.098 [2.5] | 0.032 [0.81] | 20 |
| DK | 0.492 [12.5] | 0.984 [25.0] | 0.512 [13.0] | 1.043 [26.5] | 0.512 [13.0] | 1.142 [29.0] | 0.197 [5.0] | 0.098 [2.5] | 0.032 [0.81] | 20 |
| DM | 0.492 [12.5] | 1.043 [26.5] | 0.512 [13.0] | 1.102 [28.0] | 0.512 [13.0] | 1.161 [29.5] | 0.197 [5.0] | 0.098 [2.5] | 0.032 [0.81] | 20 |
| DT | 0.492 [12.5] | 1.319 [33.5] | 0.512 [13.0] | 1.346 [34.2] | 0.512 [13.0] | 1.417 [36.0] | 0.197 [5.0] | 0.098 [2.5] | 0.032 [0.81] | 20 |
| DS | 0.492 [12.5] | 1.673 [42.5] | 0.512 [13.0] | 1.720 [43.7] | 0.512 [13.0] | 1.791 [45.5] | 0.197 [5.0] | 0.098 [2.5] | 0.032 [0.81] | 20 |
| EK | 0.630 [16.0] | 0.984 [25.0] | 0.650 [16.5] | 1.031 [26.2] | 0.650 [16.5] | 1.098 [27.9] | 0.295 [7.5] | 0.150 [3.8] | 0.032 [0.81] | 20 |
| EN | 0.630 [16.0] | 1.260 [32.0] | 0.650 [16.5] | 1.319 [33.5] | 0.650 [16.5] | 1.417 [36.0] | 0.295 [7.5] | 0.150 [3.8] | 0.032 [0.81] | 20 |
| ER | 0.630 [16.0] | 1.417 [36.0] | 0.650 [16.5] | 1.476 [37.5] | 0.650 [16.5] | 1.575 [40.0] | 0.295 [7.5] | 0.150 [3.8] | 0.032 [0.81] | 20 |
| EU | 0.630 [16.0] | 1.575 [40.0] | 0.650 [16.5] | 1.642 [41.7] | 0.650 [16.5] | 1.669 [42.4] | 0.295 [7.5] | 0.150 [3.8] | 0.032 [0.81] | 20 |
| FR | 0.709 [18.0] | 1.417 [36.0] | 0.728 [18.5] | 1.476 [37.5] | 0.728 [18.5] | 1.575 [40.0] | 0.295 [7.5] | 0.150 [3.8] | 0.032 [0.81] | 20 |
| FV | 0.709 [18.0] | 1.575 [40.0] | 0.728 [18.5] | 1.653 [42.0] | 0.728 [18.5] | 1.693 [43.0] | 0.295 [7.5] | 0.150 [3.8] | 0.032 [0.81] | 20 |

TAPE AND REEL, SPECIFICATIONS TO EIA-468D in inches [millimeters]

Formed Leads


| DIMENSIONS in inches [millimeters] AND PACKAGING QUANTITIES | | |
|---|-----------------------|----------------------|
| CASE SIZE | F LEAD SPACING | STD. QTY/REEL |
| 0.236 x 0.453 [6.0 x 11.0] | 0.197 [5.0] | 800 |
| 0.315 x 0.472 [8.0 x 12.0] | 0.197 [5.0] | 700 |

Unformed (Straight) Leads


| DIMENSIONS in inches [millimeters] AND PACKAGING QUANTITIES | | |
|---|----------------------------|----------------------|
| CASE SIZE | F LEAD SPACING | STD. QTY/REEL |
| 0.236 x 0.453 [6.0 x 11.0] | 0.098 [2.5] | 800 |
| 0.315 x 0.472 [8.0 x 12.0] | 0.140 ⁽¹⁾ [3.5] | 700 |
| 0.394 x 0.512 [10.0 x 13.0] | 0.197 [5.0] | 500 |
| 0.394 x 0.630 [10.0 x 16.0] | 0.197 [5.0] | 500 |
| 0.394 x 0.787 [10.0 x 20.0] | 0.197 [5.0] | 500 |

Note
⁽³⁾ Available as special order.



| DIMENSIONS in inches [millimeters] | | | | | |
|--|-------------------------------|-------------------------------|--------------------------------|--------------------------------|--------------------------------|
| ITEM | CASE SIZE (DIAMETER x LENGTH) | | | | |
| | 0.236 x 0.433 [6.0 x 11.0] | 0.315 x 0.472 [8.0 x 12.0] | 0.394 x 0.512 [10.0 x 13.0] | 0.394 x 0.630 [10.0 x 16.0] | 0.394 x 0.787 [10.0 x 20.0] |
| d - Lead-wire diameter | 0.025 [0.63] | 0.025 [0.63] | 0.025 [0.63] | 0.025 [0.63] | 0.025 [0.63] |
| P - Pitch of component | 0.500 [12.7] | 0.500 [12.7] | 0.500 [12.7] | 0.500 [12.7] | 0.500 [12.7] |
| P ₀ - Feed hole pitch | 0.500 [12.7] | 0.500 [12.7] | 0.500 [12.7] | 0.500 [12.7] | 0.500 [12.7] |
| F - Lead-to-lead distance | 0.197 [5.0] | 0.197 [5.0] | 0.197 [5.0] | 0.197 [5.0] | 0.197 [5.0] |
| K - Clinch height | 0.098 [2.5] | 0.157 [4.0] | n/a | n/a | n/a |
| H - Height of component from tape center | 0.728 [18.5] | 0.787 [20.0] | 0.906 [23.0] | 0.906 [23.0] | 0.906 [23.0] |
| H ₀ - Lead-wire clinch height | 0.630 [16.0] | 0.630 [16.0] | n/a | n/a | n/a |
| W - Tape width | 0.709 [18.0] | 0.709 [18.0] | 0.709 [18.0] | 0.709 [18.0] | 0.709 [18.0] |
| W ₀ - Hold down tape width | 0.591 [15.0] | 0.591 [15.0] | 0.591 [15.0] | 0.591 [15.0] | 0.591 [15.0] |
| D ₀ - Feed hole diameter | 0.157 [4.0] | 0.157 [4.0] | 0.157 [4.0] | 0.157 [4.0] | 0.157 [4.0] |
| t - Total tape thickness | 0.028 [0.7] | 0.028 [0.7] | 0.028 [0.7] | 0.028 [0.7] | 0.028 [0.7] |
| L ₁ - Maximum lead protrusion | 0.118 [3.0] | 0.118 [3.0] | 0.118 [3.0] | 0.118 [3.0] | 0.118 [3.0] |

Note

- Terminal code "I" = tape and reel. Terminal code "+" = tape and ammo.
Positive leader is standard. Negative leader is available by special order.

ORDERING EXAMPLE

Electrolytic capacitor 678D series: 678D 108 M 6R3 DG 3 D

| DESCRIPTION | |
|-------------|---|
| CODE | EXPLANATION |
| 678D | Product type |
| 108 | Capacitance value (1000 µF) |
| M | Tolerance (M = ± 20 %) |
| 6R3 | Voltage rating at 105 °C (6R3 = 6.3 V) |
| DG | Can size (see Dimensions table) |
| 3 | Sleeve and sealing (3 = P.V.C. sleeve w/epoxy end seal) |
| D | Terminal code / packaging (D = bulk; straight leads) |

Note

- For lead (Pb)-free / RoHS compliant products add suffix "E3" to part number.
Example: 678D108M6R3DG3DE3

| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | |
|---|-----------------|-----------------------------|---------------------------|--------|--|---|
| CAPACITANCE (µF) | PART NUMBER | NOMINAL CASE SIZE D x L | MAX. ESR AT +25 °C (Ω) | | MAX. RIPPLE AT +105 °C (A) 20 kHz to 100 kHz | MAX. IMPEDANCE AT +25 °C (Ω) 100 kHz |
| | | | 20 Hz | 20 kHz | | |
| 6.3 WV_{DC} at 105 °C, SURGE = 9 V | | | | | | |
| 330.0 | 678D337M6R3CC3D | 0.394 x 0.512 [10.0 x 13.0] | 0.540 | 0.213 | 0.36 | 0.213 |
| 470.0 | 678D477M6R3CD3D | 0.394 x 0.630 [10.0 x 16.0] | 0.340 | 0.133 | 0.49 | 0.132 |
| 1000.0 | 678D108M6R3DG3D | 0.492 x 0.787 [12.5 x 20.0] | 0.200 | 0.071 | 0.83 | 0.070 |
| 2200.0 | 678D228M6R3EK3D | 0.630 x 0.984 [16.0 x 25.0] | 0.110 | 0.041 | 1.36 | 0.045 |
| 3300.0 | 678D338M6R3DS3D | 0.492 x 1.673 [12.5 x 42.5] | 0.067 | 0.031 | 1.67 | 0.032 |
| 4700.0 | 678D478M6R3FR3D | 0.709 x 1.417 [18.0 x 36.0] | 0.066 | 0.029 | 2.02 | 0.031 |
| 10 WV_{DC} AT 105 °C, SURGE = 13 V | | | | | | |
| 330.0 | 678D337M010CD3D | 0.394 x 0.630 [10.0 x 16.0] | 0.350 | 0.135 | 0.46 | 0.134 |
| 470.0 | 678D477M010CG3D | 0.394 x 0.787 [10.0 x 20.0] | 0.235 | 0.092 | 0.63 | 0.090 |
| 1000.0 | 678D108M010DM3D | 0.492 x 1.043 [12.5 x 26.5] | 0.120 | 0.062 | 0.98 | 0.061 |
| 2200.0 | 678D228M010EK3D | 0.630 x 0.984 [16.0 x 25.0] | 0.115 | 0.042 | 1.52 | 0.046 |
| 3300.0 | 678D338M010EN3D | 0.630 x 1.260 [16.0 x 32.0] | 0.085 | 0.038 | 1.56 | 0.041 |
| 4700.0 | 678D487M010FR3D | 0.709 x 1.417 [18.0 x 36.0] | 0.070 | 0.031 | 1.97 | 0.033 |



| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | |
|---|-----------------|-----------------------------|------------------------------------|--------|--|--|
| CAPACITANCE (μ F) | PART NUMBER | NOMINAL CASE SIZE D x L | MAX. ESR AT +25 °C (Ω) | | MAX. RIPPLE AT +105 °C (A) 20 kHz to 100 kHz | MAX. IMPEDANCE AT +25 °C (Ω) 100 kHz |
| | | | 20 Hz | 20 kHz | | |
| 16 WV_{DC} AT 105 °C, SURGE = 20 V | | | | | | |
| 220.0 | 678D227M016CC3D | 0.394 x 0.512 [10.0 x 13.0] | 0.585 | 0.217 | 0.40 | 0.217 |
| 330.0 | 678D337M016CD3D | 0.394 x 0.630 [10.0 x 16.0] | 0.370 | 0.137 | 0.52 | 0.136 |
| 470.0 | 678D477M016CG3D | 0.394 x 0.787 [10.0 x 20.0] | 0.250 | 0.098 | 0.70 | 0.094 |
| 1000.0 | 678D108M016DM3D | 0.492 x 1.043 [12.5 x 26.5] | 0.130 | 0.066 | 1.00 | 0.065 |
| 2200.0 | 678D228M016ER3D | 0.630 x 1.417 [16.0 x 36.0] | 0.074 | 0.032 | 1.78 | 0.034 |
| 3300.0 | 678D338M016FR3D | 0.709 x 1.417 [18.0 x 36.0] | 0.074 | 0.032 | 1.94 | 0.034 |
| 20 WV_{DC} AT 105 °C, SURGE = 30 V | | | | | | |
| 220.0 | 678D227M020CD3D | 0.394 x 0.630 [10.0 x 16.0] | 0.380 | 0.150 | 0.41 | 0.148 |
| 330.0 | 678D337M020CG3D | 0.394 x 0.787 [10.0 x 20.0] | 0.270 | 0.100 | 0.61 | 0.098 |
| 470.0 | 678D477M020DG3D | 0.492 x 0.787 [12.5 x 20.0] | 0.250 | 0.077 | 0.45 | 0.075 |
| 1000.0 | 678D108M020DT3D | 0.492 x 1.280 [12.5 x 33.5] | 0.115 | 0.048 | 0.78 | 0.045 |
| 2200.0 | 678D228M020ER3D | 0.630 x 1.417 [16.0 x 36.0] | 0.077 | 0.032 | 1.80 | 0.034 |
| 3300.0 | 678D338M020FV3D | 0.709 x 1.575 [18.0 x 40.0] | 0.061 | 0.026 | 2.25 | 0.028 |
| 25 WV_{DC} AT 105 °C, SURGE = 35 V | | | | | | |
| 100.0 | 678D107M025CC3D | 0.394 x 0.512 [10.0 x 13.0] | 0.700 | 0.250 | 0.32 | 0.250 |
| 220.0 | 678D227M025CG3D | 0.394 x 0.787 [10.0 x 20.0] | 0.300 | 0.105 | 0.59 | 0.100 |
| 330.0 | 678D337M025DG3D | 0.492 x 0.787 [12.5 x 20.0] | 0.270 | 0.078 | 0.79 | 0.076 |
| 470.0 | 678D477M025DM3D | 0.492 x 1.043 [12.5 x 26.5] | 0.160 | 0.067 | 0.97 | 0.068 |
| 1000.0 | 678D108M025DS3D | 0.492 x 1.673 [12.5 x 42.5] | 0.090 | 0.034 | 1.60 | 0.036 |
| 2200.0 | 678D228M025FV3D | 0.709 x 1.575 [18.0 x 40.0] | 0.062 | 0.026 | 2.22 | 0.028 |
| 40 WV_{DC} AT 105 °C, SURGE = 55 V | | | | | | |
| 47.0 | 678D476M040CC3D | 0.394 x 0.512 [10.0 x 13.0] | 0.950 | 0.265 | 0.28 | 0.265 |
| 100.0 | 678D107M040CD3D | 0.394 x 0.630 [10.0 x 16.0] | 0.580 | 0.165 | 0.38 | 0.165 |
| 330.0 | 678D337M040DM3D | 0.492 x 1.043 [12.5 x 26.5] | 0.200 | 0.068 | 0.93 | 0.070 |
| 470.0 | 678D477M040EK3D | 0.630 x 0.984 [16.0 x 25.0] | 0.133 | 0.046 | 1.28 | 0.050 |
| 1000.0 | 678D108M040ER3D | 0.630 x 1.417 [16.0 x 36.0] | 0.080 | 0.033 | 1.76 | 0.035 |
| 50 WV_{DC} AT 105 °C, SURGE = 75 V | | | | | | |
| 47.0 | 678D476M050CC3D | 0.394 x 0.512 [10.0 x 13.0] | 1.250 | 0.275 | 0.28 | 0.275 |
| 100.0 | 678D107M050CG3D | 0.394 x 0.787 [10.0 x 20.0] | 0.520 | 0.115 | 0.57 | 0.112 |
| 220.0 | 678D227M050DM3D | 0.472 x 1.043 [12.5 x 26.5] | 0.240 | 0.069 | 0.93 | 0.071 |
| 330.0 | 678D337M050EK3D | 0.630 x 0.984 [16.0 x 25.0] | 0.150 | 0.048 | 1.26 | 0.052 |
| 470.0 | 678D477M050DS3D | 0.492 x 1.673 [12.5 x 42.5] | 0.110 | 0.036 | 1.55 | 0.039 |
| 1000.0 | 678D108M050FV3D | 0.709 x 1.575 [18.0 x 40.0] | 0.077 | 0.028 | 2.15 | 0.032 |
| 63 WV_{DC} AT 105 °C, SURGE = 80 V | | | | | | |
| 33.0 | 678D336M063CC3D | 0.394 x 0.512 [10.0 x 13.0] | 1.600 | 0.288 | 0.27 | 0.288 |
| 47.0 | 678D476M063CD3D | 0.394 x 0.630 [10.0 x 16.0] | 1.000 | 0.180 | 0.37 | 0.180 |
| 100.0 | 678D107M063DG3D | 0.492 x 0.787 [12.5 x 20.0] | 0.450 | 0.093 | 0.72 | 0.090 |
| 220.0 | 678D227M063DT3D | 0.492 x 1.280 [12.5 x 33.5] | 0.160 | 0.055 | 1.10 | 0.054 |
| 220.0 | 678D227M063EK3D | 0.630 x 0.984 [16.0 x 25.0] | 0.170 | 0.050 | 1.23 | 0.054 |
| 330.0 | 678D337M063DS3D | 0.492 x 1.673 [12.5 x 42.5] | 0.130 | 0.038 | 1.51 | 0.040 |
| 470.0 | 678D477M063ER3D | 0.630 x 1.417 [16.0 x 36.0] | 0.120 | 0.035 | 1.70 | 0.038 |

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.