


Automotive 150 V, 3 A power Schottky rectifier





Features



- Negligible switching losses
- · Low forward voltage drop for higher efficiency and extended battery life
- · Surface mount miniature package
- · Low thermal resistance
- ECOPACK2 component

Applications

- DC / DC converter
- Reverse polarity protection
- · Freewheeling diodes
- Switching diode

Description

Packaged in SMB, this device is intended for use in automotive applications where low drop forward voltage is required to reduce power dissipation.

Product status
STPS3150-Y

Product summary			
Symbol Value			
I _{F(AV)}	3 A		
V _{RRM}	150 V		
T _{j(max.)}	175 °C		
V _{F(typ.)}	0.63 V		



1 Characteristics

Table 1. Absolute ratings (limiting values at 25 °C, unless otherwise specified)

Symbol	Parameter	Value	Unit
V _{RRM}	Repetitive peak reverse voltage, T _j = -40 °C to +175 °C	150	V
I _{F(AV)}	Average forward current, δ = 0.5, square wave	3	А
I _{FSM}	Surge non repetitive forward current	80	Α
T _{stg}	Storage temperature range	-65 to +175	°C
Tj	Operating junction temperature range ⁽¹⁾	-40 to +175	°C

^{1.} $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameter

Symbol	Parameter	Max. value	Unit	
$R_{th(j-l)}$	Junction to lead	20	°C/W	

For more information, please refer to the following application note:

• AN5088 : Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I_ (1)	I _R ⁽¹⁾ Reverse leakage current	T _j = 25 °C	$V_R = V_{RRM}$	-	0.4	2.0	μA
'R'		T _j = 125 °C		-	0.6	2.0	mA
		T _j = 25 °C	I _F = 3 A	-	0.78	0.82	
V _F ⁽²⁾	Forward voltage drop	T _j = 125 °C		-	0.63	0.67	V
VF.	Forward voltage drop	T _j = 25 °C	I _F = 6 A	-	0.85	0.89	v
		T _j = 125 °C	1F - 0 M	-	0.70	0.75	

- 1. Pulse test: $t_p = 5$ ms, $\delta < 2\%$
- 2. Pulse test: $t_p = 380 \ \mu s, \ \delta < 2\%$

To evaluate the conduction losses, use the following equation:

$$P = 0.59 \times I_{F(AV)} + 0.027 \times I_{F}^{2}_{(RMS)}$$


For more information, please refer to the following application notes related to the power losses :

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode

DS7256 - Rev 2 page 2/9



1.1 Characteristics (curves)






Figure 3. Normalized avalanche power derating versus pulse duration ($T_j = 125$ °C)




Figure 4. Relative variation of thermal impedance junction to ambient versus pulse duration (SMB)




Figure 5. Reverse leakage current versus reverse voltage applied (typical values)





Figure 6. Junction capacitance versus reverse voltage applied (typical values)



DS7256 - Rev 2 page 3/9



Figure 7. Forward voltage drop versus forward current





Figure 8. Thermal resistance junction to ambient versus copper surface under each lead (SMB)(typical values)



DS7256 - Rev 2 page 4/9




2 Package information


In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.


2.1 SMB package information

- Epoxy meets UL94, V0
- · Lead-free package

Figure 9. SMB package outline








DS7256 - Rev 2 page 5/9



Table 4. SMB package mechanical data

	Dimensions					
Ref.	Millin	neters	Inches (for reference only)			
	Min.	Max.	Min.	Max.		
A1	1.90	2.45	0.074	0.097		
A2	0.05	0.20	0.001	0.008		
b	1.95	2.20	0.076	0.087		
С	0.15	0.40	0.005	0.016		
D	3.30	3.95	0.129	0.156		
E	5.10	5.60	0.200	0.221		
E1	4.05	4.60	0.159	0.182		
L	0.75	1.50	0.029	0.060		

Figure 10. SMB recommended footprint



DS7256 - Rev 2 page 6/9



3 Ordering information

Table 5. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS3150UY	G315Y	SMB	0.107 g	2500	Tape and reel

DS7256 - Rev 2 page 7/9



Revision history

Table 6. Document revision history

Date	Version	Changes
03-Nov-2011	1	Initial release.
16-Jan-2020	2	Updated Figure 1, Figure 2 and Figure 8.

DS7256 - Rev 2 page 8/9



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics - All rights reserved

DS7256 - Rev 2 page 9/9