




Automotive 60 V, dual 3 A power Schottky rectifier



Features



- PPAP capable
- 175 °C maximum operation junction temperature
- V_{RRM} guaranteed from -40 °C to 175 °C
- · High surge current capability
- ECOPACK2 compliant component

Application

- · Reverse polarity protection in E.C.U
- DC/DC converters
- Freewheeling diodes

Description

The STPS660CSFY has been developed for applications requiring an optimized VF and leakage current characteristics.

These characteristics make it ideal for use in secondary rectification functions, such as DC/DC converters or freewheeling functions.

Product status link
STPS660CSFY

Product summary			
Symbol	Value		
I _{F(AV)}	2 X 3 A		
V _{RRM}	60 V		
T _j (max.)	175 °C		
V _F (typ.)	0.50 V		



1 Characteristics

Table 1. Absolute ratings (limiting values per diode at 25 °C, unless otherwise specified)

Symbol	P	Value	Unit		
V_{RRM}	Repetitive peak reverse voltage (T _j = -40 °C to +175 °C)			60	V
I=	Average forward current 5 = 0.5	Per diode	T _c = 160 °C	3	Α
I _{F(AV)}	Average forward current, $\delta = 0.5$	Per device	T _c = 160 °C	6	A
I _{FSM}	Surge non repetitive forward current $t_p = 10 \text{ ms sinusoidal}$			120	Α
P _{ARM}	Repetitive peak avalanche power t_p = 10 μ s, T_j = 125 $^{\circ}$ C			170	W
T _{stg}	Storage temperature range			-65 to +175	°C
T _j	Operating junction temperature range ⁽¹⁾			-40 to +175	°C

^{1.} $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameters

Symbol	Parameter	Тур.	Unit
R _{th(j-c)}	Junction to case total	1.5	°C/W

For more information, please refer to the following application note:

• AN5088: Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics (per diode)

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I_ (1)	I _R ⁽¹⁾ Reverse leakage current	T _j = 25 °C	V _R = V _{RRM}	-		19	μA
IR ^(*)		T _j = 125 °C		-	3	10	mA
	V _F ⁽²⁾ Forward voltage drop	T _j = 25 °C	I _F = 3 A	-	0.56	0.61	
		T _j = 125 °C		-	0.50	0.57	
V_(2)		T _j = 25 °C	I _F = 4 A	-	0.60	0.65	V
VF.		T _j = 125 °C		-	0.53	0.60	V
		T _j = 25 °C	I _F = 6 A	-	0.67	0.74	
		T _j = 125 °C	1F - 0 V	-	0.58	0.66	

^{1.} Pulse test: $t_p = 5$ ms, $\delta < 2\%$

To evaluate the conduction losses, use the following equation:

$$P = 0.37 \times I_{F(AV)} + 0.067 \times I_{F}^{2}_{(RMS)}$$

For more information, please refer to the following application notes related to the power losses:

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses in a power diode

DS13525 - Rev 1 page 2/9

^{2.} Pulse test: $t_p = 380 \ \mu s, \ \delta < 2\%$





1.1 **Characteristics (curves)**







Figure 2. Relative variation of thermal impedance junction to case versus pulse duration 1.0 0.9 0.8 0.7 0.6 0.5 0.2 0.1 0.0 1.E-04 1.E-02 1.E-01 1.E+00 1.E-03

applied (typical values, per diode) $I_R(mA)$ 1.E+00 1.E-01 1.E-04








DS13525 - Rev 1 page 3/9



Figure 7. Thermal resistance junction to ambient versus copper surface under tab (typical values, epoxy printed board FR4, e_{Cu} = 70 μ m) (PSMC (TO-277A))



DS13525 - Rev 1 page 4/9




2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 PSMC (TO-277A) package information

- Epoxy meets UL94,V0
- Cooling method : by conduction (C)

Figure 8. PSMC (TO-277A) package outline




DS13525 - Rev 1 page 5/9



Table 4. PSMC (TO-277A) package mechanical data

	Dimensions					
Ref.		Millimeters		Inches (for reference only)		
	Min.	Тур.	Max.	Min.	Тур.	Max.
А	1.00	1.10	1.20	0.039	0.043	0.047
b	1.05	1.20	1.35	0.041	0.047	0.053
b2	1.90	2.05	2.20	0.075	0.081	0.087
b4		0.75			0.029	
С	0.15	0.23	0.40	0.006	0.009	0.016
D	4.45	4.60	4.75	0.175	0.181	0.187
D1	4.25	4.40	4.45	0.167	0.173	0.175
D2	3.40	3.60	3.70	0.134	0.142	0.146
E	6.35	6.50	6.65	0.250	0.256	0.262
E1	6.05	6.10	6.15	0.238	0.240	0.242
E2	4.50	4.60	4.70	0.177	0.181	0.185
E3		3.94			1.55	
е		2.13			0.084	
e1		3.33			0.131	
G		1.20			0.047	
G1		0.70			0.027	
L	0.90	1.05	1.24	0.035	0.041	0.049
L4	0.02			0.0008		
L5	0.02			0.0008		

Figure 9. PSMC (TO-277A) package footprint in mm (in inches)



Note: For package and tape orientation, reel and inner box dimensions and tape outline please check TN1173

DS13525 - Rev 1 page 6/9



3 Ordering information

Table 5. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS660CSFY	PS660CY	PSMC (TO-277A)	90 mg	6000	Tape and Reel

DS13525 - Rev 1 page 7/9



Revision history

Table 6. Document revision history

Date	Version	Changes
26-Oct-2020	1	Initial release.

DS13525 - Rev 1 page 8/9



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics - All rights reserved

DS13525 - Rev 1 page 9/9