


Automotive 60 V low I_r power Schottky rectifier



Features



- AEC-Q101 qualified
- Low leakage current
- Negligible switching losses
- Avalanche capability specified
- 175 °C maximum junction temperature
- V_{RRM} guaranteed from -40 °C to 175 °C
- · Wettable flanks for automatic visual inspection
- PPAP capable
- ECOPACK®2 compliant component

Application

- DC/DC converters
- Reverse polarity protection
- · Freewheeling diodes
- Switching diodes

Description

The STPS10H60SFY power Schottky rectifier has been designed for automotive applications.

Packaged in PSMC (TO-277A), this device provides a very low V_{F} in a compact package which can withstand high operating junction temperature.

Product status link			
STPS10H60SFY			
Product summary			
Symbol	Value		
I _{F(AV)}	10 A		
V _{RRM}	60 V		
T _j (max.)	175 °C		
V _F (typ.)	0.53 V		



1 Characteristics

Table 1. Absolute ratings (limiting values at 25 °C, unless otherwise specified with 2 anode terminals short-circuited)

Symbol	Parameter	Value	Unit	
V _{RRM}	Repetitive peak reverse voltage (T_j = -40 °C to +175	60	V	
I _{F(AV)}	Average forward current, δ = 0.5 T_c = 140 °C		10	Α
I _{FSM}	Surge non repetitive forward current $t_p = 10 \text{ ms sinusoidal}$		210	Α
P _{ARM}	Repetitive peak avalanche power t_p = 10 μ s, T_j = 125 $^{\circ}$ C		145	W
T _{stg}	Storage temperature range	-65 to +175	°C	
Tj	Operating junction temperature range ⁽¹⁾	-40 to +175	°C	

^{1.} $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameters

Symbol	Parameter	Тур.	Unit
$R_{th(j-c)}$	Junction to case	2.4	°C/W

For more information, please refer to the following application note:

AN5088: Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics (anode terminals short-circuited)

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
ı (1)	I _R ⁽¹⁾ Reverse leakage current	T _j = 25 °C	V _R = V _{RRM}	-		20	μA
'R'		T _j = 125 °C		-	2	10	mA
		T _j = 25 °C	I _F = 5 A	-		0.65	V
V _F ⁽²⁾	Forward voltage drop	T _j = 125 °C		-	0.515	0.58	
V _F ····································	Forward voltage drop	T _j = 25 °C		-		0.79	V
		T _j = 125 °C		-	0.60	0.67	

^{1.} Pulse test: t_p = 5 ms, δ < 2%

To evaluate the conduction losses, use the following equation:

$$P = 0.49 \times I_{F(AV)} + 0.018 \times I_{F^{2}(RMS)}$$

For more information, please refer to the following application notes related to the power losses:


- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses in a power diode

DS12671 - Rev 1 page 2/11

^{2.} Pulse test: $t_p = 380 \ \mu s, \ \delta < 2\%$




1.1 **Characteristics (curves)**



to case versus pulse duration 1.0 0.9 0.8 0.7 0.6 0.5 0.3 0.2 0.1 $t_P(s)$ 0.0 1.E-04 1.E-03 1.E-02 1.E-01 1.E+00


Figure 2. Relative variation of thermal impedance junction

applied (typical values) $I_R(\mu A)$ 1.E+04 1.E+03 1.E+02 1.E+01 1.E+00 1.E-01



DS12671 - Rev 1 page 3/11









Figure 7. Thermal resistance junction to ambient versus copper surface under tab (typical values, epoxy printed board FR4, e_{Cu} = 35 μ m) (PSMC (TO-277A))



DS12671 - Rev 1 page 4/11



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK[®] is an ST trademark.

2.1 PSMC (TO-277A) package information

- Epoxy meets UL94,V0
- Cooling method : by conduction (C)




Figure 8. PSMC (TO-277A) package outline

Table 4. PSMC (TO-277A) package mechanical data


	Dimensions						
Ref.	ef.		Millimeters		Inches (for reference only)		
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А	1.00	1.10	1.20	0.039	0.043	0.047	
b	1.05	1.20	1.35	0.041	0.047	0.053	
b2	1.90	2.05	2.20	0.075	0.081	0.087	
b4		0.75			0.029		
С	0.15	0.23	0.40	0.006	0.009	0.016	
D	4.45	4.60	4.75	0.175	0.181	0.187	
D1	4.25	4.40	4.45	0.167	0.173	0.175	
D2	3.40	3.60	3.70	0.134	0.142	0.146	

DS12671 - Rev 1 page 5/11



	Dimensions						
Ref.	Millimeters			Inches (for reference only)			
	Min.	Тур.	Max.	Min.	Тур.	Max.	
E	6.35	6.50	6.65	0.250	0.256	0.262	
E1	6.05	6.10	6.15	0.238	0.240	0.242	
E2	4.50	4.60	4.70	0.177	0.181	0.185	
E3		3.94			1.55		
е		2.13			0.084		
e1		3.33			0.131		
G		1.20			0.047		
G1		0.70			0.027		
L	0.90	1.05	1.24	0.035	0.041	0.049	
L4	0.02			0.0008			
L5	0.02			0.0008			

Figure 9. PSMC (TO-277A) package footprint in mm (in inches)



DS12671 - Rev 1 page 6/11




Figure 10. PSMC (TO-277A) marking



E : ECOPACK grade XXXX : Marking

ZZ : Manufacturing location Y : Year WW : week

Figure 11. Package orientation in reel



Taped according to EIA-481


Note: Pocket dimensions are not on scale


Pocket shape may vary depending on package

Cathode band only on unidirectional devices



Figure 13. 13" reel dimension values






DS12671 - Rev 1 page 7/11



Figure 15. Tape outline



Note: Pocket dimensions are not on scale Pocket shape may vary depending on package

Table 5. Tape dimension values

	Dimensions						
Ref.	Millimeters						
	Min.	Тур.	Max.				
D0	1.5	1.55	1.6				
D1	1.5						
F	5.45	5.5	5.55				
K0	1.3	1.4	1.5				
P0	3.9	4.0	4.1				
P1	7.9	8.0	8.1				
P2	1.95	2.0	2.05				
W	11.7	12	12.3				

DS12671 - Rev 1 page 8/11



3 Ordering information

Table 6. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS10H60SFY	S10H60Y	PSMC (TO-277A)	90 mg	6000	Tape and Reel

DS12671 - Rev 1 page 9/11



Revision history

Table 7. Document revision history

Date	Version	Changes
06-Aug-2018	1	Initial release.

DS12671 - Rev 1 page 10/11



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics - All rights reserved

DS12671 - Rev 1 page 11/11