


雅晶鑫電子

Shenzhen Yajingxin Electron Co.,Ltd

Customer	
Production Name	SMD OSC SEAM2.5*2.0
Customer P/N	N/A
P/N	F0252032768K4HFBN2T
Revision	A
Print Date	2022-09-20



Drawn	Checked	Approved




RoHS Compliant


■ Electrical Specifications

1.Model No	2520 OSC	
2.Nominal Frequency	32.768KHz	
3.Mode of Oscillation	Fundamental	
4.Operating Temperature Range	-20°C to 70 °C	
5.Storage Temperature Range	-55°C to +125°C	
6.Frequency Stability	±30ppm	
7.Power Supply Voltage	3.3V±10%	
8.Input Current	10mA Max. :	
9.Output Voltage	Logic High(Voh)	90%Vdd Min
	Logic Low(Vol)	10%Vdd Max
10.Output Load	15pF max CMOS Load	
11.Semmetry (at 50%VDD)	40-60%Normal	
12.Rise & Fall Time	50ns Max.	
13.E/D or N/C.	Tri-state	
14.Output Disable Time	100nsec	
15.Output Enable Time(start-up time)	10msec max	
16.Aging	±3ppm/year	
17.Unit Weight		

■ Part Number Configuration



■ Dimensions



■ Marking



Line 1: 客户指定印字 →

Line 2: ● → Pin#1 indication




■ Measurement Circuit


Output Wave Form



■ Input Output Condition



■ Reflow Profile



■ Reliability Specifications

No	Test Item	Test Methods
1	DROP TEST	Device are dropped from a height of 75 cm onto 3 mm thickness stainless plate executing 3 times of random drops.
2	MECHANICAL SHOCK	Device are shocked to half sine wave (1000 G) three mutually perpendicular axes each 3 times.
3	High Temp and Humidity Test	85°C/RH 85%, 500Hrs
4	High temp storage test	125°C+/-2°C 500Hrs
5	Low temp storage test	-40°C 500Hrs
6	Thermal shock test	-40°C~+85°C DWEL 60' 100cycles
7	Aging test	85°C 1000Hrs
8	Resistance to solder heat	260°C 10S
9	VIBRATION	Frequency range 10-2000 Hz Amplitude Sweep 1.5 mm Sweep Time 20 minute Test Time 2 hours
10	SOLDERABILITY	MIL - STD - 20E Method 208C Temperature 245°C±5°C Material H63A (Silver 2-3 %) Immersion depth 0.5 mm minimum Immersion time 3 ± 0.5 seconds Flux Rosin resin methyl