DATASHEET

8 PIN DIP LOW INPUT CURRENT HIGH GAIN SPLIT DARLINGTON PHOTOCOUPLER
6N138 6N139



Schematic



Pin Configuration
1. No Connection
2. Anode
3. Cathode
4. No Connection
5. Gnd
6. V_{out}
7. V_B
8. V_{CC}

Features

- High current transfer ratio–2000% typical
- High isolation voltage between input and output (Viso=5000 Vrms)
- Guaranteed performance from 0°C to 70°C
- Pb free and RoHS compliant.
- UL and cUL approved(No. E214129)
- VDE approved (No. 132249)
- SEMKO approved
- NEMKO approved
- DEMKO approved
- FIMKO approved

Description

The 6N138 and 6N139 devices each consists of an infrared emitting diode, optically coupled to a high gain split Darlington photo detector. They provide extremely high current transfer ratio between input and output, with access to a base terminal to adjust the gain bandwidth.These devices are packaged in an 8-pin DIP package and available in wide-lead spacing and SMD options.

Applications

- Digital logic ground isolation
- RS-232C line receiver
- Low input current line receiver
- Microprocessor bus isolation
- Current loop receiver

Absolute Maximum Ratings (Ta=25℃)

Parameter			Symbol	Rating	Unit
Input	Forward current		I_F	20	mA
	Peak forward current (50% duty, 1ms P.W)		I_{FP}	40	mA
	Peak transient Current (≤1μs P.W,300pps)		I_{Ftrans}	1	A
	Reverse voltage		V_R	5	V
	Power dissipation		P_{IN}	45	mW
Output	Power dissipation		P_O	100	mW
	Output current		I_O	60	mA
	Emitter-Base Reverse Voltage		V_{ER}	0.5	V
	Output voltage	6N138 6N139	V_O	-0.5 to 7 -0.5 to 18	V
	Supply voltage	6N138 6N139	V_{CC}	-0.5 to 7 -0.5 to 18	V
Isolation voltage *1			V_{ISO}	5000	V rms
Operating temperature			T_{OPR}	-40 ~ +85	°C
Storage Temperature			T_{STG}	-55 ~ +125	°C
Soldering temperature *2			T_{SOL}	260	°C

Notes:
*1 AC for 1 minute, R.H.= 40 ~ 60% R.H. In this test, pins 1, 2, 3, 4 are shorted together, and pins 5, 6, 7, 8 are shorted together.

*2 For 10 seconds

Electrical Characteristics (T_A=0 to 70°C unless specified otherwise

Input

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Forward voltage	V_F	-	1.3	1.7	V	I_F = 1.6mA
Reverse Voltage	V_R	5.0	-	-	V	I_R = 10μA, T_A=25°C
Temperature coefficient of forward voltage	$\Delta V_F/\Delta T_A$	-	-1.8	-	mV/°C	I_F =1.6mA

Output

Parameter		Symbol	Min	Typ.	Max.	Unit	Condition
Logic High Output Current	6N138	I_{OH}	-	0.01	100	μA	I_F=0mA, V_O=V_{CC}=18V
	6N139		-	-	250		
Logic Low Supply Current	6N138	I_{CCL}	-	0.6	1.5	mA	I_F=1.6mA, V_O=Open, V_{CC}=18V
	6N139						
Logic High Supply Current	6N138	I_{CCH}	-	0.05	10	μA	I_F=0mA, V_O=Open, V_{CC}=18V
	6N139						

Transfer Characteristics (T_a=0 to 70°C unless specified otherwise, Vcc=4.5V)

Parameter		Symbol	Min	Typ.	Max.	Unit	Condition
Current Transfer Ratio	6N139	CTR	400	2500	-	%	I_F = 0.5mA, V_O = 0.4V, V_{CC}=4.5V
			500	2000	-		I_F = 1.6mA, V_O = 0.4V, V_{CC}=4.5V
	6N138		300	2000	-		
Logic Low Output Voltage	6N139	V_{OL}	-	0.05	0.4	V	I_F = 0.5mA, I_O = 2mA, V_{CC}=4.5V
			-	0.09	0.4		I_F = 1.6mA, I_O = 8mA, V_{CC}=4.5V
			-	0.12	0.4		I_F = 5mA, I_O = 15mA, V_{CC}=4.5V
			-	0.17	0.4		I_F = 12mA, I_O = 24mA, V_{CC}=4.5V
	6N138		-	0.06	0.4		I_F = 1.6mA, I_O = 4.8mA, V_{CC}=4.5V

Switching Characteristics (T_a=0 to 70°C unless specified otherwise, Vcc=5V)

Parameter		Symbol	Min	Typ.	Max.	Unit	Condition
Propagation Delay Time to Logic Low (Fig. 13)	6N139	T_{PHL}	-	5	25	µs	I_F = 0.5mA , R_L=4.7kΩ, T_A=25°C
			-	-	30		I_F = 0.5mA , R_L=4.7kΩ
			-	0.2	1		I_F = 12mA , R_L=270Ω, T_A=25°C
			-	-	2		I_F = 12mA , R_L=270Ω
	6N138		-	1.4	10		I_F = 1.6mA , R_L=2.2kΩ, T_A=25°C
			-	-	15		I_F = 1.6mA , R_L=2.2kΩ
Propagation Delay Time to Logic High (Fig. 13)	6N139	T_{PLH}	-	16	60	µs	I_F = 0.5mA , R_L=4.7kΩ, T_A=25°C
			-	-	90		I_F = 0.5mA , R_L=4.7kΩ
			-	1.7	7		I_F = 12mA , R_L=270Ω, T_A=25°C
			-	-	10		I_F = 12mA , R_L=270Ω
	6N138		-	8	35		I_F = 1.6mA , R_L=2.2kΩ, T_A=25°C
			-	-	50		I_F = 1.6mA , R_L=2.2kΩ
Common Mode Transient Immunity at Logic High (Fig. 14) *3		CM_H	1,000	-	-	V/µs	I_F = 0mA , V_{CM}=10Vp-p, R_L=2.2KΩ, T_A=25°C
Common Mode Transient Immunity at Logic Low (Fig. 14) *3		CM_L	1,000	-	-	V/µs	I_F = 1.6mA , V_{CM}=10Vp-p, R_L=2.2KΩ, T_A=25°C

* Typical values at T_a = 25°C

Typical Electro-Optical Characteristics Curves

Fig.1 LED Forward Current vs. Forward Voltage



Fig.2 LED Forward Voltage vs. Temperature



Fig.3 Output Current vs. Output Voltage



Fig.4 Output Current vs. Input Diode Forward Current



Fig.5 Current Transfer Ratio vs. Forward Current



Fig.6 Current Transfer Ratio vs. Base-Emitter Resistance



Fig.7 Non-saturated Rise nand Fall Times vs. Load Resistance



Fig.8 Propagation Delay To Logic Low vs. Base-Emitter Resistance



Fig.9 Propagation Delay vs. Input Diode Forward Current



Fig.10 Propagation Delay to Logic Low vs. Pulse Period



Fig.11 Propagation Delay vs. Temperature



Fig.12 Logic Low Supply Current vs. Input Diode Forward Current



Fig. 13 Switching Time Test Circuit and Waveform



Fig. 14 Common Mode Transient Immunity Test Circuit and Waveform



Note:

*3 Common mode transient immunity in logic high level is the maximum tolerable (positive) dVcm/dt on the leading edge of the common mode pulse signal VCM, to assure that the output will remain in a logic high state (i.e., VO > 2.0V).
Common mode transient immunity in logic low level is the maximum tolerable (negative) dVcm/dt on the trailing edge of the common mode pulse signal, VCM, to assure that the output will remain in a logic low state (i.e., VO < 0.8V).

Order Information

Part Number

6N13XY(Z)-V

Note

X = Part No. (X = 8 or 9)
Y = Lead form option (S, S1, M or none)
Z = Tape and reel option (TA, TB or none).
V = VDE (optional)

Option	Description	Packing quantity
None	Standard DIP-8	45 units per tube
M	Wide lead bend (0.4 inch spacing)	45 units per tube
S (TA)	Surface mount lead form + TA tape & reel option	1000 units per reel
S (TB)	Surface mount lead form + TB tape & reel option	1000 units per reel
S1 (TA)	Surface mount lead form (low profile) + TA tape & reel option	1000 units per reel
S1 (TB)	Surface mount lead form (low profile) + TB tape & reel option	1000 units per reel

Package Dimension
(Dimensions in mm)

Standard DIP Type



Option M Type



Option S Type



Option S1 Type



Recommended pad layout for surface mount leadform



Notes.
Suggested pad dimension is just for reference only.
Please modify the pad dimension based on individual need.

Device Marking



Notes

T	denotes Factory No code : made in China T : made in Taiwan
EL	denotes EVERLIGHT
6N138	denotes Device Number
Y	denotes 1 digit Year code
WW	denotes 2 digit Week code
V	denotes VDE (optional)

Tape & Reel Packing Specifications

Option TA



Direction of feed from reel

Option TB



Direction of feed from reel

Tape dimension



Dimension No.	A	B	Do	D1	E	F
Dimension(mm)	10.4±0.1	10.0±0.1	1.5+0.1/-0	1.5±0.25	1.75±0.1	7.5±0.1
Dimension No.	Po	P1	P2	t	W	K
Dimension(mm)	4.0±0.1	12.0±0.1	2.0±0.05	0.4±0.05	16.0±0.3	4.5±0.1

Precautions for Use

1. Soldering Condition

1.1 (A) Maximum Body Case Temperature Profile for evaluation of Reflow Profile



Note: Reference: IPC/JEDEC J-STD-020D

Preheat	
Temperature min (T_{smin})	150 °C
Temperature max (T_{smax})	200°C
Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds
Average ramp-up rate (T_{smax} to T_p)	3 °C/second max
Other	
Liquidus Temperature (T_L)	217 °C
Time above Liquidus Temperature (t_L)	60-100 sec
Peak Temperature (T_P)	260°C
Time within 5 °C of Actual Peak Temperature: T_P - 5°C	30 s
Ramp- Down Rate from Peak Temperature	6°C /second max.
Time 25°C to peak temperature	8 minutes max.
Reflow times	3 times

.

DISCLAIMER

1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
2. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
3. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
4. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without the specific consent of EVERLIGHT.
5. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.
6. Statements regarding the suitability of products for certain types of applications are based on Everlight's knowledge of typical requirements that are often placed on Everlight products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Everlight's terms and conditions of purchase, including but not limited to the warranty expressed therein.