



表面安装超快速整流二极管


反向电压 50~1000 V

正向电流 2.0 A

Surface Mount Super Fast Recovery Rectifiers

Reverse Voltage 50~1000 V

Forward Current 2.0 A

**特征 Features**

- 反向漏电流低 Low reverse leakage
- 正向浪涌承受能力强 High forward surge capability
- 高信赖性 High reliability
- 高温焊接保证 High temperature soldering guaranteed:
260°C/10 秒
260°C/10seconds
- 引线和管体皆符合RoHS标准 Lead and body according with RoHS standard
- 型号后缀“-F”标记无卤素产品 Green compound with suffix "-F" on Marking

机械数据 Mechanical Data

- 封装外形:SMAF 塑封 Case:SMAF Molded plastic
- 环氧树脂 : UL易燃等级 : 94V-0
Epoxy: UL 94V-0 rate flame retardant
- 引脚 : 镀锡,无铅 Lead: Pure tin plated, lead free




最大值和特性 TA = 25°C 除非另有规定。**Maximum Ratings & Characteristics**

Ratings at 25°C ambient temperature unless otherwise specified.

参数 Parameter	符号 Symbols	RS2AF	RS2BF	RS2DF	RS2GF	RS2JF	RS2KF	RS2MF	单位 Unit
最大可重复峰值反向电压 Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	V
最大均方根电压 Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
最大直流阻断电压 Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	1000	V
最大正向平均整流电流 Maximum average forward rectified current	I _(AV)								A
正向不重复浪涌电流 8.3 ms单一正弦半波 Non-repetitive peak forward surge current 8.3 ms singlehalf sine-wave	I _{FSM}								A
最大正向电压 @IF=2.0A Maximum forward voltage	V _F								V
最大反向电流 @V _{DC} TA= 25°C Maximum reverse current TA= 125°C	I _R								μA
最大反向恢复时间 IF=0.5A , IR=1.0A ,IRR=0.25A MAX. reverse recovery time	T _{RR}								nS
典型热阻 Typical thermal resistance (Note 1)	R _{θJA}								°C/W
典型结电容 VR=4.0V,f=1MHz Type junction capacitance	C _J								pF
工作结温和存储温度 Operating junction and storage temperature rang	T _J , T _{STG}								°C

备注 Note:

- 1) 安装在PCB板上，从PN结到周围环境的热阻。
- 1) Thermal resistance from junction to ambient, PCB mounted.

特性曲线 Characteristic Curves
正向特性曲线 (典型值)
TYPICAL FORWARD CHARACTERISTIC

正向电流降额曲线
FORWARD CURRENT DERATING CURVE

浪涌特性曲线 (最大值)
MAXIMUM NON REPETITIVE
PEAK FORWARD SURGE CURRENT

反向特性曲线
Typical Reverse Characteristics
