

SM1150A

Schottky Barrier Rectifiers

Reverse Voltage 150V Forward Current 1.0A

FEATURES

- * Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- * Low power loss,high efficiency
- * For use in low voltage high frequency inverters, free wheeling,and polarity protection applications
- * Guardring for over voltage protection
- * High temperature soldering guaranteed: 260°C/10 seconds at terminals

Mechanical Data

Case: JEDEC DO-214AC,
molded plastic


Terminals: Plated axial leads, solderable per
MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end

Mounting Position: Any

Weight: 0.0023 oz., 0.065 g

Handling precaution:None



We declare that the material of product is
Halogen free (green epoxy compound)

1.Electrical Characteristic

Maximum & Thermal Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Parameter Symbol	symbol	SM1150A	Unit
device marking code		S115	
Maximum repetitive peak reverse voltage	V_{RRM}	150	V
Maximum RMS voltage	V_{RMS}	105	V
Maximum DC blocking voltage	V_{DC}	150	V
Maximum average forward rectified current at TC= 75°C	IF(AV)	1.0	A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	30	A
Typical thermal resistance (Note 1)	R θ JA	150	°C/W
Operating junction and storage temperature range	TJ, TSTG	-40 to +150	°C

Electrical Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Parameter Symbol	symbol	SM1150A	Unit
Maximum instantaneous forward voltage at 1.0A	V_F	0.85	V
Maximum DC reverse current TA = 25°C at rated DC blocking voltage TJ = 100°C	IR	0.5 10.0	mA
Typical junction capacitance at 4.0V, 1MHz	CJ	80	PF

NOTES:

1. 8.0mm² (.013mm thick) land areas

S-SM1150A

2. Ratings and Characteristic Curves (TA = 25°C unless otherwise noted)

Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-repetitive Peak Forward Surge Current




Fig 3. - Typical Instantaneous Forward Characteristics




Fig 4. - Typical Reverse Characteristics




Fig 5. - typical transient thermal impedance






Fig 6. - Typical Junction Capacitance



SM1150A

3. dimension:



SM1150A

4. Update Record

版次	更新记录	更新作者	更新日期
1	第一版	谭志伟	2018-9-12