



OSCILLATOR UNIT WITH LVPECL OUTPUT IN SMD 7.0x5.0MM CERAMIC SEAM SEAL PACKAGE.


PRODUCT FEATURES

- Small dimensions 7.0x5.0x1.6 with 6 solder pads.
- Highly reliable seam sealed ceramic package.
- wide frequency range.
- Low jitter and phase noise.
- RoHS compliant, LEAD-FREE and HALOGEN-FREE.

APPLICATIONS

- High speed communication
- Handheld equipment
- Telecom equipment

PRODUCT PHOTO (NOT IN SCALE)




PRODUCT SPECIFICATIONS

| PARAMETER | 1575P6 | CONDITIONS / REMARKS |
|-----------------------------|---|--|
| Nominal frequency range | 10 ~ 800MHz | Fund., Overtone or PLL |
| Supply voltage | 2.5V _{DC} / 3.3V _{DC} | Other option possible |
| Supply current | 100mA | Maximum, Fund mode lower I _{CC} |
| Frequency stability | ±25ppm / ±50ppm / ±100ppm | See note below. |
| Operating temperature range | -10 to +70°C or -40 to 85°C | Other options available. |
| Output waveform and load | LVPECL / 50Ω | Into V _{CC-2} |
| Output voltage level HIGH | V _{CC} -1.025V / V _{CC} -0.880V | Minimum / Maximum |
| Output voltage level LOW | V _{CC} -1.810V / V _{CC} -1.620V | Minimum / Maximum |
| Rise and Fall times | 1.5ns | @ 20~80~20%V _{CC} |
| Symmetry (duty cycle) | 45~55% | @ outputs cross point |
| Phase Jitter RMS | <1ps | Integrated 12kHz≤F _j ≤20MHz |

Note: Stability includes frequency deviations at +25°C, over temperature range, due to supply voltage changes, output load changes, shock and vibration.

PACKAGE OUTLINE / DIMENSIONS



PACKAGING INFORMATION

- Tape & Reel compliant to EIA-481.
- Embossed carrier width 16mm.
- Component pitch in carrier 8mm.
- Reel diameter 180mm.
- QTY per reel: 1,000pcs

RECOMMENDED REFLOW PROFILE

