
3VM-41QR10/610 MOS FET Relays S-VSON 4-pin, Low-output-capacitance and Low-ON-resistance Type (with Low C × R)

World's smallest class * **New S-VSON Package** with Low Output Capacitance and Low ON Resistance

- Load voltage: 40 V / 60 V.
- G3VM-41QR10: Low C × R = 4.95 pF· Ω , Coff (standard) = 0.45 pF, Rox (standard) = 11 Ω
- G3VM-61QR: Low C × R = 13.2 pF $\cdot\Omega$, Coff (standard) = 12 pF, Ron (standard) = 1.1 Ω
- High Ambient operating temperature: -40°C to +110°C

* As of March 2018 Survey by OMRON.




Note: The actual product is marked differently from the image shown here.

RoHS Compliant

Application Examples

- Semiconductor test equipment
- Communication equipment
- Test & measurement equipment Data loggers
- Package (Unit: mm, Average)



Note: The actual product is marked differently from the image shown here.

Model Number Legend

- 1. Load Voltage
 - 4: 40V

G

- 6: 60 V
- 4. Additional functions
- R: Low On-resistance
- 2. Contact form Package type 3. Package type 1: 1a (SPST-NO)
- 5. Other informations
 - When specifications overlap, serial code is added in the recorded order.
- Q: S-VSON 4 pin
 - S-VSON(L)* 4 pin
 - * (L): Low profile type

Ordering Information

	Contact form	Terminals	Load voltage (peak value) *	Continuous load current (peak value) *	Packing/Tape cut		Packing/Tape & reel		
Package type					Model	Minimum package quantity	Model	Minimum package quantity	
S-VSON4(L)4	1a	Surface-mounting	40 V	120 mA	G3VM-41QR10	1 pc.	1	G3VM-41QR10 (TR05)	500 pcs.
S-VSON4	(SPST-NO)	Terminals	60 V	400 mA	G3VM-61QR		G3VM-61QR (TR05)	500 pcs.	

* The AC peak and DC value are given for the load voltage and continuous load current.

Note: When ordering tape packing, add "(TR05)" (500 pcs/reel) to the model number.

Ask your OMRON representative for orders under 500 pcs. We can supply products with the tape already cut.

Tape-cut S-VSON is packaged without humidity resistance. Use manual soldering to mount them. Refer to common precautions.

■Absolute Maximum Ratings (Ta = 25°C)


Item		Symbol	G3VM-41QR10	G3VM-61QR	Unit	Measurement conditions
	LED forward current	lF	30		mA	
Input	LED forward current reduction rate	∆I⊧/°C	-0.3		mA/°C	Ta≥25°C
g	LED reverse voltage	VR	6		V	
	Connection temperature	TJ	12	25	°C	
	Load voltage (AC peak/DC)	Voff	40	60	V	
Ħ	Continuous load current (AC peak/DC)	lo	120	400	mA	
Outpi	ON current reduction rate	∆lo/°C	-1.2	-4	mA/°C	Ta≥25°C
0	Pulse ON current	ЮР	0.36	1.2	Α	t = 100 ms, Duty = 1/10
	Connection temperature	TJ	125		°C	
Dielectric strength between I/O *		VI-0	500		Vrms	AC for 1 min
Ambient operating temperature		Ta	-40 to +110		°C	With no icing or condensation
Ambient storage temperature		Tstg	-40 to +125		°C	
Soldering temperature		-	260		°C	10 s


* The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

■Electrical Characteristics (Ta = 25°C)

Item		Symbol		G3VM-41QR10	G3VM-61QR	Unit	Measurement conditions	
		VF	Minimum	1.1 1.21		v		
	LED forward voltage		Typical				IF = 10 mA	
			Maximum	1.4				
Input	Reverse current	IR	Maximum	1()	μA	V _R = 5 V	
dul	Capacity between terminals	Ст	Typical	30		pF	V = 0, f = 1 MHz	
	Trigger LED forward current	IFT	Typical	0.8	-	mA	lo = 100 mA	
	Thgger LED forward current	IFT	Maximum	3	3		10 = 100 MA	
	Release LED forward current	IFC	Minimum	0.1		mA	Ιογγ = 10 μΑ	
			Typical	11	1.1	Ω	G3VM-41QR10: I⊧ = 5 mA,	
ıt	Maximum resistance with output ON	Ron	Maximum	14	1.5		t<1s, lo = 120 mA G3VM-61QR: l⊧ = 5 mA, t<1s, lo = 400 mA	
Output	Current leakage when the relay is open	Ileak	Maximum	1	1000 (1)	nA	G3VM-41QR10: Voff = 40 V G3VM-61QR: Voff = 60 V (Voff = 50 V)	
		Coff	Typical	0.45	12	pF	V = 0, f = 100 MHz, t<1s	
	Capacity between terminals		Maximum	0.8	20	рг	$v = 0, i = 100 \text{ iv}(\Pi Z, l < 1S)$	
Ca	pacity between I/O terminals	CI-0	Typical	1	0.9	pF	f = 1 MHz, $Vs = 0V$	
Insulation resistance between I/O terminals		Ri-o	Typical	108		MΩ	V⊦o = 500 VDC, RoH≤60%	
			Typical	0.08	-			
Tur	rn-ON time	ton	Maximum	0.2	0.5 (0.25)	ms	IF = 5 mA, RL = 200 Ω, VDD = 20 V 	
			Typical	0.04	-		$-(1F = 10 \text{ mA}, \text{ RL} = 200 \Omega_2,$ $V_{DD} = 20 \text{ V}) *$	
Turn-OFF time		toff	Maximum	0.3	0.3 (0.3)	ms		

* Turn-ON and Turn-OFF Times





Recommended Operating Conditions

For usage with high reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.


Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.

Item	Symbol		G3VM-41QR10	G3VM-61QR	Unit
Load voltage (AC peak/DC)	Vdd	Maximum	32	48	V
		Minimum	5		mA
Operating LED forward current	lF	Typical	7.5		
		Maximum	20		
Continuous load current (AC peak/DC)	lo	Maximum	120	400	
Ambient operating temperature	Ta	Minimum	-20		°C
Ambient operating temperature	la	Maximum	85	100	U


G3VM-41QR10/61QR

■Engineering Data


•LED forward current vs. Ambient temperature




•Continuous load current vs. On-state voltage




•Turn ON, Turn OFF time vs. LED forward current




•Current leakage vs. Ambient temperature







•On-state resistance vs. Ambient temperature




•Turn ON, Turn OFF time vs. Ambient temperature




•Output terminal capacitance vs. Load voltage




LED forward current vs. LED forward voltage



Trigger LED forward current vs. Ambient temperature



Current leakage vs. Load voltage



N

G3VM-41QR10/61QR

■Appearance / Terminal Arrangement / Internal Connections

■Appearance

S-VSON (Super-Very Small Outline Non-leaded)

S-VSON4 pin / S-VSON(L)4 pin Model name *

> 600 з

> > LOT.NO.

Pin 1 mark

Actual model nam each model	e marking f	0
Model	Marking	
G3VM-41QR10	4QA	
G3VM-61QR	6Q0	


Note 1. The actual product is marked differently from the image shown here. 2. "G3VM" does not appear in the model number on the Relay.

■Dimensions (Unit: mm)

S-VSON (Super-Very Small Outline Non-leaded) S-VSON4 pin

Surface-mounting Terminals






1.45+0.0

Note: The actual product is marked differently from the image shown here. S-VSON(L)4 pin

Surface-mounting Terminals





Note: The actual product is marked differently from the image shown here.

■Safety Precautions

• Refer to "Common Precautions" for all G3VM models.

Please check each region's Terms & Conditions by region website.

OMRON Corporation

Electronic and Mechanical Components Company

Regional Contact Americas


https://www.components.omron.com/ Asia-Pacific https://ecb.omron.com.sg/ Korea https://www.omron-ecb.co.kr/

Europe http://components.omron.eu/
China https://www.ecb.omron.com.cn/
Japan https://www.omron.co.jp/ecb/

© OMRON Corporation 2017 All Rights Reserved.


In the interest of product improvement, specifications are subject to change without notice.

Terminal Arrangement/Internal Connections (Top View)



Actual Mounting Pad Dimensions


(Recommended Value, Top View)



Unless otherwise specified, the dimensional tolerance is ± 0.1 mm.

Actual Mounting Pad Dimensions

(Recommended Value, Top View)



Unless otherwise specified, the dimensional tolerance is ± 0.1 mm.

Cat. No. K291-E1-05 0318(0717)(O)