


# JE CONNECTOR

# 1.25 mm pitch/Board-to-board connectors/Mating type



The JE connector is a compact, board-to-board connector only 6.8 mm high and 4.4 mm wide. Its mating part has a 1.25 mm pitch, single row construction. High contact pressure dual beam fork contacts are combined with a housing lock mechanism to ensure a reliable connection.

- A compact design to meet today's needs
- · Secure locking and reliable connection
- Box shaped housing
- · Easy mounting and no flux problems

# Standards

Recognized E 60389 :Certified LR 20812

# Specifications

- Current rating: 1.0 A AC/DC
- Voltage rating: 50 V AC/DC
- Temperature range: -25°C to +85°C

(including temperature rise in applying electrical current)

· Contact resistance:

Initial value/ 20 m $\Omega$  max.

After environmental tests/ 40 m $\Omega$  max.

- Insulation resistance: 500 M $\Omega$  min.
- Withstanding voltage: 500 VAC/minute
- Applicable PC board thickness: 1.6 mm
- \* In using the products, refer to "Handling Precautions for Terminals and Connectors" described on our website (Technical documents of Product information page).
- \* RoHS2 compliance
- \* Dimensional unit: mm
- \* Contact JST for details.

# PC board layout and Assembly layout

#### 


- Note: 1. The above figure is the figure viewed from the connector mounting side.
  - 2. Tolerances are non-cumulative:  $\pm$  0.05mm for all centers.
  - 3. Hole dimensions differ according to the type of PC board and piercing method.

    Please contact JST for details as the dimensions shown in the above figure are reference values.

#### When using the plug without stopper

# Daughter board (4.4) Daughter board (8.9) (2.0) (1.5) Mother board

#### When using the plug with stopper




Note: The daughter board should be secured. For details of the securing method, contact JST.

Connector outline

φ0.7<sup>+0.1</sup>

# Plug




No. of	Model No.		Dimensions (mm)		Q'ty/box
circuits	Without stopper	With stopper	Α	В	Q ty/box
5	05PS-JE	05PSL-JE	5.0	7.4	1,400
7	_	07PSL-JE	7.5	9.9	1,050
9	09PS-JE	09PSL-JE	10.0	12.4	800
11	11PS-JE	11PSL-JE	12.5	14.9	700
13	13PS-JE	13PSL-JE	15.0	17.4	600
15	_	15PSL-JE	17.5	19.9	500
17	17PS-JE	17PSL-JE	20.0	22.4	450
19	19PS-JE	19PSL-JE	22.5	24.9	400

Material and Finish

Contact: Brass, tin-plated Housing: Glass-filled PA 66, UL94V-0

RoHS2 compliance

# Socket



No. of	Madal Na	Dimensions (mm)		0/4/5
circuits	Model No.	Α	В	Q'ty/box
5	05R-JE	5.0	7.4	1,000
7	07R-JE	7.5	9.9	1,000
9	09R-JE	10.0	12.4	1,700
11	11R-JE	12.5	14.9	1,400
13	13R-JE	15.0	17.4	1,200
15	15R-JE	17.5	19.9	1,000
17	17R-JE	20.0	22.4	900
19	19R-JE	22.5	24.9	800

### Material and Finish

Contact: Phosphor bronze, copper-undercoated, tin-plated Housing: Glass-filled PA 66, UL94V-0

RoHS2 compliance This product displays (LF)(SN) on a label.

- 2 - **JST**