



# 1A, 50V - 1000V Glass Passivated Bridge Rectifiers

#### **FEATURES**

- Ideal for automated placement
- Reliable low cost construction utilizing molded plastic technique
- High surge current capability
- UL Recognized File # E-326854
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21







#### **MECHANICAL DATA**

Case: Molded plastic body


Molding compound, UL flammability classification rating 94V-0

Moisture sensitivity level: level 1, per J-STD-020 Part no. with suffix "H" means AEC-Q101 qualified

Packing code with suffix "G" means green compound (halogen-free) **Terminal:** Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 2 whisker test Polarity: Polarity as marked on the body

Weight: 0.36 g (approximately)



_	+		
~	~		
		~ ~	

		DBLS DBLS DBLS DBLS DBLS DBLS DBLS					DBLS		
PARAMETER	SYMBOL	101G	102G	103G	104G	105G	106G	107G	UNIT
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	400	600	800	1000	V
Maximum RMS voltage	$V_{RMS}$	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	$V_{DC}$	50	100	200	400	600	800	1000	V
Maximum average forward rectified current	I <sub>F(AV)</sub>			•	1				Α
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>			40			3	0	Α
Rating for fusing (t<8.3ms)	l <sup>2</sup> t			6.6			3	.7	A <sup>2</sup> s
Maximum instantaneous forward voltage (Note 1) I <sub>F</sub> = 1 A	V <sub>F</sub>				1.1				V
Maximum reverse current @ rated $V_R$ $T_J$ =25°C $T_J$ =125°C	I <sub>R</sub>				2 100				μΑ
Typical junction capacitance per leg (Note 2)	CJ	25						pF	
Typical thermal resistance	$R_{ heta JL} \ R_{ heta JA}$	15 40					°C/W		
Operating junction temperature range	TJ	- 55 to +150						°C	
Storage temperature range	T <sub>STG</sub>	- 55 to +150						°C	

Note 1: Pulse Test with PW=300µs,1% Duty Cycle

Note 2: Measure at 1.0MHz and Applied Reverse Voltage of 4.0 Volts D.C.



ORDERING INFORMATION					
PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX <sup>(*)</sup>	PACKAGE	PACKING
DBLS10xG	Н	C1	G	DBLS	50 / TUBE
(Note 1)	e 1) RD		DBLS	1,500 / 13" Paper reel	


Note 1: "x" defines voltage from 50V (DBLS101G) to 1000V (DBLS107G)


<sup>\*:</sup> Optional available


EXAMPLE						
PREFERRED P/N	PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION	
DBLS107GHRDG	DBLS107G	Ħ	RD	G	AEC-Q101 qualified Green compound	

#### **RATINGS AND CHARACTERISTICS CURVES**

(T<sub>A</sub>=25°C unless otherwise noted)














FIG. 5 TYPICAL JUNCTION CAPACITANCE




# PACKAGE OUTLINE DIMENSIONS DBLS



DIM.	Unit	(mm)	Unit (inch)		
DIIVI.	Min Max		Min	Max	
Α	5.00	5.20	0.197	0.205	
В	1.02	1.20	0.040	0.047	
С	8.13	8.51	0.320	0.335	
D	2.40	2.60	0.094	0.102	
Е	9.80	10.30	0.386	0.406	
F	6.20	6.50	0.244	0.256	
G	0.22	0.33	0.009	0.013	
Н	1.02	1.53	0.040	0.060	
Ī	0.076	0.33	0.003	0.013	
J	3.90	4.10	0.154	0.161	

## **SUGGESTED PAD LAYOUT**



Symbol	Unit (mm)	Unit (inch)
Α	2.3	0.091
В	1.3	0.051
С	6.9	0.272
D	11.5	0.453
Е	2.6	0.102
F 9.2		0.362

## **MARKING DIAGRAM**



P/N = Specific Device Code G = Green Compound

YW = Date Code F = Factory Code

Document Number: DS\_D1410052





## Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Document Number: DS\_D1410052 Version: O15

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Taiwan Semiconductor:

DBLS101G DBLS102G DBLS103G DBLS104G DBLS105G DBLS106G DBLS107G DBLS104GHRDG
DBLS107GHRDG DBLS102GHRDG DBLS103G RDG DBLS102G RDG DBLS103GHRDG DBLS107G RDG
DBLS104G RDG DBLS105GHRDG DBLS105G RDG DBLS101G RDG DBLS106GHRDG DBLS101GHRDG
DBLS106G RDG DBLS102G RD DBLS104G RD DBLS103G RD DBLS106G RD DBLS105G RD DBLS101G RD
DBLS107G RD DBLS106G C1G DBLS107G C1G DBLS105G C1G DBLS104GH DBLS105GH DBLS106GH
DBLS107GH