




REV	LOCAS	DESCRIPTION	DRAW	DATE
01	NEW	INITIAL RELEASE	Junly	2010.08.16
05	△05	ECN20120040	Huang	2012.09.26
06	△06	ADD LOGO	Wang	2014.03.17



- NOTES:
- MATERIAL:
    - Housing: High Temperature Thermoplastic UL94V-0; Color Black.
    - Terminal: Copper Alloy.
    - Nail: Stainless Steel.
  - SPECIALITY:
    - Rated current: 2.0A
    - Rated voltage: 30V
    - Contact Resistance: 50mΩ MAX
    - Insulation Resistance: 100MΩ MIN
    - Dielectric withstanding voltage: 250V AC.
    - Solder ability: 245±5°C, 5±0.5s.
    - Durability: 5000 Cycles Min.
    - Operating condition: Temperature: -30°C~+80°C; Humidity: 80% R.H MAX



PART No.	DIM A	DIM B	PART No.	DIM A	DIM B
BA0307300450-26	4.50	3.00	BA0307300600-26	6.00	4.50
BA0307300500-26	5.00	3.50	BA0307300620-26	6.20	4.70
BA0307300550-26	5.50	4.00			

RECOMMENDED PCB LAYOUT  
TOLERANCE: ±0.05

QUADRANT POINT (QP)  
TANGENCY POINT (TP)  
INTERSECTION POINT (IP)

**DONGGUAN D-CHAIN Precision Components CO, Ltd**

UNLESS OTHERWISE SPECIFIED, TOLERANCE:  
 X. ±0.25  
 X.x ±0.20  
 X.xx ±0.15  
 ANGULAR ±3'

DESIGN	Huang	DATE	2012.09.26	TITLE: 3PIN BATTERY PH:3.00mm SMT TYPE WITH 2 POST
CHECKED	Andy.L	DATE	2012.09.26	
APPROVED	Andy.L	DATE	2012.09.26	
PART NO:	BA0307300XXX-26			REV: 06
DRAWING NO:	DQBA0307300450-26			SCALE: 5:1
				UNIT: mm
				SIZE: A4
				SHEET: 1/1