

REV	LOCALS	DESCRIPTION	DRWN	DATE
01	NEW	PERLUMINARY	LITAO	2016.12.19

NOTES:



1. MATERIAL:

- 1.1 Housing: High Temperature Thermoplastic
- UL94V-0, Color: Black




- 1.2 Terminal: Copper Alloy
- 1.3 Shell: stainless steel

2. SPECIALITY:


- 2.1 Rated Current: 0.5A
- 2.2 Rated Voltage: 30V
- 2.3 Contact Resistance: 50mΩ Max
- 2.4 Insulation Resistance: 100MΩ Min 100V DC
- 2.5 Dielectric Withstanding Voltage: 100V AC
- 2.6 Solder Ability: 235±5°C; 5±0.5s
- 2.7 Durability: 5000 cycles
- 2.8 Operating Condition: Temperature: -30°C~+80°C;
Humidity: 80%R.H Max



SECTION:A-A
SCALE: 1:1




DETAIL "A"
SCALE 5:1



RECOMMEND P.C.B. LAYOUT
TOLERANCE ±0.05

THESE AREA SHOULD BE FREE OF ANY CONDUCTIVE TRACES
SMT SOLDER AREA



MEASURE POINT:	(QP)
QUADRANT POINT	(TP)
TANGENCY POINT	(TP)
INTERSECTION POINT	(IP)
UNLESS OTHERWISE SPECIFIED, TOLERANCE:	
X	±0.20
X.X	±0.15
X.XX	±0.10
X.XXX	±0.05
ANGULAR	±2'

		DESIGN	Wong	DATE	2016.12.19	TITLE:	1. 8H 6P1N SIM CARD
		CHECKED		DATE			
		APPROVED		DATE			
		PART NO:	SA0607254180-09-03	REV:	01	SCALE:	1:1
		DRAWING NO:	DOS0607254180-09-03	SIZE:	A4	SHEET:	1/1
				UNIT:	mm		