



# LG-256PT2C94F-908 PHOTO TRANSISTOR **DATA SHEET**

 SPEC. NO.
 : SZ20111602

 DATE
 : 2021/03/29

 REV.
 : A/2

Approved By: Checked By: Prepared By:

Part No. LG-256PT2C94F-908 **Page** 1 of 9






## **Features**

- ♦ Pb free product—RoHS compliant
- ♦ High Photo Sensitivity
- ♦ General purpose leads
- ♦ Reliable and rugged
- ♦ Long life solid state reliability

# Package Dimension



Part NO.	Chip Material	Lens Color
LG-256PT2C94F-908	Silicon	Water Clear

#### **Notes:**

- 1. All dimensions are in millimeters.
- 2. Tolerance is  $\pm 0.20$ mm unless otherwise noted.
- 3. Protruded resin under flange is 1.0mm max.
- 4. Lead spacing is measured where the leads emerge from the package.
- 5. Specifications are subject to change without notice.

Part No.	LG-256PT2C94F-908	Page	2 of 9



## LIGHT ELECTRONICS CO., LTD.



## Absolute Maximum Ratings at Ta=25℃

Parameter	Maximum Rating	Unit	
Power Dissipation	75	mW	
Collector- Emitter Voltage	30	V	
Emitter- Collector Voltage	5	V	
Electrostatic Discharge (HBM)*3	narge (HBM)*3 4000		
Operating Temperature	-40°C~+85°C		
Storage Temperature Range	-40°C∼+100°C		
Lead Soldering Temperature [2mm From Body]	260°C for 3 Seconds		
Lead Soldering Temperature [5mm From Body]	260°C for 5 Seconds		

### 1. Storage:

The storage ambient for the LEDs should not exceed 30°C temperature or 70% relative humidity. It is recommended that LEDs out of their original packaging are used within three months. For extended storage out of their original packaging, it is recommended that the LEDs be stored in a sealed container with appropriate desiccant or in desiccators with nitrogen ambient.

#### 2. Precautions in handling:

- When soldering, leave 2mm of minimum clearance from the resin to the soldering point.
- Dipping the resin to solder must be avoided.
- Correcting the soldered position after soldering must be avoided.
- In soldering, do not apply any stress to the lead frame particularly when heated.
- When forming a lead, make sure not to apply any stress inside the resin.
- Lead forming must be done before soldering.
- It is necessary to cut the lead frame at normal temperature.

#### 3. Caution in ESD:

Static Electricity and surge damages the LED. It is recommend to use a wrist band or anti-electrostatic glove when handling the LED. All devices, equipment and machinery must be properly grounded.

Part No.	LG-256PT2C94F-908	Page	3 of 9
----------	-------------------	------	--------



# LIGHT ELECTRONICS CO., LTD.




## Electrical Optical Characteristics at Ta=25°C

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST CONDITIONS
Range of Spectral Bandwidth	$\lambda_{0.5}$	400		1100	nm	
Wavelength of Peak Sensitivity	$\lambda_{ m P}$		860		nm	
Collector- Emitter Breakdown Voltage	V <sub>(BR)CEO</sub>	30			V	I <sub>C</sub> =0.1mA Ee=0mW/cm <sup>2</sup>
Emitter-Collector Breakdown Voltage	V <sub>(BR)ECO</sub>	5			V	$I_R$ =0.1mA Ee=0 mW/cm <sup>2</sup>
Collector- Emitter Saturation Voltage	V <sub>CE(SAT)</sub>			0.4	V	$I_C$ =0.1mA Ee=1.0mW/cm <sup>2</sup>
Rise Time	$T_{r}$		15		μS	Vcc=5V $R_L=1K\Omega$ $I_C=1mA$
Fall Time	$T_{\mathrm{f}}$		15		μS	Vcc=5V $R_L=1K\Omega$ $I_C=1mA$
Viewing Angle	$2\theta_{1/2}$		55		Deg.	
Collector Dark Current	I <sub>CEO</sub>			100	nA	V <sub>CE</sub> =10V E <sub>e</sub> =0 mW/cm <sup>2</sup>
On State Collector Current	$I_{C(ON)}$	2.2	4.5		mA	$V_{CE}$ =5 $V_{e}$ =1.0 $m$ W/cm <sup>2</sup> $\lambda_{p}$ =940 $m$

#### Note:

- 1.  $2\theta_{1/2}$  is the off-axis angle at which the  $I_{C(ON)}$  is half the axial  $I_{C(ON)}$ .
- 2. The  $I_{C(ON)}$  guarantee should be added  $\pm 15\%$  tolerance.

## Recommended Wave Soldering Profile









# Photo Transistor Diode Specification

●Commodity: Photo Transistor

●Ic(on) Bin Code (V<sub>CE</sub>=5V, Ee=1mW/cm², λp=940nm)

BIN CODE	Min. (mA)	Max. (mA)
BIN1	2.2	2.6
BIN2	2.6	3.1
BIN3	3.1	3.7
BIN4	3.7	4.4
BIN5	4.4	5.3

**NOTE**: The Ic(on) guarantee should be added  $\pm 15\%$  tolerance.


Part No. LG-256PT2C94F-908 Page 5 of 9
--




# LIGHT ELECTRONICS CO., LTD.




# Typical Electrical / Optical Characteristics Curves (25℃ Ambient Temperature Unless Otherwise Noted)














FIG.5 Collector Dark Current Vs. Ambient Temperature





Part No.	LG-256PT2C94F-908	Page	6 of 9
	_ 0 _ 0 0 1 _ 0 0 1 0 0 0		0 0- /








### LED MOUNTING METHOD


1. The lead pitch of the LED must match the pitch of the mounting holes on the PCB during component placement. Lead-forming may be required to insure the lead pitch matches the hole pitch. Refer to the figure below for proper lead forming procedures (Fig.1).




"o" Correct mounting method "x" Incorrect mounting method

Note 1-2: Do not route PCB trace in the contact area between the lead frame and the PCB to prevent short-circuits.

2. When soldering wire to the LED, use individual heat-shrink tubing to insulate the exposed leads to prevent accidental contact short-circuit (Fig.2).



3. Use stand-offs (Fig.3) or spacers (Fig.4) to securely position the LED above the PCB.



Part No. LG-256PT2C94F-908 Page 7 of 9









#### LEAD FORMING PROCEDURES


1. Maintain a minimum of 2mm clearance between the base of the LED lens and the first lead bend (Fig.5 and Fig.6).



- 2. Lead forming or bending must be performed before soldering, never during or after soldering.
- 3. Do not stress the LED lens during lead-forming in order to fractures in the lens epoxy and damage the internal structures.
- 4. During lead forming, use tools or jigs to hold the leads securely so that the bending force will not be transmitted to the LED lens and its internal structures. Do not perform lead forming once the component has been mounted onto the PCB (Fig.7).
- 5. Do not bend the leads more than twice (Fig. 8).



6. After soldering or other high-temperature assembly, allow the LED to cool down to 50°C before applying outside force (Fig.9). In general, avoid placing excess force on the LED to avoid damage. For any questions please consult with LIGHT representative for proper handling procedures.





Part No.	LG-256PT2C94F-908	Page	8 of 9
----------	-------------------	------	--------






# PACKAGE







Bag minimum volume	Bag volume	Inner box volume	Outer carton volume	
(pcs / Bag)	(pcs / Bag)	(Bag / box)	(Box / Carton)	
500	1000	10	4	

Part No.	LG-256PT2C94F-908	Page	9 of 9
----------	-------------------	------	--------