




REV	LOCAS	DESCRIPTION	DRAW	DATE
01	NEW	INITIAL RELEASE	LIU	2021.06.29
02		UPDATED	LIU	2021.08.10
03			LIU	2021.09.02



NOTES:

1. MATERIAL:



- 1.1 SWITCH BLOCK
- :HOUSING:THERMOPLASTIC,UL 94V-0;COLOR:BLACK
- 1.2 CONTACT:COPPER ALLOY
- 1.3 CRANK:STAINLESS STEEL T=0.4mm
- 1.4 ROD:STAINLESS STEEL T=0.5mm
- 1.5 SHELL:STAINLESS STEEL T=0.15mm
- 1.6 SWITCH BLOCK :THERMOPLASTIC,UL 94V-0,COLOR:BLACK
- 1.7 SWITCH PIN:COPPER ALLOY T=0.12mm

2 FINISH:


- 2.1 CONTACT: GOLD PLATING ON CONTACT AREA&ON SOLDER TAILS, 50u" MIN. NICKEL UNDERPLATING.
- 2.2 SHELL: GOLD PLATING ON SOLDER TAILS, 50u" NICKEL UNDERPLATED.

3. SPECIALITY:


- 3.1 VOLTAGE RATING:50V
- 3.2 WITHSTANDING VOLTAGE:AC250V R.M.S
- 3.3 CURRENT RATING:1.0A
- 3.4 INSULATION RESISTANCE:1000MEG.OHM MIN AT DC 250V
- 3.5 CONTACT RESISTANCE:100 MILL.OHM MAX
- 3.6 OPERATION TEMPERATURE: -20°C~+85°C
- 3.7 DURABILITY:1000 CYCLES



COMPOSITION OF DETECTION



G1-G10	GND
SW	SWITCH PIN



/// SMT SOLDER AREA  
RECOMMENDED PCB LAYOUT  
GENERAL TOLERANCE ±0.05

MEASURE POINT:  
QUADRANT POINT (QP)  
TANGENCY POINT (TP)  
INTERSECTION POINT (IP)



DongGuan D-CHAIN Precision Components CO, Ltd

UNLESS OTHERWISE SPECIFIED, TOLERANCE:	DESIGN	LIU	DATE	2021.06.29	TITLE:	1.35H 左侧顶出分体式 三选二 组合式卡座 (外壳组件)				
X. ±0.25	CHECKED		DATE		REV:	03	SCALE:	1:1	UNIT:	mm
X.x ±0.20	APPROVED		DATE		SIZE:	A4	SHEET:	1/1		
X.xx ±0.15	PART NO:	SA3201254135-148								
ANGULAR ±3°	DRAWING NO:									