

## **SAW Single Filter**

**for WIFI / Bluetooth / Unbalanced / 5pin /1411**

- **Co-existence of 4G LTE &WIFI signals**
- **High Rejection in B7/B41/B40 bands**

## 1 Description

SAWF14112G45AT is a high-performance Surface Acoustic Wave (SAW) Bandpass filter optimized for co-existence between cellular 4G/LTE Bands B40, B38, B41, B7, and Wi-Fi/Bluetooth applications operating in the range of 2.4-2.5 GHz license-free ISM band. It is designed to provide both low insertion loss in the Wi-Fi/BT Band and high rejection in the cellular Bands, in order to enable simultaneous operation of Wi-Fi/BT and 4G/LTE within the same device, such as smartphones.

SAWF14112G45AT uses advanced Chip Scale Package (CSP) technology and is housed in an industry standard, 5-pin 1.4mmx1.1mm package with a low profile of 0.6mm max.

## 2 Features

- Low Insertion Loss: 0.9dB at Mid-Band
- High Rejection in B40/B41/B7
- Small Footprint:  $0.325 \pm 0.05\text{mm} \times 0.25 \pm 0.05\text{mm}$ .
- Package size  $1.4 \pm 0.05\text{mm} \times 1.1 \pm 0.05\text{mm}$
- Electrostatic Sensitive Device(ESD)
- Package height 0.6mm max.
- Single-Ended Operation
- RoHS Compliant

### 3 Package & Dimensions:




Figure 1: Drawing of Package with each tolerance range

### 4 Pin configuration

- 1 Input (recommended)
- 4 Output (recommended)
- 2,3,5 To be grounded

### 5 Matching Circuit(recommended)




Figure 2: Schematic of matching circuit.

R1: 50 Ohm	L1: NC
R2: 50 Ohm	L2: NC



## 6 Absolute Maximum Ratings

Parameter	Rating	Unit
Operating Temperature	-30 to +85	°C
Storage Temperature	-40 to +85	°C
Maximum Input Power	+24	dBm
Maximum DC Voltage	5	V
Input terminating impedance	50	Ω
Output terminating impedance	50	Ω
Input Power@input port	Pin=24dBm Continuous wave for 2000h@+55°C	

**7 Electrical Specifications**

Parameter	Conditions	Min	Typ.	Max	Unit	Note
Insertion Loss	2403 - 2471 MHz	-	1.9	2.5	dB	
	2458 - 2476 MHz	-	1.8	2.4	dB	
	2463 - 2481 MHz	-	2.2	2.8	dB	
Passband Ripple	2403 - 2481 MHz	-	1.2	1.6	dB	
Attenuation	800 - 2300 MHz	25	29	-	dB	
	2300 - 2370 MHz	29	35	-	dB	
	2370 - 2380 MHz	23	25	-	dB	
	2500 - 2502 MHz	26	30	-	dB	
	2502 - 2570 MHz	30	34	-	dB	
	2570 - 2620 MHz	30	33	-	dB	
	2620 - 2690 MHz	28	30	-	dB	
VSWR Input	2403 - 2481 MHz	-	1.7	2.0	-	
VSWR Output	2403 - 2481 MHz	-	1.7	2.1	-	

## 8 Transmission coefficient



## 9 Reflection coefficients




Figure 5: VSWR

