






REV AO	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12




RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

- SPECIFICATION:**
- ELECTRICAL:**
 VOLTAGE RATING: 30VAC RMS;
 CURRENT RATING: 2.0 A(pin1,5);1.0A(pin2,3,4)
 CONTACT RESISTANCE: 50 MILLIOHMS MAX;
 INSULATION RESISTANCE: 100MEGOHMS MIN
 DIELECTRIC WITHSTANDING VOLTAGE:500V AC FOR 1MINUTE
 - MECHANICAL:**
 OPERATING LIFE:5000CYCLES
 - ENVIRONMENTAL:**
 OPERATING TEMPERATURE: -40°C TO 85°C.



Pin Assignments

Contact No.	Signal Name
1	VBUS
2	D-
3	D+
4	ID
5	GND
SHELL	Shield



		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话: 0755-23304126 传真: 0755-29940187			
		-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: MICRO公头反贴	
X.X ±0.30	X.X* ±3°	APPD: 核准: CHECK: 校对: 王建业 DRAW: 绘图: 黄艳兰	PART NO: 产品编号: MICRO-ZD-101PWB		
X.XX ±0.20	X.XX* ±2°		DATE	SCALE	UNIT
X.XXX ±0.10	X.XXX* ±1°		2016-03-12	1:1	mm
				CODE NUMBER	A001