



THINKING ELECTRONIC INDUSTRIAL CO., LTD.

HEAD OFFICE: 8F-1, No.93, Ta-Shun 1st Rd., Kaohsiung, Taiwan
TEL: 886-7-5577660 FAX: 886-7-5570560

MANUFACTURING SITE

- KAOHSIUNG FACTORY: No.51, Kaifa Road, Nantze Export Processing Zone, Kaohsiung City 81170, Taiwan
TEL: 886-7-9616668 FAX: 886-7-9616698
- CHANGZHOU FACTORY: No.82, Renmin Mid Rd., WuJin High&New-Tech Industrial Development Zone, ChangZhou, JiangSu, China
TEL:86-519-86556426 FAX:86-519-86558643 ZIP:213161
- DONG GUAN FACTORY: Chiao-Tou Tsun. Sha-Tao Hsiang. Chang-An Town. Dong-Guan City, Guang-Dong, China
TEL:86-769-85542016 FAX:86-769-85546890
- YICHANG FACTORY: No. 283 Xiaoting Avenue, Xiaoting Dist., Yichang City 443007, Hubei, China
TEL:86-717-6510010 FAX:86-717-6511430



SPECIFICATION FOR APPROVAL

CUSTOMER

CERTIFIED

MODEL/TYPE

PART NO.

APPLICATION

CUSTOMER P/N

ISSUE DATE

REV. NO

REV. DATE

TVR20102-D

TVR20102KSC6AW(RoHS)

Jul.18,2014

| FOR CUSTOMER APPROVAL | CHECKED BY |
|-----------------------|----------------|
| | Yun Xu |
| | APPROVED BY |
| | Huaifang Zhang |





REVISED RECORD SHEET

| REV. NO | REV. DATE | REVISED CONTENT |
|---------|-----------|-----------------|
| | | |



| INDEX | Page |
|--|-------------|
| ■ Part Number Code | 1 |
| ■ Structure and Dimensions | 2 |
| ■ Electrical Characteristics | 2 |
| ■ Reliability | 3 ~ 4 |
| ■ Soldering Recommendation | 5 |
| ■ Power Derating Curve | 6 |
| ■ RoHS Compliant Declaration | 6 |
| ■ Warehouse Storage Conditions of Products | 6 |
| ■ Safety Approvals | 7 |
| ■ Certificates | 7 |
| ■ Max. Surge Current Derating Curves | 8 |
| ■ Max. Leakage Current and Max. Clamping Voltage Curve | 9 |




Part Number Code

Example :

TVR **20** **102** **K** **S** **C6A** **W**
(1) (2) (3) (4) (5) (6) (7)

| No. | Item | Digit | Specification |
|-----|-------------------------------|-------|--|
| (1) | Product Type | TVR | Thinking varistor TVR type |
| (2) | Body Size | 20 | φ 20 mm |
| (3) | Varistor Voltage | 102 | $10 \times 10^2 \text{ V} = 1000\text{V}$ ($V_{1\text{mA}}$) |
| (4) | Tolerance of $V_{1\text{mA}}$ | K | ±10% |
| (5) | Appearance | S | Straight lead , epoxy coating |
| (6) | Packaging | C6A | Cut 6.0 mm Lead & bulk |
| (7) | Optional Suffix | W | RoHS compliance & High surge series |

Structure and Dimensions



| Body Size | D | P | d | A max. | C | T | W |
|-----------|-----------|--------|-----------|--------|-----|---------|---------|
| φ 20D | 22.0~24.5 | 10.0±1 | 1.00±0.02 | 28.5 | 6±1 | 6.1~7.9 | 4.2±1.0 |

*Coating material rating:UL 94 V-0

Electrical Characteristics (Ambient Ta=25 °C)

| Part No. | Varistor Voltage (@ 1mA DC) | MMax. Continuous Voltage | | Max. Clamping Voltage (8/20μS) | | Max. Surge Current (8/20μS) | Max. Energy (10/1000μS) |
|----------------|--------------------------------|-----------------------------|------------------------|-----------------------------------|-----------------------|--------------------------------|----------------------------|
| | V _{1mA} (V) | V _{AC(rms)} (V) | V _{DC} (V) | V _p (V) | I _p (A) | I (A) | W (J) |
| TVR20102KSC6AW | 1000 ± 10 % | 625 | 825 | 1650 | 100 | 13000 | 650 |

| Part No. | Rated Power | Impulse Response Time | Max. Leakage Current at 75%V _{1mA} | Operating Temperature Range | Storage temperature Range | Applications | | |
|----------------|-------------|-----------------------|---|-----------------------------|---------------------------|--------------|-------------|--------------|
| | P (W) | nSec | I _L (μA) | (°C) | (°C) | UL 1449 | IEC 60950-1 | IEC 60065 |
| TVR20102KSC6AW | 1 | <25 | 20 | -40 ~ +85 | -40 ~ +125 | SPD Type 3 | Annex Q | Clause 14.12 |



Reliability


| Item | Standard | Test conditions / Methods | Specifications | | | | | | | | | | | | | | | |
|-------------------------------|------------------------|---|--|------------------|------------------|-----|------------|--------|--------|------------------|--|---|--------|--------|---|------------------|-------|--|
| Tensile Strength of Terminals | IEC60068-2-21 | <p>Gradually applying the force specified and keeping the unit fixed for 10±1 sec.</p> <table border="1"> <thead> <tr> <th>Terminal diameter (mm)</th> <th>Force (Kg)</th> </tr> </thead> <tbody> <tr> <td>0.5<d≤0.8</td> <td>1.0</td> </tr> <tr> <td>0.8<d≤1.25</td> <td>2.0</td> </tr> <tr> <td>1.25<d</td> <td>4.0</td> </tr> </tbody> </table> | Terminal diameter (mm) | Force (Kg) | 0.5<d≤0.8 | 1.0 | 0.8<d≤1.25 | 2.0 | 1.25<d | 4.0 | No visible damage ΔV/V _{1mA} ≤5% | | | | | | | |
| Terminal diameter (mm) | Force (Kg) | | | | | | | | | | | | | | | | | |
| 0.5<d≤0.8 | 1.0 | | | | | | | | | | | | | | | | | |
| 0.8<d≤1.25 | 2.0 | | | | | | | | | | | | | | | | | |
| 1.25<d | 4.0 | | | | | | | | | | | | | | | | | |
| Bending Strength of Terminals | IEC60068-2-21 | <p>Hold specimen and apply the force specified below to each lead. Bend the specimen to 90°, then return to the original position. Repeat the procedure in the opposite direction.</p> <table border="1"> <thead> <tr> <th>Terminal diameter (mm)</th> <th>Force (Kg)</th> </tr> </thead> <tbody> <tr> <td>0.5<d≤0.8</td> <td>0.5</td> </tr> <tr> <td>0.8<d≤1.25</td> <td>1.0</td> </tr> <tr> <td>1.25<d</td> <td>2.0</td> </tr> </tbody> </table> | Terminal diameter (mm) | Force (Kg) | 0.5<d≤0.8 | 0.5 | 0.8<d≤1.25 | 1.0 | 1.25<d | 2.0 | No visible damage ΔV/V _{1mA} ≤5% | | | | | | | |
| Terminal diameter (mm) | Force (Kg) | | | | | | | | | | | | | | | | | |
| 0.5<d≤0.8 | 0.5 | | | | | | | | | | | | | | | | | |
| 0.8<d≤1.25 | 1.0 | | | | | | | | | | | | | | | | | |
| 1.25<d | 2.0 | | | | | | | | | | | | | | | | | |
| Vibration | IEC 60068-2-6 | <p>Frequency range:10~55Hz Amplitude:0.75mm or 98m/S² Direction:3 mutually perpendicular directions,2hrs each.</p> | ΔV/V _{1mA} ≤5% No visible damage | | | | | | | | | | | | | | | |
| Solderability | IEC60068-2-20 | 245 ± 3 °C , 3 ± 0.3 sec | At least 95% of terminal electrode is covered by new solder | | | | | | | | | | | | | | | |
| Resistance to Soldering Heat | IEC60068-2-20 | 260 ± 3 °C , 10 ± 1 sec | No visible damage ΔV/V _{1mA} ≤5% | | | | | | | | | | | | | | | |
| High Temperature Storage | IEC60068-2-2 | 125 ± 5 °C , 1000 ± 24 hrs | No visible damage ΔV/V _{1mA} ≤5% | | | | | | | | | | | | | | | |
| Damp Heat, Steady State | IEC 60068-2-78 | <p>The test is divided into two groups . a.40 ± 2°C , 90 ~ 95 % RH , 1344 hrs b.40 ± 2°C , 90 ~ 95 % RH , at 10%V_{DC}, 1344 hrs</p> | No visible damage ΔV/V _{1mA} ≤10% Insulation Resistance ≥ 100MΩ | | | | | | | | | | | | | | | |
| Rapid Change of Temperature | IEC60068-2-14 | <p>The conditions shown below shall be repeated 5 cycles</p> <table border="1"> <thead> <tr> <th>Step</th> <th>Temperature (°C)</th> <th>Period (minutes)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-40 ± 3</td> <td>30 ± 3</td> </tr> <tr> <td>2</td> <td>Room temperature</td> <td>5 ± 3</td> </tr> <tr> <td>3</td> <td>85 ± 2</td> <td>30 ± 3</td> </tr> <tr> <td>4</td> <td>Room temperature</td> <td>5 ± 3</td> </tr> </tbody> </table> | Step | Temperature (°C) | Period (minutes) | 1 | -40 ± 3 | 30 ± 3 | 2 | Room temperature | 5 ± 3 | 3 | 85 ± 2 | 30 ± 3 | 4 | Room temperature | 5 ± 3 | No visible damage ΔV/V _{1mA} ≤5% |
| Step | Temperature (°C) | Period (minutes) | | | | | | | | | | | | | | | | |
| 1 | -40 ± 3 | 30 ± 3 | | | | | | | | | | | | | | | | |
| 2 | Room temperature | 5 ± 3 | | | | | | | | | | | | | | | | |
| 3 | 85 ± 2 | 30 ± 3 | | | | | | | | | | | | | | | | |
| 4 | Room temperature | 5 ± 3 | | | | | | | | | | | | | | | | |
| High Temp. Load | MIL-STD-202 Method 108 | 85 ± 2 °C , 1000 ± 24 hrs, at V _{DC} or V _{rms} (Max. Operating Voltage) | ΔV/V _{1mA} ≤10% No visible damage | | | | | | | | | | | | | | | |



| Item | Standard | Test conditions / Methods | Specifications |
|------------------------------------|------------------------|--|---|
| Operating Duty Cycle test | UL1449 3 rd | 6KV/3KA 1.2/50μs+8/20μs combination waveform with Vac(@ Deg 90) for 15 times. Interval time between tests is 60 secs. | $ \Delta V_p / V_p \leq 10\%$ No visible damage |
| 8/20μS Surge Life | IEC 61051-1 4.6 | 10,000 pulses(8/20 μ S) , unipolar, interval 10 secs, amplitude corr. to max. Surge current derating curves for 20 μ S | $ \Delta V / V_{1mA} \leq 10\%$ No visible damage |
| 10/1000μS Surge Life | IEC 61051-1 4.6 | 10/1000μS waveform, 10 surge currents,unipolar,interval 2mins, amplitude corr. to max. surge current derating curves for 1000μS | $ \Delta V / V_{1mA} \leq 10\%$ No visible damage |
| Varistor Voltage Temp. Coefficient | Specification Standard | $\frac{V_{1mA} \text{ at } 85^{\circ}\text{C} - V_{1mA} \text{ at } 25^{\circ}\text{C}}{V_{1mA} \text{ at } 25^{\circ}\text{C}} \times \frac{1}{60} \times 100 (\% / ^{\circ}\text{C})$ $\frac{V_{1mA} \text{ at } -40^{\circ}\text{C} - V_{1mA} \text{ at } 25^{\circ}\text{C}}{V_{1mA} \text{ at } 25^{\circ}\text{C}} \times \frac{1}{65} \times 100 (\% / ^{\circ}\text{C})$ | $-0.05 \leq TC \leq 0.05 (\% / ^{\circ}\text{C})$ |
| Voltage Proof | IEC 61051-1 4.9 | Metal balls method, 2500 Vac 1 min | No visible damage |

Soldering Recommendation

■ Wave Soldering Profile




- Note 1 : $(1\sim 3)^{\circ}\text{C}/\text{sec}$
 Note 2 : Approx. $200^{\circ}\text{C}/\text{sec}$
 Note 3 : $5^{\circ}\text{C}/\text{sec}$ Max

■ Recommended Reworking Conditions with Soldering Iron

| Item | Conditions |
|-----------------------------------|------------------------------|
| Temperature of Soldering Iron-tip | 360°C (max.) |
| Soldering Time | 3 sec (max.) |
| Distance from Varistor | 2 mm (min.) |

Power Derating Curve

When operating temperature exceeds 85°C, the power, the Max.continuous operation Voltage,the Max.Surge Current and the Max.Energy should be derated as below figure, the derated coefficient is -2.5%.



RoHS Compliant Declaration

We hereby declare that the components delivered to your company are compliant with RoHS directive 2011/65/EU.

Warehouse Storage Conditions of Products

(I) Storage Conditions :

- 1.Storage Temperature : -10°C ~+40°C
- 2.Relative Humidity : $\leq 75\%RH$
- 3.Keep away from corrosive atmosphere and sunlight.

(II) Period of Storage : 1 year

Safety Approvals (Certified Model/Type :TVR20102-D)

- * UL 1449 3rd / cUL recognized (File # E314979)
- UL1449 (file number E314979) for use in SPD Type 3
- Meet the surge requirements 6KV/3KA combination wave of IEC 60950-1 Annex Q and IEC 60065 14.12



- * VDE IEC 61051-1:2007-04 / IEC 61051-2:1991
IEC 61051-2-2:1991 recognized (File # 40021243)



- * CQC GB/T10193-1997 \ GB/T10194-1997 recognized
(File # CQC10001041750/CQC10001041751)

Certificates

- (1) TS 16949 certificate
- (2) ISO 9001 certificate


Test Report

- (1) RoHS test report



Max. Surge Current Derating Curves

TVR20102KSC6AW





Max. Leakage Current and Max. Clamping Voltage Curve

