


Trench MOS Barrier Schottky Rectifier
Reverse Voltage - 200 V
Forward Current - 5 A
FEATURES

- ◆ Advanced trench technology
- ◆ Low forward voltage drop
- ◆ Low power losses
- ◆ High efficiency operation
- ◆ Lead free in comply with EU RoHS 2011/65/EU directives


MECHANICAL DATA

- ◆ Case: DO-201AD/DO-27
- ◆ Terminals: Solderable per MIL-STD-750, Method 2026
- ◆ Approx. Weight: 0.98g / 0.0345oz


Maximum Ratings (Per Leg) at Ta=25°C unless otherwise specified

Parameter	Symbols	Value	Units
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	200	V
Maximum RMS voltage	V _{RMS}	200	V
Maximum DC Blocking Voltage	V _{DC}	200	V
Maximum Average Forward Rectified Current Per diode	I _{F(AV)}	5	A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave superimposed on rated load per diode	I _{FSM}	100	A
Operating Temperature Range	T _J	-55 ~ +150	°C
Storage Temperature Range	T _{STG}	-55 ~ +150	°C
Typical Thermal Resistance Per diode(munted on FR-4 PCB)	DO-27	R _{θJC}	22 °C/W

Note1: Thermal resistance from Junction to case per leg mounted on heatsink.


Electrical Characteristics (Per Leg) unless otherwise specified

Characteristics	Symbols	Value		Units
Forward Voltage Drop(Note2)	V _F	Typ	Max	V
at I _F =3A Instantaneous forward voltage per diode		0.79	0.83	
		0.68	-	
at I _F =5A Instantaneous forward voltage per diode		0.84	-	
		0.79	-	
Instantaneous reverse current per diode at rated reverse voltage	I _R	-	2	uA
		-	80	mA


Note2: (1)Pulse test: 300 μs pulse width, 1 % duty cycle

(2) Pulse test: Pulse width ≤ 40 ms


RATINGS AND CHARACTERISTIC CURVES




Current Derating, Case




Typical Forward Voltage



Typical Junction Capacitance




Maximum Repetitive Surge Current



Typical Reverse Current

Package Outline DO-201AD(DO-27)



DIM	DIMENSIONS				NOTE	
	INCHES		MM			
	MIN	MAX	MIN	MAX		
A	---	.370	---	9.50		
B	---	.250	---	6.40		
C	.048	.052	1.20	1.30		
D	1.000	---	25.40	---		

Summary of Packing Options

Package	Packing Description	Packing Quantity	Industry Standard
DO-201AD(DO-27)	BOX	250/1000/1250	EIA-481-1