

Description

The HXY20P03D uses advanced trench technology

to provide excellent R_{DS(ON)}, low gate charge and

operation with gate voltages as low as 4.5V. This

device is suitable for use as a

Battery protection or in other Switching application.



TO252-2L

General Features

 $V_{DS} = -30V I_{D} = -20A$

 $R_{DS(ON)}$ < 42 m Ω @ V_{GS} =10V



P-Channel MOSFET

Application

Battery protection

Load switch

Uninterruptible power supply

Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
HXY20P03D	TO252-2L	20P03 XXX YYYY	2500

Absolute Maximum Ratings (T_c=25[°]Cunless otherwise noted)

Symbol	Parameter	Rating	Units	
VDS	Drain-Source Voltage	-30	V	
VGS	Gate-Source Voltage	±25	V	
I _D @T _C =25°C	Continuous Drain Current, V _{GS} @ 10V ¹	ous Drain Current, V _{GS} @ 10V ¹ -20		
I _D @T _C =100°C	Continuous Drain Current, V _{GS} @ 10V ¹) 10V ¹ -15		
IDM	Pulsed Drain Current ²	-50	А	
P _D @T _C =25°C	Total Power Dissipation ⁴	29		
TSTG	Storage Temperature Range	-55 to 150	°C	
TJ	Operating Junction Temperature Range	-55 to 150	°C	
ReJA	Thermal Resistance Junction-ambient ¹	75 °C.		
R₀JC	Thermal Resistance Junction-Case ¹	4.32 °C/W		



Electrical Characteristics (T_A=25 ℃ unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Тр	Max.	Unit
BVDSS	Drain-Source Breakdown Voltage	VGS=0V , ID=-250uA	-30			V
∆BVDSS/∆TJ	BVDSS Temperature Coefficient	Reference to 25°C , ID=-1mA		22		V/°C
RDS(ON)	Static Drain-Source On-Resistance2	VGS=-10V , ID=-15A	32	38	42	mΩ
		VGS=-4.5V , ID=-10A	48	60	70	
VGS(th)	Gate Threshold Voltage	VGS=VDS , ID =-250uA	-1.0		-2.5	V
△VGS(th)	VGS(th) Temperature Coefficient			4.6		mV/°C
		VDS=-24V , VGS=0V ,			-1	
IDSS		TJ=25℃				
	-Drain-Source Leakage Current	VDS=-24V, VGS=0V,			-5	uA
		TJ=55°C				
IGSS	Gate-Source	VGS=±25V , VDS=0V			±100	nA
	LeakageCurrent					
gfs	Forward	VDS=-5V , ID=-15A		19		S
	Transconductance					
Rg	Gate Resistance	VDS=0V , VGS=0V , f=1MHz		13		
Qg	Total Gate Charge (-4.5V)			12.5		
Qgs	Gate-Source Charge	VDS=-15V , VGS=-4.5V , ID=-15A		5.4		nC
Qgd	Gate-Drain Charge	_		5		1
Td(on)	Turn-On Delay Time			4.4		
Tr	Rise Time	VDD=-15V , VGS=-10V , RG=3.3 ,		11.2		1
Td(off)	Turn-Off Delay Time	ID=-15A		34		ns
Tf	Fall Time			18		
Ciss	Input Capacitance			1345		
Coss	Output Capacitance	VDS=-15V , VGS=0V , f=1MHz		194		pF
Crss	Reverse Transfer Capacitance			158		†


Notes:

- 1. Repetitive Rating: Pulse width limited by maximum junction temperature.
- **2.** Surface Mounted on FR4 Board, $t \le 10$ sec.
- 3. Pulse Test: Pulse Width $\leq 300 \mu s$, Duty Cycle $\leq 2\%$.
- 4. Guaranteed by design, not subject to production




Typical Electrical and Thermal Characteristics

Figure 5 Output Characteristics



Vgs Gate-Source Voltage (V)
Figure 7 Transfer Characteristics



Vgs Gate-Source Voltage (V)
Figure 9 Rdson vs Vgs




Figure 11 Gate Charge






Figure 8 Drain-Source On-Resistance



Vds Drain-Source Voltage (V)
Figure 10 Capacitance vs Vds



Vsd Source-Drain Voltage (V)
Figure 12 Source- Drain Diode Forward






Figure 13 Safe Operation Area





Figure 14 Normalized Maximum Transient Thermal Impedance



TO252-2L Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches			
	Min.	Max.	Min.	Max.		
A	2.200	2.400	0.087	0.094		
A1	0.000	0.127	0.000	0.005		
b	0.660	0.860	0.026	0.034		
С	0.460	0.580	0.018	0.023		
D	6.500	6.700	0.256	0.264		
D1	5.100	5.460	0.201	0.215		
D2	4.83	4.830 TYP.		0.190 TYP.		
E	6.000	6.200	0.236	0.244		
е	2.186	2.386	0.086	0.094		
L	9.800	10.400	0.386	0.409		
L1	2.90	2.900 TYP.		0.114 TYP.		
L2	1.400	1.700	0.055	0.067		
L3	1.600 TYP.		0.063 TYP.			
L4	0.600	1.000	0.024	0.039		
Ф	1.100	1.300	0.043	0.051		
θ	0°	8°	0°	8°		
h	0.000	0.300	0.000	0.012		
V	5.350 TYP.		0.211 TYP.			



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production.

 HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.