

















2方4圆



3方3圆



3方5圆



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:7A AC/DC

额定电流: 7A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X9357 H M - 2xXX - N2

① ② ③ ④ ⑤ ⑥

- 1. Series No
- 2. Category:H-HSG
- 3. Category:M-Male Housing
- 4. Row No.Pin No:2xXX-2x01~2x12P
- 5. Material:N2-PA66 UL94V-2 White

| Poles | Dimensions(mm) | |
|-------|----------------|-------|
| | A | B |
| 2x01 | 5.40 | / |
| 2x02 | 9.60 | 4.20 |
| 2x03 | 13.80 | 8.40 |
| 2x04 | 18.00 | 12.60 |
| 2x05 | 22.20 | 16.80 |
| 2x06 | 26.40 | 21.00 |
| 2x07 | 30.60 | 25.20 |
| 2x08 | 34.80 | 29.40 |
| 2x09 | 39.00 | 33.60 |
| 2x10 | 43.20 | 37.80 |
| 2x12 | 51.60 | 46.20 |

| | | | |
|-----------------|----------|--------------------|-----------------------|
| X9357HM-2xXX-N2 | PA66 | X9357W-A | X9357TF |
| PART NO | Material | Suitable XKB Wafer | Suitable XKB Terminal |

| | | | |
|------|--|-------------|--|
| DSND | | SCALE: N/A | MODEL TYPE: 4.2mm Crimp Style Connector |
| DWN | | VIEW: | PART NO.: X9357HM-2xXX-N2 |
| CHKD | | UNIT: mm/in | DWG NO.: X-X9357HM-2xXX-N2 |
| APPD | | SIZE: A4 | |



XKB INDUSTRIAL PRECISION CO.,LIMITED

| | | |
|--------|-------|----------|
| WEIGHT | SHEET | REVISION |
| | 1/1 | A0 |

广东星坤科技股份有限公司

| | | |
|------|-------------|------|
| Δx | | 日期 |
| Δx | | 日期 |
| Δx | | 日期 |
| MARK | DESCRIPTION | DATE |

文件工程章

| | | | | | |
|---|--|--|--|-------------|------------------------|
| | | | | ANGLAR | ±5° |
| | | | | L ≤ 4 | ±0.2 |
| | | | | 4 < L ≤ 16 | ±0.3 |
| | | | | 16 < L ≤ 63 | ±0.4 |
| | | | | L > 63 | ±0.5 |
| REVISIONS | | | | | UNSPECIFIED TOLERANCES |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn | | | | | |