


JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

AD-BAV16WS/1N4148WS Plastic-Encapsulated Diode


AD-BAV16WS/1N4148WS Schottky barrier diode

FEATURES

- High switching speed
- Surface mount package ideally suited for automatic insertion
- For general purpose switching applications
- High conductance
- AEC-Q101 qualified



MARKING



T6 = Device code AD-BAV16WS

The marking bar indicates the cathode



T4 = Device code AD-1N4148WS

The marking bar indicates the cathode

MAXIMUM RATINGS (T_j = 25°C unless otherwise specified)


| Parameter | Symbol | Value | Unit |
|---|----------------------|-----------|------|
| Non-repetitive peak reverse voltage | V _{RM} | 100 | V |
| Peak repetitive reverse voltage | V_{RRM} | 100 | V |
| Working peak reverse voltage | V_{RWM} | 100 | V |
| DC blocking voltage | V_{R} | 100 | V |
| RMS reverse voltage | V _R (RMS) | 71 | V |
| Forward continuous current | I _{FM} | 300 | mA |
| Average rectified output current | Ιο | 150 | mA |
| Non-repetitive peak forward surge current @ t = 8.3ms | I _{FSM} | 2.0 | Α |
| Power dissipation | P_D | 200 | mW |
| Thermal resistance from junction to ambient | R _{θJA} 1) | 625 | °C/W |
| Operating junction and storage temperature range | T_{j},T_{stg} | -55 ~ 150 | °C |


ELECTRICAL CHARACTERISTICS ($T_j = 25^{\circ}C$ unless otherwise specified)


| Parameter | Symbol | Test condition | Min | Тур | Max | Unit |
|-------------------------------|-----------------|--|-----|-----|-------|------|
| | V _{F1} | I _F = 1mA | - | - | 0.715 | |
| Convert voltage | V _{F2} | I _F = 10mA | - | - | 0.855 | v |
| Forward voltage | V _{F3} | I _F = 50mA | - | - | 1.0 | \ \ |
| | V _{F4} | I _F = 150mA | - | - | 1.25 | |
| Davana aumant | I _{R1} | V _R = 75V | - | - | 1 | μA |
| Reverse current | I _{R2} | V _R = 20V | - | - | 25 | nA |
| Capacitance between terminals | Ст | V _R = 0V, f = 1MHz | - | - | 2 | pF |
| Reverse recovery time | t _{rr} | $I_F = I_R = 10 \text{mA}, I_{rr} = 1 \text{mA}, R_L = 100 \Omega$ | - | - | 4 | ns |


¹⁾ Measured with the device mounted on 1 inch 2 FR-4 board with 1oz. single-side copper, in a still air environment with T_a = 25 $^{\circ}$ C.

TYPICAL CHARACTERISTICS












SOD-323 PACKAGE OUTLINE DIMENSIONS








| Cumbal | Dimensions | In Millimeters | Dimension | s In Inches |
|--------|------------|----------------|-----------|-------------|
| Symbol | Min | Max | Min | Max |
| Α | | 1.100 | | 0.043 |
| A1 | 0.000 | 0.100 | 0.000 | 0.004 |
| A2 | 0.800 | 1.000 | 0.031 | 0.039 |
| b | 0.250 | 0.350 | 0.010 | 0.014 |
| С | 0.080 | 0.150 | 0.003 | 0.006 |
| D | 1.200 | 1.400 | 0.047 | 0.055 |
| E | 1.600 | 1.800 | 0.063 | 0.071 |
| E1 | 2.500 | 2.750 | 0.098 | 0.108 |
| L | 0.475 REF | | 0.019 | REF |
| L1 | 0.250 | 0.400 | 0.010 | 0.016 |
| θ | 0° | 8° | 0° | 8° |

SOD-323 SUGGESTED PAD LAYOUT




Note:

- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

SOD-323 TAPE AND REEL

SOD-323 Embossed Carrier Tape





Packaging Description:

SOD-323 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

| Dimensions are in millimeter | | | | | | | | | | |
|------------------------------|------|-----|------|-------|------|------|------|------|------|------|
| Pkg type | Α | В | С | d | E | F | P0 | Р | P1 | W |
| SOD-323 | 1.48 | 3,3 | 1.25 | Ø1.50 | 1.75 | 3.50 | 4.00 | 4.00 | 2.00 | 8.00 |

SOD-323 Tape Leader and Trailer





| Dimensions are in millimeter | | | | | | | | |
|------------------------------|---------|-------|-------|--------|--------|-------|------|-------|
| Reel Option | D | D1 | D2 | G | Н | I | W1 | W2 |
| 7"Dia | Ø178.00 | 54.40 | 13.00 | R78.00 | R25.60 | R6.50 | 9.50 | 12.30 |

| REEL | Reel Size | Box | Box Size(mm) | Carton | Carton Size(mm) | G.W.(kg) |
|----------|-----------|------------|--------------|-------------|-----------------|----------|
| 3000 pcs | 7 inch | 45,000 pcs | 203×203×195 | 180,000 pcs | 438×438×220 | |

PUBLISHED BY

JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

13th Floor, C Block, Tengfei Building, Yan Chuang Yuan, Nanjing Jiangbei New Area, China

LEGAL DISCLAIMER

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples, hints or typical values stated herein and/or any information regarding the application of the device, JSCJ hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of JSCJ in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

INFORMATION

For further information on technology, delivery terms and conditions as well as prices, please contact your nearest JSCJ office (www.jscj-elec.com).

WARNINGS

Due to technical requirements, products may contain dangerous substances. For information on the types in question, please contact your nearest JSCJ office.

Except as otherwise explicitly approved by JSCJ in a written document signed by authorized representatives of JSCJ, JSCJ's products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.