



REV.	ECN NO.	REVISED	DATE

NOTE:


1.MATERIAL:

- a.HOUSING:PP BLACK
- b.SPRING:MUSIC WIRE
(SURFACE PLATING: NI100u"~120u")

SEE ORDERING INFORMATION


2.ELECTRIC:

- a.DIELECTRIC VOLTAGE: 270V AC ONE SEC LEVEL
- b.OPERATING TEMPERATURE: -40° C~ +80° C



②

2-Ø2,60



①

ORDERING INFORMATION
BH-AA-B1AJ011

电池盒

电池型号

SMT 180° TYPE

PLATING:

- A-Au1U"
- J-Ni100U"~120U"
- K-Sn100U"~120U"

MATERIAL:

- 1A-PP BLACK
- 1B-PA66 BLACK
- 2A-PPA BROWN
- 2B-PPA BLACK
- 3A-PPS BROWN
- 3B-PPS BLACK
- 4A-LCP WHITE
- 4B-LCP BLACK



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND YangFeng	DATE 2020-11-28
		CHKD ZhouRuicai	DATE 2020-11-28
		APVD XueShunyong	DATE 2020-11-28
WEIGHT:		SCALE:	SIZE: A4
SHEET 1 OF 1		VIEW:	OBJECT: MY
		UNIT: mm	REV.: A/1
		DATE: 2020-11-28	TITLE: 电池盒BH-AA-3J (26#线长150mm带PH2.0反向插头)
		DATE: 2020-11-28	PART NO.: BH-AA-B1AJ011
		DATE: 2020-11-28	DRAW NO.:WD-CP-0113

2	SPRING	3	MUSIC WIRE	Ni-Plating
1	HOUSING	1	PP	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR