# EVERLIGHT

# DATASHEET

# 3mm Photodiode,T-1 PD234-6B/L3



#### **Features**

- •Fast response time
- •High photo sensitivity
- Small junction capacitance
- •Pb free
- •This product itself will remain within RoHS compliant version.
- •Compliance with EU REACH
- •

## Description

PD234-6B/L3 is a high speed and high sensitive PIN photodiode in a standard  $3\Phi$  plastic package. The device is Spectrally matched to visible and infrared emitting diode.

## Applications

- •Automatic door sensor
- •Copier
- Game machine

#### **Device Selection Guide**

| Chip<br>Materials | Lens Color |
|-------------------|------------|
| Silicon           | Black      |

# Absolute Maximum Ratings (Ta=25℃)

| Parameter                          | Symbol           | Rating     | Unit |  |  |
|------------------------------------|------------------|------------|------|--|--|
| Reverse Voltage                    | VR               | 32         | V    |  |  |
| Operating Temperature              | T <sub>opr</sub> | -40 ~ +85  | C    |  |  |
| Storage Temperature                | T <sub>stg</sub> | -40 ~ +100 | Ĵ    |  |  |
| Soldering Temperature              | T <sub>sol</sub> | 260        | Ĵ    |  |  |
| Power Dissipation at<br>(or below) | Pc               | 150        | mW   |  |  |
| 25℃ Free Air Temperature           |                  |            |      |  |  |
|                                    |                  |            |      |  |  |


# Electro-Optical Characteristics (Ta=25°C)


| Parameter                      | Symbol                           | Min. | Тур. | Max. | Unit | Condition  |
|--------------------------------|----------------------------------|------|------|------|------|--|
| Range Of Spectral Bandwidth    | λ0.5                             | 840  |      | 1100 | nm   |  |
| Wavelength Of Peak Sensitivity | λP                               |      | 940  |      | nm   |  |
| Open-Circuit Voltage           | V <sub>oc</sub>                  |      | 0.42 |      | V    | Ee=1mW/cm²<br>λp=940nm   |
| Short- Circuit Current         | Isc                              |      | 9    |      | μA   | Ee=1mW/cm²<br>λp=940nm   |
| Reverse Light Current          | IL.                              | 3.9  | 10   |      | μA   | Ee=1mW/cm <sup>2</sup><br>$\lambda p$ =940nm<br>V <sub>R</sub> =5V |
| Reverse Dark Current           | ID                               |      |      | 10   | nA   | Ee=0mW/cm <sup>2</sup><br>V <sub>R</sub> =10V                      |
| Reverse Breakdown Voltage      | V <sub>BR</sub>                  | 32   | 170  |      | μA   | Ee=0mW/cm²<br>I <sub>R</sub> =100µA                                |
| Total Capacitance              | Ct                               |      | 10   | -    | pF   | Ee=0mW/cm <sup>2</sup><br>V <sub>R</sub> =5V<br>f=1MHz             |
| Rise Time/ Fall Time           | t <sub>r/</sub> / t <sub>f</sub> |      | 10   |      | ns   | V <sub>R</sub> =10V<br>R <sub>L</sub> =100Ω                        |


#### Note:

Tolerance of Luminous Intensity: ±10% Tolerance of Dominant Wavelength: ±1nm Tolerance of Forward Voltage: ±0.1V










DATASHEET 3mm Phototransistor PD234-6B/L3




# **Package Dimension**



Note: Tolerances unless dimensions ±0.25mm



Label Form Specification



- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number
- X: Month
- Reference: Identify Label Number

Packing Quantity

- 1. 200~1000 PCS/1 Bag, 4 Bags/1 Box
- 2. 10 Boxes/1 Carton

#### DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.