



ITEM	XRRH 3.5*3.0*0.8TAPING
PART NO.	
ELECTRICAL REQUIREMENTS	IMPEDANCE Z: 35 MIN OHM(100MHZ)

### TEST MEHOD

APPEARANCE STANDARD	VISION
INSPECTION LEVEL	MIL-SID-105D AQL=0.1
CHARACT&SIZE	LEVEL S-3
SURFACE	LEVEL II
TEST EQUIPMENT	HP-4191A
TEST FREQUENCY	100MHZ
COIL SPEC	

### DIMENSION

(UNIT:mm)



$$A=3.50 \pm 0.20\text{m/m}$$

$$C=0.80 \pm 0.20\text{m/m}$$

$$D=3.00 \pm 0.20\text{m/m}$$



ITEM	XRRH 3.5*3.0*0.8TAPING
PART NO.	

**PACKAGING**

Available in tape and reel bulk


**TAPE DIMENSION:**

TYPE	B	E	F	H	I	J	P	d1-d2
XRRH3.5*3.0*0.8	63.00	6.00	52.2	4.20	1.35	0.80	5.00	1.20
	±3.00	±0.50	±1.50	MIN	MAX	MAX	±0.50	MAX




### TEST DATA

CUSTOMER		QUANTITY							
ITEM	XRRH 3.5*3.2*0.8 TAPING	COIL SPEC							
PART NO.		TEST FREQUENCY	100MHZ						
HUMIDITY	63%	TEST EQUIPMENT	HP-4191A						
TEMPERATURE	23°C								
	TESTRESOLUTION		DIMENSION(UNIT:mm)						
	Z MHZ	Z1 MHZ	Z2 100MHZ	A	B	C	D	E	F
SPEC	Ω MIN	Ω MIN	35 Ω MIN	3.50 ±0.20		0.80 ± 0.20	3.00 ±0.20		
1			38	3.45		0.80	3.20		
2			37	3.48		0.85	3.12		
3			41	3.50		0.90	3.15		
4			39	3.52		0.98	3.18		
5			42	3.55		0.99	3.19		
6									
7									
8									
9									
10									
MEAN									
R									



ITEM: XRRH 3.5\*3.0\*0.8 TAPING



METER: HP-4191A