



ITEM	L5 XRRH 3.5*8.0*0.8TAPING
PART NO.	RH358008N
ELECTRICAL REQUIREMENTS	IMPEDANCE Z:85 MIN OHM(100MHZ)

TEST MEHOD

APPEARANCE STANDARD	VISION
INSPECTION LEVEL	MIL-SID-105D AQL=0.1
CHARACT&SIZE	LEVEL S-3
SURFACE	LEVEL II
TEST EQUIPMENT	HP-4191A
TEST FREQUENCY	100MHZ
COIL SPEC	

DIMENSION

(UNIT:mm)



$$A=3.50 \pm 0.20\text{m/m}$$

$$C=0.80 \pm 0.20\text{m/m}$$

$$D=8.00 \pm 0.20\text{m/m}$$



ITEM	XRRH 3.5*8.0*0.8TAPING
PART NO.	

PACKAGING

Available in tape and reel bulk


TAPE DIMENSION:

TYPE	B	E	F	H	I	J	P	d1-d2
XRRH3.5*8.0*0.8	63.00	6.00	52.2	4.20	1.35	0.80	5.00	1.20
	±3.00	±0.50	±1.50	MIN	MAX	MAX	±0.50	MAX




TEST DATA

CUSTOMER		QUANTITY							
ITEM	XRRH 3.5*8.0*0.8 TAPING	COIL SPEC							
PART NO.		TEST FREQUENCY	100MHZ						
HUMIDITY	63%	TEST EQUIPMENT	HP-4191A						
TEMPERATURE	23°C								
	TESTRESOLUTION		DIMENSION(UNIT:mm)						
	Z MHZ	Z MHZ	Z 100MHZ	A	B	C	D	E	F
SPEC	Ω MIN	Ω MIN	85 Ω MIN	3.50 ±0.20		0.80 ± 0.20	8.00 ±0.20		
1			117	3.49		0.80	7.98		
2			117	3.51		0.86	8.00		
3			116	3.48		0.87	7.97		
4			118	3.50		0.92	8.01		
5			117	3.52		0.95	7.99		
6									
7									
8									
9									
10									
MEAN			147	3.48			7.99		
R			2	0.02			0.04		



ITEM: XRRH 3.5*8.0*0.8TAPING



METER: HP-4191A