







REV.	ECN NO OR DESCRIPTION	REVISED	DATE



CARD INSERT LARYUOT





NOTES:

- ELECTRICAL:
 VOLTAGE :50V AC
 CURRENT: 0.5A Max
 CONTACT RESISTANCE: 40MΩ MAX
 VOLTAGE PROOF: 500V AC
 INSULATION RESISTANCE: 1000MΩ MIN
- MECHANICAL:
 CARD INSERTION/WITHDRAWAL FORCE: 10N MAX
 PUSH IN STRENGTH: 10N
 DURABILITY: 5,000 CYCLES
- MATERIAL:
 HOUSING: LCP UL94V-0 BLACK
 SLIDE: LCP UL94V-0 BLACK
 LATCH: PHOSPHOR BRONZE
 CONTACT:PHOSPHOR BRONZE
 SHELL:STAINLESS STEEL
 SPRING:STAINLESS STEEL
 CRANK-AXLE:STAINLESS STEEL

PIN ASSIGNMENTS

Pin#	Name	Description
1	DAT2	Data Line(Bit 2)
2	CD/DAT3	Card Detect/Data line(Bit 3)
3	CMD	Command/Response
4	V _{DD}	Supply voltage
5	CLK	Clock
6	V _{SS}	Supply voltage ground
7	DAT0	Data Line (Bit 0)
8	DAT1	Data Line (Bit 1)
9	GND	
10	COMMON	CD1
11	DETECT SW(GND)	CD2



RECOMMENDED P.C.B HOLE LAYOUT COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS:	ANGLES:	TITLE T-FLASH CARD PUSH PUSH 1.29H		
X :±0.30	X :±2°	DWN	xiong	PART NO. MR-1207-P8
X.X :±0.25	X.X :±1°	CHKD	lee	SCALE:1:1 UNIT: mm
X.XX :±0.10		APVD	wang	SIZE: A4 SHEET:10F 1 REV: A4
CUSTOMER COPY				