





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2005
 © COPYRIGHT 2005 BY - ALL RIGHTS RESERVED.

△ MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC
 POLYESTER(94V-0), COLOR: BLACK
 CONTACT: COPPER ALLOY
 RETENTION LEG: PRE-TIN COPPER ALLOY
 △2 FINISH(ALL OVER): NICKEL PL. 1.27μmMIN
 △3 FINISH(CONTACT AREA): TIN PL. 1.0μmMIN AFTER △2
 △4 FINISH(CONTACT TAIL): TIN PL. 2μmMIN AFTER △2

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASED	26JUN2017	N.W	C.W



RECOMMEND PC BOARD HOLE PATTERN
 : CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
 PC BOARD THICKNESS : 1.0~1.6±0.1mm.



20	X	9	18.0	21.0	22.6	1-2271887-0
10	X	4	8.0	11.0	12.6	1-2271887-5
POS.	KEY	n	A	B	C	PART NO.

20P: 1-2271887-0

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-PLC ±0.3, ±3° 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ± FINISH	DWN	Ning Wang	22MAY2017
		CHK	Chris Wang	22MAY2017
MATERIAL	△1 △2 △3 △4	APVD	Chris Wang	22MAY2017
		PRODUCT SPEC	108-78298	
		APPLICATION SPEC	114-5377	
		WEIGHT		




Customer Drawing

NAME		DYNAMIC D1100D 2.0mmPITCH HDR ASSY, H-TYPE 4-20POS	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2271887	
SCALE	6:1	SHEET	1 OF 2
REV	A		


STE TE Connectivity

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2005
 © COPYRIGHT 2005 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-		SEE SHEET 1	-	-



10P: 1-2271887-5

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Ning Wang 22MAY2017	 TE Connectivity															
DIMENSIONS: mm		CHK Chris Wang 22MAY2017																
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Chris Wang 22MAY2017	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY, H-TYPE 4-20POS															
<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±0.3</td></tr> <tr><td>2 PLC</td><td>±0.10</td></tr> <tr><td>3 PLC</td><td>±0.001</td></tr> <tr><td>4 PLC</td><td>±0.0001</td></tr> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>FINISH</td><td></td></tr> </table>		0 PLC	±	1 PLC	±0.3	2 PLC	±0.10	3 PLC	±0.001	4 PLC	±0.0001	ANGLES	±	FINISH		PRODUCT SPEC 108-78298	SIZE A200779	
0 PLC	±																	
1 PLC	±0.3																	
2 PLC	±0.10																	
3 PLC	±0.001																	
4 PLC	±0.0001																	
ANGLES	±																	
FINISH																		
MATERIAL		APPLICATION SPEC 114-5377	DRAWING NO C-2271887															
		WEIGHT	RESTRICTED TO															
		Customer Drawing	SCALE 6:1 SHEET 2 OF 2 REV A															