



Features:

- Fast Switching
- Low ON Resistance ($R_{dson} \leq 0.8\Omega$)
- Low Gate Charge (Typical Data: 29nC)
- Low Reverse transfer capacitances (Typical: 25pF)
- 100% Single Pulse avalanche energy Test

Applications:

- Power switch circuit of adaptor and charger

V_{DSS}	500	V
I_D	8	A
$P_D(T_C=25^\circ C)$	45	W
$R_{DS(ON).TYP.}$	0.6	Ω



Absolute ($T_c=25^\circ C$ unless otherwise specified):

Symbol	Parameter	Rating	Units
V_{DSS}	Drain-to-Source Voltage	500	V
I_D	Continuous Drain Current	8	A
	Continuous Drain Current $T_C=100^\circ C$	5.7	A
I_{DM}^{a1}	Pulsed Drain Current	32	A
V_{GS}	Gate-to-Source Voltage	± 30	V
E_{AS}^{a2}	Single Pulse Avalanche Energy	620	mJ
dv/dt^{a3}	Peak Diode Recovery dv/dt	5.0	V/ns
P_D	Power Dissipation	45	W
	Derating Factor above $25^\circ C$	0.36	W/ $^\circ C$
T_J, T_{stg}	Operating Junction and Storage Temperature Range	150, -55 to 150	$^\circ C$
T_L	Maximum Temperature for Soldering	300	$^\circ C$

Caution Stresses greater than those in the "Absolute Maximum Ratings" may cause permanent damage to the device

Thermal Characteristics

Symbol	Parameter	Rating	Units
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	2.78	$^\circ C/W$
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	100	$^\circ C/W$

Electrical Characteristics (Tc= 25°C unless otherwise specified):

OFF Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
V _{DSS}	Drain to Source Breakdown Voltage	V _{GS} =0V, I _D =250μA	500	--	--	V
I _{DSS}	Drain to Source Leakage Current	V _{DS} =500V, V _{GS} =0V, T _a =25°C	--	--	1.0	μA
		V _{DS} =400V, V _{GS} =0V, T _a =125°C	--	--	100	
I _{GSS(F)}	Gate to Source Forward Leakage	V _{GS} = +30V	--	--	100	nA
I _{GSS(R)}	Gate to Source Reverse Leakage	V _{GS} = -30V	--	--	-100	nA

ON Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
R _{DS(ON)}	Drain-to-Source On-Resistance	V _{GS} = 10V, I _D =4.5A	--	0.6	0.80	Ω
V _{GS(TH)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	2.0	--	4.0	V
g _{fs}	Forward Trans conductance	V _{DS} = 15V, I _D =4.5A	--	6.2	--	S
Pulse width <380μs; duty cycle <2%.						

Dynamic Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
C _{iss}	Input Capacitance	V _{GS} =0V V _{DS} =25V f=1.0MHz	--	850	--	pF
C _{oss}	Output Capacitance		--	150	--	
C _{rss}	Reverse Transfer Capacitance		--	25	--	

Resistive Switching Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
t _{d(ON)}	Turn-on Delay Time	I _D =8A, V _{DD} =250V V _{GS} = 10V, R _g =25Ω	--	65	--	ns
t _r	Rise Time		--	50	--	
t _{d(OFF)}	Turn-Off Delay Time		--	100	--	
t _f	Fall Time		--	65	--	
Q _g	Total Gate Charge	I _D =8A, V _{DD} =400V V _{GS} = 10V	--	29	--	nC
Q _{gs}	Gate to Source Charge		--	4.3	--	
Q _{gd}	Gate to Drain ("Miller")Charge		--	13	--	

Source-Drain Diode Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
I_{SD}	Continuous Source Current (Body Diode)		--	--	8	A
I_{SM}	Maximum Pulsed Current (Body Diode)		--	--	32	A
V_{SD}	Diode Forward Voltage	$I_S=8A, V_{GS}=0V$	--	--	1.4	V
t_{rr}	Reverse Recovery Time	$I_S=8A, T_J=25^\circ C$	--	330	--	ns
Q_{rr}	Reverse Recovery Charge	$di_F/dt=100A/\mu s, V_{GS}=0V$	--	2.5	--	μC

a1: Repetitive rating; pulse width limited by maximum junction temperature

a2: $L=10mH, I_D=11.1A$, Start $T_J=25^\circ C$

a3: $I_{SD}=8A, di/dt \leq 100A/\mu s, V_{DD} \leq BV_{DS}$, Start $T_J=25^\circ C$

Characteristics Curves




Figure 1 Maximum Forward Bias Safe Operating Area




Figure 2 Maximum Power Dissipation vs Case Temperature




Figure 3 Maximum Continuous Drain Current vs Case Temperature




Figure 4 Typical Output Characteristics




Figure 5 Maximum Effective Thermal Impedance, Junction to Case




Figure 6 Maximum Peak Current Capability




Figure 7 Typical Transfer Characteristics




Figure 8 Typical Drain to Source ON Resistance vs Gate Voltage and Drain Current




Figure 9 Typical Drain to Source ON Resistance vs Drain Current




Figure 10 Typical Drain to Source on Resistance vs Junction Temperature




Figure 11 Typical Threshold Voltage vs Junction Temperature




Figure 12 Typical Breakdown Voltage vs Junction Temperature




Figure 13 Typical Capacitance vs Drain to Source Voltage




Figure 14 Typical Gate Charge vs Gate to Source Voltage




Figure 15 Typical Body Diode Transfer Characteristics




Figure 16 Unclamped Inductive Switching Capability