

DESCRIPTION

This new series of digital transistors is designed to replace a single device and its external resistor bias network. The BRT (Bias Resistor Transistor) contains a single transistor with a monolithic bias network consisting of two resistors; a series base resistor and a base-emitter resistor. The BRT eliminates these individual components by integrating them into a single device. The use of a BRT can reduce both system cost and board space. The device is housed in the SOT-723 package which is designed for low power surface mount applications.

The DTC144EM ~ DTC144TM are available in SOT-723 package


FEATURES

- Simplifies Circuit Design
- Reduces Board Space
- Reduces Component Count
- The SOT-723 Package can be Soldered using Wave or Reflow.
- Available in 4 mm, 8000 Unit Tape & Reel
- Available in SOT-723 package

ORDERING INFORMATION

| Package Type | Part Number |
|--|--------------------|
| SOT-723 | DTC114EM |
| | DTC124EM |
| | DTC144EM |
| | DTC114YM |
| | DTC114TM |
| | DTC143TM |
| | DTC123EM |
| | DTC143EM |
| | DTC143ZM |
| | DTC124XM |
| | DTC123JM |
| | DTC115EM |
| | DTC144WM |
| | DTC144TM |
| Note | SPQ: 8,000Pcs/Reel |
| AiT provides all RoHS Compliant Products | |

PIN DESCRIPTION



ABSOLUTE MAXIMUM RATINGS

$T_A = 25^\circ\text{C}$, unless otherwise noted

| | |
|---------------------------------------|---------------------|
| V_{CBO} , Collector-Base Voltage | 50Vdc |
| V_{CEO} , Collector-Emitter Voltage | 50Vdc |
| I_C , Collector Current | 100mA _{dc} |

Stresses above may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated in the Electrical Characteristics are not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

THERMAL CHARACTERISTICS

| Parameter | Symbol | Value | Unit |
|---|-----------------|--|---------------------------|
| Total Device Dissipation $T_A = 25^\circ\text{C}$ Derate above 25°C | P_D | 260 ^{NOTE1} | mW |
| | | 600 ^{NOTE2} | |
| | | 2.0 ^{NOTE1} | mW/ $^\circ\text{C}$ |
| | | 4.8 ^{NOTE2} | |
| Thermal Resistance – Junction-to-Ambient | $R_{\theta JA}$ | 480 ^{NOTE1} 205 ^{NOTE2} | $^\circ\text{C}/\text{W}$ |
| Junction Temperature | T_J | 150 | $^\circ\text{C}$ |
| Storage Temperature Range | T_{STG} | -55 to +150 | $^\circ\text{C}$ |

NOTE1: FR-4 @ Minimum Pad

NOTE2: FR-4 @ 1.0 x 1.0 inch Pad

ELECTRICAL CHARACTERISTICS

T_A = 25°C, unless otherwise noted

| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Unit | | | | |
|--|----------------------|--|------|------|----------|----------|-----|-----|--|--|
| OFF CHARACTERISTICS | | | | | | | | | | |
| Collector-Base Cutoff Current | I _{CBO} | V _{CB} = 50V, I _E = 0 | - | - | 100 | nAdc | | | | |
| Collector-Emitter Cutoff Current | I _{CEO} | V _{CE} = 50V, I _B = 0 | - | - | 500 | nAdc | | | | |
| Emitter-Base Cutoff Current | I _{EBO} | V _{EB} = 6.0V, I _C = 0 | - | - | DTC114EM | 0.5 | | | | |
| | | | | | DTC124EM | 0.2 | | | | |
| | | | | | DTC144EM | 0.1 | | | | |
| | | | | | DTC114YM | 0.2 | | | | |
| | | | | | DTC114TM | 0.9 | | | | |
| | | | | | DTC143TM | 1.9 | | | | |
| | | | | | DTC123EM | 2.3 | | | | |
| | | | | | DTC143EM | 1.5 | | | | |
| | | | | | DTC143ZM | 0.18 | | | | |
| | | | | | DTC124XM | 0.13 | | | | |
| | | | | | DTC123JM | 0.2 | | | | |
| | | | | | DTC115EM | 0.05 | | | | |
| | | | | | DTC144WM | 0.13 | | | | |
| DTC144TM | 0.2 | | | | | | | | | |
| Collector-Base Breakdown Voltage | V _{(BR)CBO} | I _C = 10μA, I _E = 0 | 50 | - | - | Vdc | | | | |
| Collector-Emitter Breakdown Voltage ^{NOTE3} | V _{(BR)CEO} | I _C = 2.0mA, I _B = 0 | 50 | - | - | Vdc | | | | |
| ON CHARACTERISTICS^{NOTE3} | | | | | | | | | | |
| DC Current Gain | h _{FE} | V _{CE} =10V, I _C =5.0mA | | | | DTC114EM | 35 | 60 | | |
| | | | | | | DTC124EM | 60 | 100 | | |
| | | | | | | DTC144EM | 80 | 140 | | |
| | | | | | | DTC114YM | 80 | 140 | | |
| | | | | | | DTC114TM | 160 | 350 | | |
| | | | | | | DTC143TM | 160 | 350 | | |
| | | | | | | DTC123EM | 8.0 | 15 | | |
| | | | | | | DTC143EM | 15 | 30 | | |
| | | | | | | DTC143ZM | 80 | 200 | | |
| | | | | | | DTC124XM | 80 | 150 | | |
| | | | | | | DTC123JM | 80 | 140 | | |
| | | | | | | DTC115EM | 80 | 150 | | |
| | | | | | | DTC144WM | 80 | 140 | | |
| DTC144TM | 160 | 350 | | | | | | | | |

| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Unit | |
|--------------------------------------|---------------|---|------|------|--|------|--|
| Collector-Emitter Saturation Voltage | $V_{CE(sat)}$ | $I_C = 10\text{mA}, I_B = 0.3\text{mA}$ | - | - | 0.25 | Vdc | |
| | | $I_C = 10\text{mA}, I_B = 5\text{mA}$ | | | | | DTC123EM |
| | | $I_C = 10\text{mA}, I_B = 1\text{mA}$ | | | | | DTC143TM DTC114TM DTC143EM DTC143ZM DTC124XM DTC144TM |
| Output Voltage (on) | V_{OL} | $V_{CC} = 5.0\text{V}, V_B = 2.5\text{V}, R_L = 1.0\text{k}\Omega$ | - | - | 0.2 | Vdc | |
| | | | | | DTC114EM DTC124EM DTC114YM DTC114TM DTC143TM DTC123EM DTC143EM DTC143ZM DTC124XM DTC123JM | | 0.2 |
| | | $V_{CC} = 5.0\text{V}, V_B = 3.5\text{V}, R_L = 1.0\text{k}\Omega$ | | | DTC144EM DTC144TM | | 0.2 |
| | | $V_{CC} = 5.0\text{V}, V_B = 5.5\text{V}, R_L = 1.0\text{k}\Omega$ | | | DTC115EM | | 0.2 |
| | | $V_{CC} = 5.0\text{V}, V_B = 4.0\text{V}, R_L = 1.0\text{k}\Omega$ | | | DTC144WM | | 0.2 |
| Output Voltage (off) | V_{OH} | $V_{CC} = 5.0\text{V}, V_B = 0.5\text{V}, R_L = 1.0\text{k}\Omega$ | 4.9 | - | - | Vdc | |
| | | $V_{CC} = 5.0\text{V}, V_B = 0.25\text{V}, R_L = 1.0\text{k}\Omega$ | | | | | DTC143TM DTC143ZM DTC114TM DTC144TM |

| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Unit | |
|----------------|--------------------------------|--|---------------------|---|----------|------|---|
| Input Resistor | R1 | DTC114EM | 7.0 | 10 | 13 | kΩ | |
| | | DTC124EM | 15.4 | 22 | 28.6 | | |
| | | DTC144EM | 32.9 | 47 | 61.1 | | |
| | | DTC114YM | 7.0 | 10 | 13 | | |
| | | DTC114TM | 7.0 | 10 | 13 | | |
| | | DTC143TM | 3.3 | 4.7 | 6.1 | | |
| | | DTC123EM | 1.5 | 2.2 | 2.9 | | |
| | | DTC143EM | 3.3 | 4.7 | 6.1 | | |
| | | DTC143ZM | 3.3 | 4.7 | 6.1 | | |
| | | DTC124XM | 15.4 | 22 | 28.6 | | |
| | | DTC123JM | 1.54 | 2.2 | 2.86 | | |
| | | DTC115EM | 70 | 100 | 130 | | |
| | | DTC144WM | 32.9 | 47 | 61.1 | | |
| | | DTC144TM | 32.9 | 47 | 61.1 | | |
| Resistor Ratio | R ₁ /R ₂ | DTC114EM/DTC124EM/ DTC144EM/DTC115EM | 0.8 | 1.0 | 1.2 | | |
| | | DTC114YM | 0.17 | 0.21 | 0.25 | | |
| | | DTC143TM/DTC114TM/ DTC144TM | - | - | - | | |
| | | DTC123EM/DTC143EM | 0.8 | 1.0 | 1.2 | | |
| | | DTC143ZM | 0.055 | 0.1 | 0.185 | | |
| | | DTC124XM | 0.38 | 0.47 | 0.56 | | |
| | | DTC123JM | 0.038 | 0.047 | 0.056 | | |
| | | DTC144WM | 1.7 | 2.1 | 2.6 | | |
| | | Input Voltage | V _{I(off)} | V _{CC} = 5.0V, I _O = 100μA | DTC123JM | | - |
| Input Voltage | V _{I(on)} | V _O = 0.3V, I _O = 5mA | DTC123JM | 1.1 | - | - | V |


NOTE3: Pulse Test: Pulse Width < 300 μs, Duty Cycle < 2.0%

RESISTOR VALUES

| Device | R1 (k) | R2 (k) |
|----------|--------|--------|
| DTC114EM | 10 | 10 |
| DTC124EM | 22 | 22 |
| DTC144EM | 47 | 47 |
| DTC114YM | 10 | 47 |
| DTC114TM | 10 | ∞ |
| DTC143TM | 4.7 | ∞ |
| DTC123EM | 2.2 | 2.2 |
| DTC143EM | 4.7 | 4.7 |
| DTC143ZM | 4.7 | 47 |
| DTC124XM | 22 | 47 |
| DTC123JM | 2.2 | 47 |
| DTC115EM | 100 | 100 |
| DTC144WM | 47 | 22 |
| DTC144TM | 47 | ∞ |

TYPICAL CHARACTERISTICS

Figure 1. Derating Curve



DTC114EM

Figure 2. $V_{CE(sat)}$ vs. I_C




Figure 3. DC Current Gain




Figure 4. Output Capacitance




Figure 5. Output Current vs. Input Voltage





Figure 6. Input Voltage vs. Output Current



DTC124EM

Figure 7. $V_{CE(sat)}$ vs. I_C




Figure 8. DC Current Gain




Figure 9. Output Capacitance




Figure 10. Output Current vs. Input Voltage





Figure 11. Input Voltage vs. Output Current



DTC144EM

Figure 12. $V_{CE(sat)}$ vs. I_C




Figure 14. Output Capacitance




Figure 16. Input Voltage vs. Output Current




Figure 13. DC Current Gain





Figure 15. Output Current vs. Input Voltage



DTC114YM

Figure 17. $V_{CE(sat)}$ vs. I_C




Figure 19. Output Capacitance




Figure 21. Input Voltage vs. Output Current




Figure 18. DC Current Gain





Figure 20. Output Current vs. Input Voltage



DTC143ZM

Figure 22. $V_{CE(sat)}$ versus I_C




Figure 24. Output Capacitance




Figure 23. DC Current Gain




Figure 25. Output Current vs. Input Voltage





Figure 26. Input Voltage vs. Output Current



TYPICAL APPLICATIONS FOR NPN BRTs

Figure 27. Level Shifter: Connects 12 or 24 Volt Circuits to Logic




Figure 28. Open Collector Inverter:
 Inverts the Input Signal






Figure 29. Inexpensive, Unregulated Current Source




PACKAGE INFORMATION

Dimension in SOT-723 (Unit: mm)



SOLDERING FOOTPRINT



| DIM | MILLIMETERS | | INCHES | |
|-----|-------------|------|-----------|--------|
| | MIN | MAX | MIN | MAX |
| A | 0.45 | 0.55 | 0.018 | 0.022 |
| b | 0.15 | 0.27 | 0.0059 | 0.0106 |
| b1 | 0.25 | 0.35 | 0.010 | 0.014 |
| C | 0.07 | 0.17 | 0.0028 | 0.0067 |
| D | 1.15 | 1.25 | 0.045 | 0.049 |
| E | 0.75 | 0.85 | 0.03 | 0.034 |
| e | 0.40 BSC | | 0.016 BSC | |
| HE | 1.15 | 1.25 | 0.045 | 0.049 |
| L | 0.15 | 0.25 | 0.0059 | 0.0098 |