



## Features

- Low Crss (typical 22pF )
- Low gate charge
- 100% avalanche tested
- Improved dv/dt capability
- RoHS product



## Applications

- UPS
- High efficiency switch mode power supplies
- Electronic lamp ballasts based on half bridge



## Absolute Ratings (Tc=25°C)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V <sub>DSS</sub>	400	V
Gate-Source Voltage	V <sub>GSS</sub>	±30	V
Drain Current-continuous	I <sub>D</sub>	10	A
Drain Current-pulse	I <sub>DM</sub>	30	A
Single Pulsed Avalanche Energy	E <sub>AS</sub>	450	mJ
Maximum Power Dissipation(TO-220)	PD	134	W
Maximum Power Dissipation(TO-220F)	PD	68	
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-55~+150	°C

\*Drain current limited by maximum junction temperature

## Electrical Characteristics(T<sub>CASE</sub>=25°C unless otherwise specified)

Parameter	Symbol	Tests conditions	Min	Typ	Max	Units
Drain-Source Voltage	BV <sub>DSS</sub>	I <sub>D</sub> =0.25mA, V <sub>GS</sub> =0V	400	-	-	V
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> =V <sub>DSS</sub> , V <sub>GS</sub> =0V	-	-	10	μA
Gate-Body Leakage Current	I <sub>GSS</sub>	V <sub>GS</sub> =±30V, V <sub>DS</sub> =0V	-	-	±100	nA

<b>On-Characteristics</b>						
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=0.25mA$	2.0	-	4.0	V
Static Drain-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10V, I_D=5A$	-	0.43	0.54	$\Omega$
Forward Transconductance	$g_{fs}$	$V_{DS}=40V, I_D=5A$	-	9.6	-	S
<b>Dynamic Characteristics</b>						
Input capacitance	$C_{iss}$	$V_{DS}=25V, V_{GS}=0V, f=1.0MHz$	-	650	809	pF
Output capacitance	$C_{oss}$		-	70	95	pF
Reverse transfer capacitance	$C_{rss}$		-	25	33	pF

**Electrical Characteristics**( $T_{CASE}=25^{\circ}C$  unless otherwise specified)

Parameter	Symbol	Tests conditions	Min	Typ	Max	Units
<b>Switching-Characteristics</b>						
Turn-On delay time	$t_{d(on)}$	$V_{DS}=200V, I_D=10A, R_G=25\Omega$	-	20	50	ns
Turn-On rise time	$t_r$		-	80	170	ns
Turn-Off delay time	$t_{d(off)}$		-	125	260	ns
Turn-Off rise time	$t_f$		-	85	180	ns
Total Gate Charge	$Q_g$	$V_{DS}=320V, I_D=10A, V_{GS}=10V$	-	19.7	25.6	nC
Gate-Source charge	$Q_{gs}$		-	7.38	-	nC
Gate-Drain charge	$Q_{gd}$		-	4.66	-	nC
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
Maximum Continuous Drain-Source Diode Forward Current	$I_{SD}$	$V_{GS}=0V, I_S=10A$	-	1.5	-	V
Diode Forward Current	$I_S$	$TC=25^{\circ}C$	-	-	10	A
Reverse recovery time	$T_{rr}$	$I_S=10A, di/dT=100A/\mu S$	-	-	217	nS
Reverse recovery charge	$Q_{rr}$		-	2.45	-	$\mu C$

### Thermal Characteristic

Parameter	Symbol	Value	Unit
Thermal Resistance, junction to Case	$R_{th(j-C)}$	0.93	$^{\circ}C/W$
Thermal Resistance, junction to Ambient	$R_{th(j-A)}$	62.5	$^{\circ}C/W$

Notes:


1. Pulse width limited by maximum junction temperature
2.  $L=7.9mH$ ,  $I_{AS}=10A$ ,  $V_{DD}=50V$ ,  $R_G=25\ \Omega$ , Starting  $T_J=25^{\circ}C$
3.  $ISD \leq 10A$ ,  $di/dt \leq 300A/\mu s$ ,  $V_{DD} \leq B_{VDSS}$ , Starting  $T_J=25^{\circ}C$
4. Pulse Test: Pulse Width  $\leq 300\mu s$ , Duty Cycle  $\leq 2\%$
5. Essentially independent of operating temperature

### Order information


Order codes	Package	Packaging
MS10N40HGT0	TO-220	Tube
MS10N40HGT1	TO-220F	Tube

### Electrical Characteristics


#### On-Region Characteristics




#### Transfer Characteristics




#### On-Resistance Variation vs. Drain Current and Gate Voltage




#### Body Diode Forward Voltage Variation vs. Source Current and Temperature




#### Capacitance Characteristics




#### Gate Charge Characteristics




### Breakdown Voltage Variation vs. Temperature




### On-Resistance Variation vs. Temperature




### Maximum Safe Operating Area




### Maximum Drain Current vs. Case Temperature



### Transient Thermal Response Curve



## Package Mechanical DATA



**TO-220**

**Unit: mm**

