


1 Scope

These specifications define the requirements for surface mount conductive polymer hybrid aluminum electrolytic capacitors HXJ series.

2 Part Numbering System



① Category

Category	Code
	1st
Hybrid	H

⑥ Capacitance code

Capacitance [μ F]	Capacitance code		
	11th	12th	13th
330	3	3	1

② Series code

Series name	Series code		
	2nd	3rd	4th
HXJ	H	X	J

⑦ Capacitance tolerance code

Capacitance tolerance [%]	Capacitance tolerance code
	14th
± 20	M

③ Voltage code

Voltage [V]	Voltage code		
	5th	6th	7th
35	3	5	0

⑧ Size code

ϕ D [mm]	Size code	L [mm]	Size code	
	15th		16th	17th
10	J	10	A	0

④ Terminal code

Type	Terminal code
	8th
No dummy terminal	A

⑨ Supplement code


Terminal plating material	Supplement code
	18th
Sn-Bi	G

⑤ Taping code


Taping type	Reel dia. ϕ [mm]	Taping code	
		9th	10th
Plastic Reel	380	R	A

3 Appearance and dimensions

3.1 Dimension




3.2 Recommended solder land on PC board



Land dimensions				[mm]
Size code	a	b	c	
JA0	4.5	4.4	2.2	

4 Construction



※ No ozone depleting substance has been used.

Compliant to the RoHS Directive (2011/65/EU) and the revisions (2015/863/EU)
Halogen-Free

5 Substance Requirements

All homogeneous materials within a component or product must meet the criteria in Table-1, and Table-2. A homogeneous material has uniform composition throughout and cannot be mechanically disjointed into different materials.

Table-1 Substance restrictions for halogen-free products.

Substance	Permissible Limit (by weight)
Bromine (Br)	$\leq 900\text{ppm}$ (0.09%)
Chlorine (Cl)	$\leq 900\text{ppm}$ (0.09%)
Total concentration of chlorine (Cl) + bromine (Br)	$\leq 1500\text{ppm}$ (0.15%)

Table-2 Additional substance restrictions.

Substance	Permissible Limit (by weight)
Antimony Trioxide (Sb_2O_3)	$\leq 1000\text{ ppm}$ (0.1%)
Red Phosphorus	$\leq 1000\text{ ppm}$ (0.1%)

6 Rating and characteristics

No.	Item	Specification
1	Category temperature range	- 55 to + 125°C
2	Rated voltage range	35V _{DC}
3	Surge voltage	See Table-1
4	Rated capacitance range	See the standard rating table
5	Capacitance tolerance	- 20 to + 20%
6	Dissipation factor (tan δ)	See the standard rating table
7	Leakage current	See the standard rating table
8	Rated ripple current	See the standard rating table
9	Equivalent series resistance	See the standard rating table

Table-1 Surge voltage

Rated voltage [V _{DC}]	35
Surge voltage [V _{DC}]	40

Rated ripple current multipliers


Frequency multipliers

Frequency [Hz]	120	1k	5k	10k	20k	30k	100k to 500k
Capacitance [μ F]							
330	0.15	0.50	0.70	0.75	0.85	0.85	1.00

When a frequency is different from the specified condition shown in the table of standard ratings, do not exceed the value obtained by multiplying the permissible maximum ripple current by the multiplier above.

7 Marking

(Example)



The following items shall be marked on each capacitor.

- ① Rated voltage (Symbol)
- ② Rated capacitance
- ③ Negative polarity marking
- ④ Lot No.
- ⑤ Series code 「HJ」

Rated voltage symbol

Rated voltage [V _{DC}]	35
Symbol	V

8 Performance

Unless otherwise specified, the capacitors shall be measured at a temperature of + 15 to + 35°C , a humidity of 45 to 75%RH and a atmospheric pressure of 86 to 106kPa. However, if any doubt arises on the judgment, the measurement conditions shall be + 20 ± 2°C , 60 to 70%RH and 86 to 106kpa.

8.1 Leakage current (L.C.)

[Conditions] Rated voltage shall be applied to capacitors in series with a resistor of 1000 ± 10 Ω . Then, the leakage current shall be measured at two minutes later after the capacitors reached the rated voltage across the terminals, which is performed after the following voltage treatment.

[Voltage treatment]

A DC voltage equal to the rated voltage shall be applied to capacitors in series with a resistor of 10 to 1000 Ω for two hours at + 105 ± 2°C . Then, after restored to an ambient temperature, the capacitors are discharged through a resistor of about 1 Ω /V and left as it is in standard condition for 24 hours. (Note: The voltage treatment may be omitted.)

[Criteria] Shall not exceed the values specified in the table of Standard Ratings.

8.2 Capacitance (Cap.)

[Conditions] Measuring frequency : 120Hz ± 20%
 Measuring voltage : 0.5V rms max. + 1.5 to 2.0V_{DC}
 Measuring circuit : Series equivalent circuit (○—||—∩—○)

[Criteria] Shall be within the specified capacitance tolerance.

8.3 Dissipation factor (tan δ)

[Conditions] Measuring frequency : 120Hz ± 20%
 Measuring voltage : 0.5V rms max. + 1.5 to 2.0V_{DC}
 Measuring circuit : Series equivalent circuit (○—||—∩—○)

[Criteria] Shall not exceed the values specified in the table of Standard Ratings.

8.4 Equivalent series resistance (ESR)

- [Conditions] Measuring frequency : 100kHz \pm 10kHz
 Measuring voltage : 0.5V rms max. + 1.5 to 2.0V_{DC}
 Ambient temperature : + 20 \pm 2°C
 [Criteria] Shall not exceed the values specified in the table of Standard Ratings.

8.5 Soldering heat

- [Conditions] The capacitor shall be soldered according to recommended reflow soldering conditions, and then restored at + 20°C for the measurements.
 [Criteria] Appearance : No significant damage, legible marking no leakage of electrolyte.
 Leakage current : Shall not exceed the initial specified value (after the voltage treatment).
 Capacitance change : Shall be within \pm 10% of the initial measured value
 Tan δ : Shall not exceed the initial specified value.
 ESR : Shall not exceed the initial specified value.

SOLDERING METHODS AND THEIR RECOMMENDED CONDITIONS (Air reflow or Infrared reflow)


The following conditions are recommended for air or infrared reflow soldering of the surface mount capacitors onto a glass epoxy circuit board of 90^l \times 50^w \times 0.8^{mm} (With resist) by cream solder. The shown temperatures are the surface temperature values on the top of the can and on the capacitor terminal.

Reflow should be performed twice or less.

Please ensure that the capacitor became cold enough to the room temperature (5 to 35°C) before the second reflow.

(The reflow soldering conditions are different between the first reflow and the second reflow.)

《REFLOW TEMPERATURE PROFILE》



Preheat	Time maintained above 217°C	Time maintained above 230°C	Peak temp.	Reflow number
150 to 180°C 120 sec.max.	50 sec.max.	40 sec.max.	260°C max.	1-cycle only
			245°C max.	2-cycle allowed

8.6 Solderability

- [Conditions] Type of solder : Sn-3Ag-0.5Cu
 Flux : Ethanol solution (25 wt.% rosin)
 Solder temperature : + 245 \pm 3°C
 Immersion time : 3 \pm 0.3 sec.
 [Criteria] Solder shall cover at least 3/4 of the lead surface immersed.

8.7 Adhesion

- [Conditions] A force of 5N shall be applied to the center of the plane parallel to the line connecting the centers of terminals and at right angles to the plane of a PC board, the direction of which shall be at right angles to the plane. The force shall be applied to the capacitor body gradually without any shock and kept for 10 \pm 1 seconds.
 [Criteria] No visible damage.

8.8 Rapid change of temperature

[Conditions]

Step	
1	+ 125 ± 2°C 30 ± 3min.
2	Temperature changing time Three minutes or less
3	- 55 ± 3°C 30 ± 3min.
4	Temperature changing time Three minutes or less

Number of cycles: 100 cycles

[Criteria]	Leakage current	: Shall not exceed the initial specified value (after the voltage treatment).
	Capacitance change	: Shall be within ± 10% of the initial measured value
	Tan δ	: Shall not exceed the initial specified value.
	ESR	: Shall not exceed the initial specified value.

8.9 Vibration

[Conditions]	Vibration frequency range	: 10 to 55Hz
	Amplitude or Acceleration	: 0.75mm (Half amplitude) or 98m/s ² (Whichever is less severe)
	Sweep rate	: 10 to 55 to 10Hz in about 1 minute
	Direction and period of motion	: 2 hours in each of 3 mutually perpendicular directions (total of 6 hours)
[Criteria]	Appearance	: No significant damage, legible marking, and no electrolyte leakage.
	Capacitance change	: Shall be within ± 5% of the initial measured value.
	Leakage current	: Shall not exceed the initial specified value.
	Tan δ	: Shall not exceed the initial specified value.

8.10 Damp heat

[Conditions]	The following specifications shall be satisfied when the capacitors are restored to + 20°C after the rated voltage applied for 2,000 ⁺⁷² ₀ hours at + 85°C , 85% RH.	
[Criteria]	Appearance	: No significant damage, legible marking, and no electrolyte leakage.
	Leakage current	: Shall not exceed the initial specified value.
	Capacitance change	: Shall be within ± 30% of the initial measured value.
	Tan δ	: Shall not exceed 200% of the initial specified value.
	ESR	: Shall not exceed 200% of the initial specified value.

8.11 Endurance

[Conditions]	After the capacitors are put to a DC voltage with the rated ripple current within the rated voltage for 4,000 ⁺⁷² ₀ hours at + 125 ± 2°C , the following specifications shall be satisfied when the capacitors are restored to + 20°C . The sum of a DC voltage and a peak AC voltage must not exceed their full rated voltage.	
[Criteria]	Appearance	: No significant damage, legible marking, and no electrolyte leakage.
	Leakage current	: Shall not exceed the initial specified value.
	Capacitance change	: Shall be within ± 30% of the initial measured value.
	Tan δ	: Shall not exceed 200% of the initial specified value.
	ESR	: Shall not exceed 200% of the initial specified value.

8.12 High temperature storage

[Conditions]	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 ⁺⁴⁸ ₀ hours at + 125 ± 2°C without voltage applied. Before the measurements, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4.	
[Criteria]	Appearance	: No significant damage, legible marking, and no electrolyte leakage.
	Leakage current	: Shall not exceed the initial specified value.
	Capacitance change	: Shall be within ± 30% of the initial measured value.
	Tan δ	: Shall not exceed 200% of the initial specified value.
	ESR	: Shall not exceed 200% of the initial specified value.

8.13 Pressure relief vent

[Conditions]	Apply a reverse voltage with the DC current of 1 amp.(DC reverse voltage test)	
[Criteria]	When the pressure relief vent operated, the capacitor shall not flame although gas generation or expulsion of a part of the inside element is allowable. If the vent does not operate with the voltage applied for 30 minutes, the test is considered to be passed.	

8.14 Surge voltage test

[Conditions]	Test temperature	: + 15 to + 35°C
	Series protective resistor	: 1000 Ω
	Test voltage	: Surge voltage shown in Table-1
	Applying of voltage	: Charge 30 seconds and open circuit 5minutes 30 seconds.
	Test cycle	: 1000 cycles
	(Note) Surge voltage test intends to evaluate capacitors in durability of an exceptional excessive voltage under specific conditions. It does not imply long-term use at all.	
[Criteria]	Appearance	: No significant damage and no electrolyte leakage.
	Leakage current	: Shall not exceed the initial specified value.
	Capacitance change	: Shall be within ± 30% of the initial measured value.
	Tan δ	: Shall not exceed 200% of the initial specified value.
	ESR	: Shall not exceed 200% of the initial specified value.

8.15 High and Low Temperature characteristics

[Conditions]

Step	Temperature[°C]
1	+ 20 ± 2
2	- 25 ± 3, - 55 ± 3
3	+ 125 ± 2

Step1 : Measure ESR and impedance.

2 : Measure ESR and impedance.

3 : Measure ESR and impedance.

[Criteria] Impedance ratio (100kHz ± 10kHz)
ESR (100kHz ± 10kHz)

	[100kHz]
Z _{-25°C} / Z _{+20°C}	≤ 1.5
Z _{-55°C} / Z _{+20°C}	≤ 2.0
ESR _{-25°C} / ESR _{+20°C}	≤ 1.15
ESR _{-55°C} / ESR _{+20°C}	≤ 1.25

9 Reference standard

HXJ series is applicable to chip capacitors of JIS C 5101-18-2(1999).

The others test conditions shall comply with JIS C 5101-18-2 and JIS C 5101-1 1998.

10 Others

10.1 Export Trade Control Ordinance (To be complied for aluminum electrolytic capacitors be exported from Japan)

(1) Export Trade Control Ordinance (Section 1 through 15 of Appendix Table 1)

Export regulation of the capacitors for pulse use (750V or higher) and the capacitors for high voltage (5,000V or higher) is carried out according to (item 41-4) in Section 2 of Appendix Table 1 (Section 49 in Chapter 1 of METI's Ordinance) and (item 7) in Section 7 of Appendix Table 1 (Section 6 in Chapter 6 of METI's Ordinance). However, the aluminum electrolytic capacitors, which are described in this specification, don't fulfill the regulated level. Therefore, the aluminum electrolytic capacitors are not applicable to Export Trade Control Ordinance.

(2) Export Trade Control Ordinance (Section 16 of Appendix Table 1)

The aluminum electrolytic capacitors, which are described in this specification, applicable to goods under Export Regulations (Category 85 of Appendix Table in Customs Tariff Law) based on Section 16 of Appendix Table 1 in Export Trade Control Ordinance.

If the exporter got information that their exporting goods are used to any development of massive weapon, the exporter must apply for exporting permission to Ministry of Economy, Trade and Industry (METI), and get METI's approval. Regardless of the above, if the exporter is notified by METI that his/her exporting goods are potentially used to any development of extensive destructive weapons, the exporter must seek permission from METI to export, and get METI's approval. When Nippon Chemi-Con receives such notice from METI, we will inform your company of that.

10.2 Cleaning PC board

(1) Alcohol system

Higher alcohol system / Isopropyl alcohol cleaning agents

Recommended cleaning agents:

Pine Alpha ST-100S (Arakawa Chemical)

Clean Through 750H, 750K, 750L, and 710M (Kao)

Technocare FRW-14,15,16,17 (Momentive performance materials)

Cleaning conditions:

Using these cleaning agents, capacitors are capable of withstanding immersion or ultrasonic cleaning for 10 minutes at a maximum liquid temperature of 60°C . Find optimum conditions for washing, rinsing, and drying. Be sure not to rub off the marking of the capacitors by coming in contact with any other components or the PC board. Note that shower cleaning adversely affects the markings on the sleeve.

It is necessary to maintain a flux content in the cleaning liquid in of 2 Wt.% or less, and to control for alkaline components not to remain in the final cleaning process.

10.3 Manufacturing plant

CHEMI-CON EAST JAPAN CORPORATION MIYAGI PLANT (JAPAN)

10.4 For aluminum electrolytic capacitors, please refer to PRECAUTIONS AND GUIDELINES (Conductive Polymer hybrid).


11 Taping

11.1 Scope

This specification defines the taping requirements for aluminum electrolytic capacitors, complying with JIS C 0806-3(1999).

11.2 Taping dimensions and taping configurations

(1) Carrier tape




Carrier tape dimensions

[mm]


Size code	W ± 0.3	A ± 0.2	B ± 0.2	B' ± 0.2	F ± 0.1	P ± 0.1	t ± 0.2
JA0	24.0	10.7	10.7	11.9	11.5	16.0	11.0

(2) Edges of carrier tape and cover tape

The cover tape shall not extend more than 0.5mm beyond the edge of the carrier tape.




The cover tape shall not extend exceeding 0.75mm to the sprocket holes.



11.3 Taping method and polarity


(1) Polarity

The parts shall be so oriented that their positive polarity shall be the right side for the direction of unreeling. (Except for bi-polarized capacitors)




(2) Peeling strength of cover tape

- 1) Rupture strength of cover tape : 10N min.
- 2) Peeling strength of cover tape
 - ① Peeling angle : 165 to 180° to adhesive surface
 - ② Peel-off speed : 300 ± 10 mm/minute
 - ③ Peeling force : 0.1N to 1.3N




3) Other

When the cover tape is taken off and the carrier tape turned upside down, all of the parts shall fall out of the carrier tape.



(3) Taping method and marking

1) Taping method is shown below.




2) Marking of reel

The following marking shall be printed on the reel.

- ① Part Numbering System
- ② Lot No.
- ③ Manufacturer's name
- ④ Quantity


(4) Reel dimensions



To reel up the tape so that the parts can face the reel core.

Reel dimensions [mm]				
Size code	W	φ N min.	φ A max.	φ C ± 0.5
JA0	26	50	382	13

11.4 Packaging quantity and Packaging box



Quantity per reel/box

Size code	Quantity		
	pcs/reel	pcs/box	reel/box
JA0	500	1500	3

This may change according to a delivered quantity.

※ The dimensions may change according to the size of the reel.

11.5 Others

- (1) Missing parts shall be no more than 0.1% of the total packaging quantity.
- (2) Carrier tapes may be spliced and/or a part of cover tapes may be spliced with an adhesive tape, because of manufacturing reasons.

STANDARD RATINGS

WV [Vdc]	Cap [μ F]	Size code	tan δ Max.	LC [μ A] Max.	ESR [m Ω Max./20°C]	Rated ripple current [mA rms/125°C]	Part No.
				2minutes	100kHz	100kHz	
35	330	JA0	0.12	115	20	2800	HHXJ350ARA331MJA0G

PRECAUTIONS AND GUIDELINES (Conductive Polymer Hybrid)

Conductive Polymer Hybrid Aluminum Electrolytic Capacitors (Hereinafter called capacitor) that uses highly conductive polymer electrolytic materials and electrolyte. Please read the following in order to get the most out of your capacitor.

The circuits described as examples in the catalog and the "specifications" are featured in order to show the operations and usage of our products, however, this fact does not guarantee that the circuits are available to function in your equipment systems.

We are not in any case responsible for any failures or damage caused by the use of information contained herein.

You should examine our products, of which the characteristics are described in the "specifications" and other documents, and determine whether or not our products suit your requirements according to the specifications of your equipment systems. Therefore, you bear final responsibility regarding the use of our products.

Please make sure that you take appropriate safety measures such as use of redundant design and malfunction prevention measures in order to prevent fatal accidents and/or fires in the event any of our products malfunction.

[1] Device circuits design considerations

1) Confirm installation and operating requirements for the capacitors, then use them within the performance limits prescribed in this catalog or product specifications.

2) Polarity

Capacitors are polarized.

Never apply a reverse voltage or AC voltage. Connecting with wrong polarity will short-circuit or damage the capacitor with the pressure relief vent opening early on. To identify the polarity of a capacitor, see the relevant diagram in the catalogs or product specifications, or the polarity marking on the body of the capacitors.

3) Operating voltage

Do not apply an over-voltage that exceeds a rated voltage specified for the capacitors.

The total peak value of the ripple voltage plus the DC voltage must not exceed the rated voltage of the capacitors. Capacitors do not require voltage derating within the category temperature. Although capacitors specify a surge voltage that exceeds the full rated voltage, it does not assure long-term use but limited use under specific conditions.

4) Ripple current

Do not apply an over current that exceeds the rated ripple current specified for the capacitors. Excessive ripple current will increase heat production within the capacitors, causing the capacitors to be damaged as follows:

- Shorten lifetime
- Open pressure relief vent
- Short circuit

At the time of low DC bias voltage, reverse voltage may be applied if uses with less than rated ripple current. Please use it as far as the reverse voltage is not applied. The rated ripple current is specified along with a specific ripple frequency. When using the capacitors at any ripple frequency other than the specified frequency, calculate the allowable ripple current by multiplying the rated ripple current by a frequency compensation factor (Frequency Multiplier) specified for each product series.

5) Operating temperature (Category temperature)

Do not apply high temperatures that exceed the upper limit of the category temperature range specified for the capacitors.

Using the capacitors at temperatures higher than the upper limit will considerably shorten the lifetime of the capacitors and make the pressure relief vent open. The temperature, please confirm the temperature of the capacitors which included the ambient temperature of the device, not only the temperature in the device but also radiant heat of the heating element (power transistor, resistance) in the apparatus, self heating caused by the ripple current. Additionally, please do not place heating element on the back side of the capacitors. In addition, please use the capacitors within category temperature range because the life of the capacitors are affected by the operating temperature. In other words, lowering ambient temperatures will extend the expected lifetime of the capacitors.

6) Lifetime

Select the capacitors to meet the service life requirements of device.

7) Charging and discharging

Do not use capacitors in circuits intended for rapid charge and discharge cycle operations.

If capacitors are used in the circuits that repeat a charge and discharge with a large voltage drop or a rapid charge and discharge at short interval cycle, capacitance will decrease and/or the capacitors will be damaged by internal heat generation.

Please consult us the capacitors to use for the circuit where rapid charge and discharge is repeated.

Please be careful about rush currents. Recommend to install protective circuit.

8) Leakage current

The leakage current may increase due to thermal stress such as reflow soldering. After that, however, the leakage current will gradually decrease by self-healing action of the dielectric oxide layer when the capacitors are applied with a voltage less than the rated voltage within the Category Temperature range. As the voltage is closer to the rated voltage and the temperature is closer to the upper limit of Category Temperature range, the leakage current decreases faster.

The leakage current will increase by the following factors,

- ① Soldering
- ② Testing of high temperature exposure with no voltage applied, high temperature/humidity storage, temperature cycles, etc.

9) Failure mode of capacitors

Non-solid aluminum electrolytic capacitors have a limited lifetime which ends in an open circuit failure mode, in general. Depending on the product type and operating conditions, the failure mode may involve in opening of the pressure relief vent. But it may lead to short circuit mode failure when capacitor is used in the overload more than the guarantee ranges including over voltage and the over current.

10) Capacitor insulation

The can case of capacitor does not assure electrical insulation.

The outer coating on can case is aimed for indication and does not assure function of the electrical insulation.

Electrically isolate the outer can case of a capacitor from the negative terminal, the positive terminal and circuit patterns.

11) Operating conditions

Do not use/expose capacitors to the following conditions:

- ① Direct contact with water, salt water or oil, or high condensation environment.
- ② Direct sunlight
- ③ Toxic gases such as hydrogen sulfide, sulfurous acid, nitrous acid, chlorine and its compounds, bromine and its compounds and ammonium.
- ④ Ozone, ultraviolet rays or radiation.
- ⑤ Extreme vibration or mechanical shock that exceeds limits in the catalogs or product specifications.

The standard vibration condition is applicable to JIS C 5101-4.

12) Mounting

Capacitors contain paper separators and electric-conductive electrolyte that contains organic solvent as main solvent material, both of which are flammable. If the electrolyte leaks onto a printed circuit board, it can erode the device circuit pattern, may short-circuit the copper traces, smoke and burn. Make sure of designing a PC board as follows:

- ① Provide clearance space (2mm minimum) over the pressure relief vent of a capacitor to avoid blocking the correct opening of the pressure relief vent for 10mm case diameter of capacitor.
- ② Do not locate any wire or circuit pattern over the pressure relief vent of a capacitor.
- ③ Avoid locating any heat source components near capacitors or on the opposite side of the PC board under capacitors.
- ④ Design the solder land on the PC board in accordance with the catalog or the product specification.
- ⑤ Do not print any copper trace under the seal (terminal) side of a capacitor. When the electrolyte leaks out, it may occur circuit pattern short-circuit, and tracking or migration. Copper traces should be 1 mm (preferably 2mm or more) spaced apart from the side of the capacitor body.
- ⑥ In designing a double-sided PC board, do not locate any through-hole via or unnecessary hole underneath a capacitor.
- ⑦ In designing a double-sided PC board, do not print any circuit pattern underneath a capacitor.

13) Using capacitors for significantly safety-oriented applications

Consult with us in advance of usage of our products in the following listed applications. ① Aerospace equipment ② Power generation equipment such as thermal power, nuclear power etc. ③ Medical equipment ④ Transport equipment (automobiles, trains, ships, etc.) ⑤ Transportation control equipment ⑥ Disaster prevention / crime prevention equipment ⑦ Highly publicized information processing equipment ⑧ Submarine equipment ⑨ Other applications that are not considered general- purpose applications.

14) Others

Design device circuits taking into consideration the following conditions:

- ① Electrical characteristics of a capacitor depend on the temperature and frequency. In designing the device circuits, consider the change in the characteristics.
- ② If using more than one capacitor connected in parallel, design the device circuits to balance the current flow in individual capacitors.
- ③ If using more than one capacitor connected in series, connect shunting resistors in parallel with the individual capacitors to balance the voltage.

[2] Installation

1) Assembling

- ① Do not try to reuse the capacitors once assembled and electrified
- ② Capacitors may have been spontaneously recharged with time by a recovery voltage phenomenon.
Capacitors may produce recovery voltage higher than aluminum electrolytic capacitors and conductive polymer aluminum solid capacitors. In this case, discharge electricity through approximately 1k Ω before use.
- ③ If capacitors have been stored at any conditions more than 35° C and 75%RH for long storage periods of time more than the limits specified in the catalogs or product specifications, they may have high leakage current. In this case, make pre-conditioning by applying the rated voltage through a resistor of approximately 1k Ω .
- ④ Confirm the rated capacitance and voltage of capacitors before installation.
- ⑤ Confirm the polarity of capacitors before installation.
- ⑥ Do not try to use the capacitors that were dropped to the floor and so forth.
- ⑦ Do not deform the can case of a capacitor.
- ⑧ Do not apply excessive mechanical force to capacitors more than the limits prescribed in the catalogs or product specifications. Avoid excessive mechanical force while the capacitors are in the process of vacuum-picking, placing and positioning by automatic mounting machines or cutting the lead wires by automatic insertion machines.

2) Soldering and heat resistance

- ① For soldering using a soldering iron, consider the following conditions:

Soldering conditions (temperature and time) should be $(380 \pm 10^\circ \text{C}, 3 \pm 0.5\text{second})$.

Do not touch the body of a capacitor with the hot tip of the soldering iron.

- ② For reflow soldering, consider the following conditions:

Soldering conditions (preheat, reflow temperature and time) should be within the limits prescribed in the catalogs or product specifications.

- When using the infrared heater and setting its temperatures, adjust the heating levels taking into consideration that the color and materials of a capacitor vary in their infrared absorbance.
- The allowable number of reflow passes is specified in the catalogs or product specifications.
- Please consult us about vapor phase soldering (VPS).
- Flow soldering must not be used.

- ③ Do not try to reuse the capacitors once assembled.

3) Handling after soldering

After soldering the PC board, do not apply the following mechanical stress to the capacitor:

- ① Do not tilt, push down or twist the body of the capacitor.
- ② Do not grab the body of the capacitor to carry the assembly board.
- ③ Do not hit anything against the capacitor. When stacking the assembled boards, do not put any of the PC boards or other components against the capacitor.
- ④ Do not drop the assembled board.

4) Cleaning assembly boards

- ① Do not clean capacitors with the following cleaning agents:

- Halogenated solvents: cause capacitor failures due to corrosion.
- Alkali system solvents: corrode (dissolve) the aluminum can case.
- Terpene and petroleum system solvents: deteriorate the rubber seal materials.
- Xylene and toluene: deteriorates the rubber seal materials as well.
- Acetone: erases the markings printed on a capacitor.

Where cleaning is necessary, use only solvent resistant type capacitors that have been assured for the cleaning within the specific cleaning conditions prescribed in the catalogs or product specifications. In particular, carefully set up the conditions for ultrasonic cleaning system. Consult us regarding alternative CFCs or other cleaners before use.

- ② Where cleaning the capacitors, confirm the following conditions:

- Control the contamination (the conductivity, pH, specific gravity, water content, etc.) of the cleaning agents.
- After the cleaning, do not leave the capacitors (assembly boards) in an environment of cleaning agent-rich or in a closed container. Sufficiently evaporate the residual cleaning agent from the assembly boards and the capacitors by forced hot air at temperatures less than the upper limit of category temperature range for more than 10 minutes.

In general, aluminum electrolytic capacitors are sensitive to contamination of halogen ions (particularly to chlorine ions). Depending on the properties of the electrolyte and rubber seal materials used in a capacitor, the halogen ions lead up to catastrophic failures on the capacitor. Where the inside of a capacitor has been contaminated with more than a certain amount of halogen ions and the capacitor is in use, the corrosion reaction of aluminum occurs. The corrosion causes the capacitor to have a significant increase in leakage current with heat produced, open the pressure relief vent and become open circuit mode failure.

Due to global environmental issues (greenhouse effects and other environmental destruction by depletion of the ozone layer), the conventional cleaning solvents of CFC 113, Trichloroethylene and 1,1,1-trichloroethylene were replaced by substitutes.

The following are some substitute cleaning agents and allowable cleaning conditions:

a) Fatty-alcohol cleaning agents

Pine Alpha ST-100S (Arakawa Chemical)

Clean Through 750H, 750K, 750L and 710M (Kao)

Technocare FRW-14, 15, 16 and 17 (Momentive Performance Materials)

[Cleaning conditions]

Either of immersion or ultrasonic cleaning, for a maximum of 10 minutes and at a maximum liquid temperature of 60°C is acceptable.

Make sure that the markings on the capacitor are not rubbed against any other component or the PC board during cleaning. Note that shower cleaning affects the markings on the capacitor.

b) Alternative CFCs

AK225AES (Asahi Glass)

[Cleaning conditions]

Solvent resistant type capacitors, which were originally developed to intend to resist Freon TE or Freon TES, are also capable of withstanding any one of immersion, ultrasonic or vapor cleaning, for a maximum of 5 minutes.

However, this type of cleaning agent is not recommended to use, as the cleaning materials may be banned in near future in view of global environmental issues

c) IPA (Isopropyl Alcohol)

Immersion cleaning with a maximum flux concentration of 2 wt% is acceptable.

5) Adhesives and coating materials

- ① Do not use any adhesive or coating materials containing halogenated solvents.
- ② Make sure of the following conditions before applying adhesive or coating materials to a capacitor.
 - No flux residue nor stain is left between the rubber seal of a capacitor and PC board.
 - Dry the capacitor to remove residual cleaning agents before applying adhesive and coating materials. Do not cover up the entire surface of the rubber seal of the capacitor with adhesives or coating materials.
 - Consult us Heating and curing conditions for adhesives and coating materials.
 - Covering up the entire surface of the rubber seal with resin mold materials will obstruct the normal diffusion of internal hydrogen gas from a capacitor and result in serious failures.
Also, where the adhesive and coating materials contain a large amount of halogen ions, the halogen ions will contaminate the inside of the capacitor through the rubber seal materials, causing the capacitor to become a failure.
 - Depending on solvent materials that the adhesive or coating materials contains, note that the surface of a capacitor may change in appearance.

6) Fumigation

In exporting or importing electronic devices, they may be exposed to fumigation with halide such as methyl bromide.

Where the capacitors are exposed to halide such as methyl bromide, the capacitors will be damaged with the corrosion reaction with halogen ions in the same way as cleaning agents. For the export and import, Nippon Chemi-Con considers using some packaging method and so forth so that fumigation is not required. For customers to export or import electronic devices, semi-assembly products or capacitor components, confirm if they will be exposed to fumigation and also consider final condition of packaging. (Note that either cardboard or vinyl package has a risk of fumigation gas penetration.)

[3] Precautions during operation of devices

- 1) Never touch the terminals of a capacitor directly with bare hands.
- 2) Do not short-circuit between the capacitor terminals with anything conductive. Also, do not spill any conductive liquid such as acid or alkaline solution over a capacitor.
- 3) Confirm environmental conditions where the device will be placed. Do not use the device in the following environmental conditions:
 - ① Water or oil spatters, or high condensation environment.
 - ② Direct sunlight.
 - ③ Ozone, ultraviolet rays or radiation.
 - ④ Toxic gases such as hydrogen sulfide, sulfuric acid, nitrous acid, chlorine and its compounds, bromine and its compounds and ammonium.
 - ⑤ Extreme vibration or mechanical shock that exceeds the limits in the catalogs or product specifications.
The standard vibration condition is applicable to JIS C 5101-4.

[4] Maintenance inspections

- 1) For industrial use capacitors, make periodic inspections of the capacitors. Before the inspections, turn off the power supply of the device and discharge the electricity of the capacitors. When checking it by a volt-ohm meter, confirm the polarity beforehand. Do not apply mechanical stress to the terminals of the capacitors during inspection.
- 2) Characteristics to be inspected
 - ① Significant damage in appearance: vent opening, electrolyte leakage, etc.
 - ② Electrical characteristics: leakage current, capacitance, $\tan \delta$ and other characteristics prescribed in the catalogs or product specifications. If finding anything abnormal on the characteristics above, check the specifications of the capacitor and take appropriate actions such as replacement.

[5] Contingencies

- 1) A capacitor with more than a certain case size has the pressure relief vent functioning to escape abnormal gas pressure increase. If gas expels from a venting capacitor, disconnect the power supply of the device or unplug the power supply cord. If not disconnecting the power supply, the device circuit may be damaged due to the short circuit failure of the capacitor or short-circuited with the liquid that the gas was condensed to. It may cause secondary damages such as device burnout in the worst case scenario. The gas that comes out of the open vent is vaporized electrolyte not smoke.
- 2) The gas expelled from a venting capacitor is more than 100° C. Never expose your face to the capacitor. If your eyes are exposed to the gas or you inhale it, immediately flush your eyes and/or gargle with water. If the electrolyte comes in contact with the skin, wash with soap and water.

[6] Storage

- 1) Do not store capacitors at high temperature or high humidity.
Store the capacitors indoors at temperatures of 5 to 35° C and humidities of less than 75%RH.
In principle, aluminum electrolytic capacitors should be used within 2 years after production.
- 2) Keep capacitors packed in the original packaging material wherever possible.

3) Avoid the following storage environmental conditions:

- ① Water spattering, high temperatures, high humidity or condensation environment.
- ② Oil spattering or oil mist filled.
- ③ Salt water spattering or salt filled.
- ④ Acidic toxic gases such as hydrogen sulfide, sulfuric acid, nitrous acid, chlorine, bromine and methyl bromide filled.
- ⑤ Alkaline toxic gases such as ammonium filled.
- ⑥ Acid or alkaline solutions spattering.
- ⑦ Direct sunlight, ozone, ultraviolet rays or radiation.
- ⑧ Extreme vibration or shock loading.

4) JEDEC J-STD-020 is not applicable.

【7】 Capacitor disposal

Please consult with a local organization for the proper disposal of industrial waste. For incinerating capacitors, apply a high temperature incineration (over 800° C). Incinerating them at temperatures lower than that may produce toxic gases such as chlorine. To prevent capacitors from explosion, punch holes in or sufficiently crush the can cases of the capacitors, then incinerate.

【8】 About AEC-Q200

The Automotive Electronics Council (AEC) was originally established by major American automotive related manufactures. Today, the committees are composed of representatives from the sustaining Members of manufacturing companies in automotive electrical components. It has standardized the criteria for "stress test qualification" and "reliability tests" for electronic components.

AEC-Q200 is the reliability test standard for approval of passive components in Automotive applications. It specifies the test type, parameters and quantity, etc. for each component. The criteria of the reliability tests such as for our main products, "Aluminum Electrolytic Capacitors" are described in this standard.

Pursuant to the customer's specific testing requirements, Chemi-Con submits the test results according to AEC-Q200 for Aluminum Electrolytic Capacitors used in automotive applications on request.

An electronic component manufacturer cannot simply claim that their product is "AEC-Q200 Qualified". It can be claimed "Compliant", "Capable", "Available", etc., however each component must be tested per each users "Qualification Test Plan" in order to claim AEC-Q200 status.

Please contact us for more information.

【9】 Response to the Substances of Concern

1) Nippon Chemi-Con aims for developing products that meet laws and regulations concerning substances of concern.

(Some products may contain regulated substances for exempted application)

Please contact us for more information about law-compliance status.

2) According to the content of REACH handbook (Guidance on requirements for substances in articles which is published on May 2008), our electronic components are "articles without any intended release". Therefore they are not applicable for "Registration" for EU REACH Regulation Article 7 (1). Reference: Electrolytic Condenser Investigation Society "Study of REACH Regulation in EU about Electrolytic Capacitor" (publicized on 13 March 2008)

【10】 Safety Application Guide

For more details, refer to JEITA RCR-2367D (March 2019) with the title of "Safety Application Guide for fixed aluminum electrolytic capacitors for use in electronic equipment".