





REV.	ECN NO OR DESCRIPTION	REVISED	DATE



NOTE:

△ 材质与电镀规格见表;

2. 开关电路图

PIN 1	# C1:	VCC
PIN 2	# C5:	Grand
PIN 3	# C2:	Reset
PIN 4	# C6:	VPP
PIN 5	# C3:	Clock
PIN 6	# C7:	I/O



3. 特征:

- 3-1. 额定电流 :1A max.
- 3-2. 接触电阻 :50mOhms max
- 3-3. 绝缘电阻:100Mhms min./500VDC
- 3-4. 耐压: 500VAC/1minute
- 3-5. 插入力: 10N Max, 拔出力: 1N Min. ;
- 3-6. 耐久: 1500 Cycles
- 3-7. 工作温度:-25° C to+85° C

6	壳	SUS304	镀金0.8u"镀镍50u"
5	杆	SUS301	/
4	凸轮	SUS301	/
3	塑胶	LCP	黑色,UL94V-0
2	端子	C5191	接触区镀金3u"焊接区镀金0.8u"整体镀镍50u"
1	端子	C5191	接触区镀金3u"焊接区镀金0.8u"整体镀镍50u"
Item	零件名称	材质	电镀规格

Recommended PCB Layout  
Tolerance: ±0.05

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD	
DECIMALS:	ANGLES:	TITLE 1.5H NANO SIM Card CONN With Dctrct	
X :±0.30	X :±2°	DWN	xiong PART NO. SNO-1460
X.X :±0.20	X.X :±1°	CHKD	lee SCALE:1:1 UNIT: mm
X.XX :±0.10		APVD	wang SIZE: A4 SHEET:10F 1
		REV: A4	
CUSTOMER COPY			