


High Current Chip Perforation Bead

◆ PRODUCT IDENTIFICATION

SBH 1155 S 601 N T T
(1) (2) (3) (4) (5) (6) (7)

- 1: Series Type
- 2: Chip Size (mm): Length X Width
- 3: Material Code
- 4: Nominal Impedance: 600=60 Ω ; 601=600 Ω ;
- 5: Impedance Tolerance: N= $\pm 25\%$
- 6: Company Code
- 7: Packaging: Tape Carrier Package

◆ DIMENSION (: mm)





A	B	C	D	E
5.0 \pm 0.2	5.0 \pm 0.2	8.3 \pm 0.2	2.5 \pm 0.2	11.0 \pm 0.5

◆ ELECTRICAL SPECIFICATION

MEAS. ITEM	SPEC.				TEST FREQ.
Z	600	Ω	\pm	25%	100MHZ/0.25V
RDC	0.012	Ω	Max.		VR3302 LCR Meter
IDC	6000	mA	Max.		VR712 VR1133H
TEMPERATURE	15°C	35°C			
HUMIDITY	25%	85%	RH		

● HP 4191A MILLIOHMETER

◆ PACKAGING INFORMATION


Part No.	D	P	A0	B0	Packing Quantity
SBH1155S601NTT	24±0.3	12±0.1	7.0±0.3	12.5±0.3	1000PCS/R