



ITEM	XRRH 3.5*9.0*0.8TAPING
PART NO.	
ELECTRICAL REQUIREMENTS	IMPEDANCE Z:90 MIN OHM(100MHZ)

TEST MEHOD

APPEARANCE STANDARD	VISION
INSPECTION LEVEL	MIL-SID-105D AQL=0.1
CHARACT&SIZE	LEVEL S-3
SURFACE	LEVEL II
TEST EQUIPMENT	HP-4191A
TEST FREQUENCY	100MHZ
COIL SPEC	

DIMENSION

(UNIT:mm)



$$A=3.50 \pm 0.20\text{m/m}$$

$$C=0.80 \pm 0.20\text{m/m}$$

$$D=9.00 \pm 0.20\text{m/m}$$



ITEM	XRRH 3.5*9.0*0.8TAPING
PART NO.	

PACKAGING

Available in tape and reel bulk


TAPE DIMENSION:

TYPE	B	E	F	H	I	J	P	d1-d2
XRRH3.5*9.0* 0.8	63.00	6.00	52.2	4.20	1.35	0.80	5.00	1.20
	±3.00	±0.50	±1.50	MIN	MAX	MAX	±0.50	MAX




TEST DATA

CUSTOMER				QUANTITY					
ITEM	XRRH 3.5*9.0*0.8 TAPING			COIL SPEC					
PART NO.				TEST FREQUENCY	100MHZ				
HUMIDITY	63%			TEST EQUIPMENT	HP-4191A				
TEMPERATURE	23°C								
	TESTRESOLUTION			DIMENSION(UNIT:mm)					
	Z MHZ	Z1 MHZ	Z2 100MHZ	A	B	C	D	E	F
SPEC	Ω MIN	Ω MIN	90 Ω MIN	3.50 ±0.20		0.80 ± 0.20	9.00 ±0.20		
1			144.6	3.48		0.80	8.97		
2			149.6	3.49		0.85	8.99		
3			145.9	3.49		0.88	8.99		
4			147.1	3.49		0.90	8.98		
5			150.4	3.48		0.98	8.98		
6									
7									
8									
9									
10									
MEAN			147.5	3.49			8.98		
R			5.8	0.01			0.02		



ITEM: XRRH 3.5*9.0*0.8TAPING



METER: HP-4191A