

HIGH-SIDE AND LOW-SIDE GATE DRIVER IN SO-14 (Type TH)

Description

The DGD21814 is a high-voltage/high-speed gate driver capable of driving N-Channel MOSFETs and IGBTs in a half-bridge configuration. High-voltage processing techniques enable the DGD21814's high-side to switch to 600V in a bootstrap operation.

The DGD21814 logic inputs are compatible with standard TTL and CMOS levels (down to 3.3V) for easy interfacing with controlling devices. The driver outputs feature high pulse current buffers designed for minimum driver cross conduction.

The DGD21814 is offered in SO-14 package and the operating temperature extends from -40°C to +125°C.

но

Vв

Vs

сом

Typical Configuration

DGD21814

Applications

- DC-DC Converters
- DC-AC Inverters
- AC-DC Power Supplies
- Motor Controls
- Class D Power Amplifiers

V_{cc} o

HIN o

LIN o

Features

- Floating High-side Driver in Bootstrap Operation to 600V
- Drives Two N-Channel MOSFETs or IGBTs in a Half Bridge Configuration
- 1.9A Source / 2.3A Sink Output Current Capability
- Outputs Tolerant to Negative Transients
- Wide Low-side Gate Driver and Logic Supply: 10V to 20V
- Logic Input (HIN and LIN) 3.3V Capability
- Schmitt Triggered Logic Inputs with Internal Pull Down
- Undervoltage Lockout for High and Low Side Drivers
- Extended Temperature Range: -40°C to +125°C
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.
- https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Case: SO-14 (Type TH)
- Case Material: Molded Plastic. "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish—Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 ⁽³⁾
- Weight: 0.142 grams (Approximate)



Top View

Ordering Information (Note 4)

HIN

LIN

Vss

Part Number	Marking	Reel Size (inches)	Tape Width (mm)	Quantity Per Reel
DGD21814S14-13	DGD21814	13	16	2500

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/


Up to 600

Ţ

TO LOA

Marking Information


Notes:



)'' = Manufacturer's marking
DGD21814 = Product Type Marking Code
YY = Year (ex: 19 = 2019)
WW = Week (01 to 53)




Pin Diagrams



Pin Descriptions

Pin Number	Pin Name	Function
1	HIN	Logic input for high-side gate driver output, in phase with HO
2	LIN	Logic input for low-side gate driver output, in phase with LO
3	Vss	Logic ground
4, 8, 9, 10, 14	NC	No connection (No Internal Connection)
5	COM	Low-side and logic return
6	LO	Low-side gate drive output
7	Vcc	Low-side and logic fixed supply
11	Vs	High-side floating supply return
12	HO	High-side gate drive output
13	VB	High-side floating supply

Functional Block Diagram





Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
High-side Floating Supply Voltage	VB	-0.3 to +624	V	
High-side Floating Supply Offset Voltage	Vs	V _B -24 to V _B +0.3	V	
High-side Floating Output Voltage	V _{HO}	V _S -0.3 to V _B +0.3	V	
Offset Supply Voltage Transient	dV _S / dt	50	V/ns	
Low-side Fixed Supply Voltage	V _{CC}	-0.3 to +24	V	
Logic Supply Offset Voltage	V _{SS}	V _{CC} -24 to V _{CC} +0.3	V	
Low-side Output Voltage	V _{LO}	-0.3 to V _{CC} +0.3	V	
Logic Input Voltage (HIN and LIN)	VIN	-0.3 to V _{CC} +0.3	V	

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation Linear Derating Factor (Note 5)	PD	1.0	W
Thermal Resistance, Junction to Ambient (Note 5)	R _{eja}	120	°C/W
Operating Temperature	TJ	+150	
Lead Temperature (Soldering, 10s)	TL	+300	°C
Storage Temperature Range	T _{STG}	-55 to +150	

Note: 5. When mounted on a standard JEDEC 2-layer FR-4 board.

Recommended Operating Conditions

Parameter	Symbol	Min	Max	Unit
High Side Floating Supply Absolute Voltage	VB	V _S + 10	V _S + 20	V
High Side Floating Supply Offset Voltage	Vs	(Note 6)	600	V
High Side Floating Output Voltage	Vно	Vs	VB	V
Low Side Fixed Supply Voltage	Vcc	10	20	V
Low Side Output Voltage	VLO	0	Vcc	V
Logic Input Voltage (HIN and LIN)	Vin	0	Vcc	V
Logic Ground	Vss	-5	5	V
Ambient Temperature	T _A	-40	+125	°C

Note: 6. Logic operation for V_S of -5V to +600V.





DC Electrical Characteristics (V_{BIAS} (V_{CC}, V_{BS}) = 15V, @T_A = +25°C, unless otherwise specified.) (Note 7)

Parameter	Symbol	Min	Тур	Max	Unit	Conditions
Logic "1" Input Voltage (Note 8)	VIH	2.5	_	_	V	V _{CC} = 10V to 20V
Logic "0" Input Voltage (Note 8)	VIL	—	—	0.8	V	V _{CC} = 10V to 20V
High Level Output Voltage, V _{BIAS} - V _O	V _{OH}	—	—	1.4	V	I _O = 0mA
Low Level Output Voltage, V _O	Vol	—	—	0.2	V	I _O = 20mA
Offset Supply Leakage Current	I _{LK}	—	—	50	μA	$V_{B} = V_{S} = 600V$
Quiescent V _{BS} Supply Current	I _{BSQ}	20	60	150	μA	V _{IN} = 0V or 5V
Quiescent V _{CC} Supply Current	Iccq	50	120	240	μA	VIN = 0V or 5V
Logic "1" Input Bias Current	I _{IN+}	—	25	60	μA	V _{IN} = 5V
Logic "0" Input Bias Current	I _{IN-}	—	—	5.0	μA	V _{IN} = 0V
V _{BS} Supply Undervoltage Positive Going Threshold	V _{BSUV+}	8.0	8.9	9.8	V	
V _{BS} Supply Undervoltage Negative Going Threshold	V _{BSUV-}	7.4	8.2	9.0	V	<u> </u>
V _{CC} Supply Undervoltage Positive Going Threshold	V _{CCUV+}	8.0	8.9	9.8	V	—
V _{CC} Supply Undervoltage Negative Going Threshold	V _{CCUV-}	7.4	8.2	9.0	V	-
Output High Short Circuit Pulsed Current	I _{O+}	1.4	1.9	—	A	Vo = 0V, PW ≤ 10µs
Output Low Short Circuit Pulsed Current	I _{O-}	1.8	2.3		A	V _O = 15V, PW ≤ 10µs

Note: 7. The V_{IN} and I_{IN} parameters are applicable to the two logic input pins: HIN and LIN. The V₀ and I₀ parameters are applicable to the respective output pins: HO and LO.

8. For optimal operation, it is recommended that the input pulses (HIN and LIN) should have a minimum amplitude of 2.5V with a minimum pulse width of 360ns.


AC Electrical Characteristics (V_{BIAS} (V_{CC}, V_{BS}) = 15V, C_L = 1,000pF, @T_A = +25°C, unless otherwise specified.)

Parameter	Symbol	Min	Тур	Max	Unit	Conditions
Turn-on Propagation Delay	t _{ON}		180	270	ns	$V_{\rm S} = 0V$
Turn-off Propagation Delay	toff	+	220	330	ns	V _S = 0V or 600V
Delay Matching, HO & LO Turn-on/off	t _{DM}			35	ns	—
Turn-on Rise Time	tr		40	60	ns	$V_{\rm S} = 0V$
Turn-off Fall Time	tr		20	35	ns	$V_{\rm S} = 0V$





Timing Waveforms






Figure 1. Input / Output Timing Diagram

Figure 2. Delay Matching Waveform Definitions




Figure 3. Switching Time Waveform Definitions



Typical Performance Characteristics (Vcc=15V, @T_A = +25°C, unless otherwise specified.)




Figure 4. Turn-on Propagation Delay vs. Supply Voltage





Figure 6. Turn-off Propagation Delay vs. Supply Voltage



150 140 Turn On Propagation Delay (ns) 130 120 110 100 90 80 ton High Side 70 ton Low Side 60 50 -20 -40 0 20 40 60 80 100 120

Temperature (°C)

Figure 5. Turn-on Propagation Delay vs. Temperature






Figure 7. Turn-off Propagation Delay vs. Temperature






Typical Performance Characteristics (Cont.)






Typical Performance Characteristics (Cont.)




DGD21814 Document number: DS38329 Rev. 4 - 3



Typical Performance Characteristics (Cont.)












Figure 26. Offset Supply Leakage Current vs. Temperature





Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.





IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or

- 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com