
SCLS507 - JUNE 2003

- Controlled Baseline
 - One Assembly/Test Site, One Fabrication Site
- Extended Temperature Performance of -55°C to 125°C
- Enhanced Diminishing Manufacturing Sources (DMS) Support
- Enhanced Product-Change Notification
- Qualification Pedigree[†]
- Inputs Are TTL-Voltage Compatible

† Component qualification in accordance with JEDEC and industry standards to ensure reliable operation over an extended temperature range. This includes, but is not limited to, Highly Accelerated Stress Test (HAST) or biased 85/85, temperature cycle, autoclave or unbiased HAST, electromigration, bond intermetallic life, and mold compound life. Such qualification testing should not be viewed as justifying use of this component beyond specified performance and environmental limits.

- Latch-Up Performance Exceeds 250 mA Per JESD 17
- ESD Protection Exceeds JESD 22
 - 2000-V Human-Body Model (A114-A)
 - 200-V Machine Model (A115-A)

D OR PW PACKAGE (TOP VIEW)



description/ordering information

The 'AHCT00 device performs the Boolean function $Y = \overline{A \bullet B}$ or $Y = \overline{A} + \overline{B}$ in positive logic.

ORDERING INFORMATION

| TA | PACKA | ORDERABLE PART NUMBER | TOP-SIDE MARKING | |
|----------------|------------|--------------------------|---------------------|-----------|
| -55°C to 125°C | SOIC - D | Tape and reel | SN74AHCT00MDREP | AHCT00MEP |
| | TSSOP – PW | Tape and reel | SN74AHCT00MPWREP | AHT00EP |

[‡] Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

FUNCTION TABLE (each gate)

| INP | JTS | OUTPUT |
|-----|-----|--------|
| Α | В | Y |
| Н | Н | L |
| L | Χ | Н |
| X | L | Н |

logic diagram, each gate (positive logic)





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



SCLS507 - JUNE 2003

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

| Supply voltage range, V _{CC} | 0.5 V to 7 V |
|---|--------------------------------|
| Input voltage range, V _I (see Note 1) | 0.5 V to 7 V |
| Output voltage range, VO (see Note 1) | -0.5 V to V_{CC} + 0.5 V |
| Input clamp current, I_{IK} ($V_I < 0$) | –20 mA |
| Output clamp current, I _{OK} (V _O < 0 or V _O > V _{CC}) | ±20 mA |
| Continuous output current, I_O ($V_O = 0$ to V_{CC}) | ±25 mA |
| Continuous current through V _{CC} or GND | ±50 mA |
| Package thermal impedance, θ _{JA} (see Note 2): D package | 86°C/W |
| PW package | 113°C/W |
| Storage temperature range, T _{stg} | –65°C to 150°C |

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

recommended operating conditions (see Note 3)

| | | MIN | MAX | UNIT |
|----------------|------------------------------------|-----|-----|------|
| VCC | Supply voltage | 4.5 | 5.5 | V |
| VIH | High-level input voltage | 2 | | V |
| VIL | Low-level input voltage | | 0.8 | V |
| ٧ _I | Input voltage | 0 | 5.5 | V |
| VO | Output voltage | 0 | VCC | V |
| loh | High-level output current | | -8 | mA |
| loL | Low-level output current | | 8 | mA |
| Δt/Δν | Input transition rise or fall rate | | 20 | ns/V |
| TA | Operating free-air temperature | -55 | 125 | °C |

NOTE 3: All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| DADAMETER | TEGT COMPLETIONS | V | T, | ղ = 25°C | ; | SN74AHCT00-EP | | | |
|--------------------|---|--------------|------|----------|------|---------------|------|------|--|
| PARAMETER | TEST CONDITIONS | VCC | MIN | TYP | MAX | MIN | MAX | UNIT | |
| | I _{OH} = -50 μA | 45.1/ | 4.4 | 4.5 | | 4.4 | | V | |
| VOH | I _{OH} = -8 mA | 4.5 V | 3.94 | | | 3.8 | | V | |
| | I _{OL} = 50 μA | 451/ | | | 0.1 | | 0.1 | ., | |
| VOL | I _{OL} = 8 mA | 4.5 V | | | 0.36 | | 0.44 | V | |
| IĮ | V _I = 5.5 V or GND | 0 V to 5.5 V | | | ±0.1 | | ±1 | μΑ | |
| Icc | $V_I = V_{CC}$ or GND, $I_O = 0$ | 5.5 V | | | 2 | | 20 | μΑ | |
| Δl _{CC} ‡ | One input at 3.4 V, Other inputs at V _{CC} or GND | 5.5 V | | | 1.35 | | 1.5 | mA | |
| Ci | $V_I = V_{CC}$ or GND | 5 V | | 2 | 10 | | | pF | |

 $[\]ddagger$ This is the increase in supply current for each input at one of the specified TTL voltage levels, rather than 0 V or V_{CC}.



NOTES: 1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

^{2.} The package thermal impedance is calculated in accordance with JESD 51-7.

SCLS507 - JUNE 2003

switching characteristics over recommended operating free-air temperature range, V_{CC} = 5 V \pm 0.5 V (unless otherwise noted) (see Figure 1)

| | FROM | ТО | LOAD | T _A = 25°C | | | SN74AHC | | |
|------------------|----------|----------|------------------------|-----------------------|-----|-----|---------|-----|------|
| PARAMETER | (INPUT) | (OUTPUT) | CAPACITANCE | MIN | TYP | MAX | MIN | MAX | UNIT |
| ^t PLH | A = :: D | | 0 45 -5 | | 5 | 6.9 | 1 | 8 | |
| t _{PHL} | A or B | Υ | C _L = 15 pF | | 5 | 6.9 | 1 | 8 | ns |
| ^t PLH | A or B | V | C 50 pF | | 5.5 | 7.9 | 1 | 9 | 20 |
| t _{PHL} | AUID | T T | $C_L = 50 pF$ | | 5.5 | 7.9 | 1 | 9 | ns |

noise characteristics, V_{CC} = 5 V, C_L = 50 pF, T_A = 25°C (see Note 4)


| | PARAMETER | MIN | TYP | MAX | UNIT |
|---------------------|---|-----|------|------|------|
| V _{OL(P)} | Quiet output, maximum dynamic V _{OL} | | 0.4 | 0.8 | V |
| V _{OL(V)} | Quiet output, minimum dynamic V _{OL} | | -0.4 | -0.8 | V |
| VOH(V) | Quiet output, minimum dynamic VOH | | 4.5 | | V |
| V _{IH} (D) | High-level dynamic input voltage | 2 | | | V |
| V _{IL(D)} | Low-level dynamic input voltage | | | 0.8 | V |

NOTE 4: Characteristics are for surface-mount packages only.

operating characteristics, V_{CC} = 5 V, T_A = 25°C

| | PARAMETER | TEST CO | ONDITIONS | TYP | UNIT |
|-----------------|-------------------------------|----------|-----------|------|------|
| C _{pd} | Power dissipation capacitance | No load, | f = 1 MHz | 10.5 | pF |

PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_I includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- All input pulses are supplied by generators having the following characteristics: $PRR \le 1 \text{ MHz}$, $Z_O = 50 \Omega$, $t_f \le 3 \text{ ns}$, $t_f \le 3 \text{ ns}$.
- D. The outputs are measured one at a time with one input transition per measurement.
- E. All parameters and waveforms are not applicable to all devices.

Figure 1. Load Circuit and Voltage Waveforms





PACKAGE OPTION ADDENDUM

10-Dec-2020

PACKAGING INFORMATION

www.ti.com

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|------------|--------------|--------------------|------|----------------|--------------|-------------------------------|--------------------|--------------|----------------------|---------|
| | | | | | | | (6) | | | | |
| SN74AHCT00MDREP | ACTIVE | SOIC | D | 14 | 2500 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | AHCT00MEP | Samples |
| SN74AHCT00MPWREP | ACTIVE | TSSOP | PW | 14 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | AHT00EP | Samples |
| V62/03653-01XE | ACTIVE | TSSOP | PW | 14 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | AHT00EP | Samples |
| V62/03653-01YE | ACTIVE | SOIC | D | 14 | 2500 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -55 to 125 | AHCT00MEP | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



PACKAGE OPTION ADDENDUM

10-Dec-2020

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN74AHCT00-EP:

■ Catalog: SN74AHCT00

Military: SN54AHCT00

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Jun-2022

TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width |
|----|---|
| В0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| SN74AHCT00MDREP | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74AHCT00MPWREP | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Jun-2022



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AHCT00MDREP | SOIC | D | 14 | 2500 | 340.5 | 336.1 | 32.0 |
| SN74AHCT00MPWREP | TSSOP | PW | 14 | 2000 | 356.0 | 356.0 | 35.0 |

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated