

PAM8902H

30 VPP MONO CLASS-D AUDIO AMPLIFIER FOR PIEZO/CERAMIC SPEAKERS

PVCC

(A1)

OUT+

(в1)

OUT-

(01

PGND2

(D1

vou

VSET

PGND1

3

Δ

16 Ball CSP

Top View

sw

A3

COMP

B3

VCI

INN

(Da

View

20

P8902H

XXXYW

6 17

5

AVDD

: Pin 1 Indicator

PGND2

3

8

VCM AGND 12 ENA

11

10

9

GSET

INN

INP

QFN 4X4 16L

PGND1

(A4)

AVDD

84

AGND

(c4)

INP

D4

VOUT

A2)

VSET

В2

GSE

02

ENA

D2

Top

Pin Assignments

Description

The PAM8902H is a mono, Class-D audio amplifier with integrated boost Converter designed for piezo and ceramic speakers. The PAM8902H is capable of driving a ceramic/ piezo speaker with 30V_{PP} (10.6Vrms) from a 3.6V power supply. The PAM8902H's Boost converter operates at a fixed frequency of 1.5MHz, and provides a 17.5V supply with a minimum number of external components. The PAM8902H features an integrated audio low pass filter that rejects high frequency noise thus improving audio fidelity. And three gain modes of 21dB, 26dB and 32.5dB easy for using. The PAM8902H also provides thermal, short, under and over voltage protection.

The PAM8902H is available in a 16-ball 1.95mm x 1.95mm CSP package and 16-pin QFN4x4 package.

Features


- Supply Voltage Range from 2.5V to 5.5V
- 30 V_{PP} Output Load Voltage from a 2.5V Supply
- Integrated Boost Converter Generates 17.5V Supply
- Programmable Soft-Start
- Small Boost Converter Inductor
- Selectable Gain of 21dB, 26dB, and 32.5dB
- Selectable Boost Output Voltage of 8V, 12V, and 17.5V
- Low Shutdown Current: <1µA
- Built-In Thermal, OCP, OVP, Short Protection
- Available in Space Saving Packages:
 - 16-Ball 1.95mmx1.95mm CSP-16L Package
 - 16-Pin QFN4x4-16L Package

Applications

- Wireless or Cellular Handsets
- Portable DVD Player
- Personal Digital Assistants (PDAs)
- Electronic Dictionaries
- Digital Still Cameras



Typical Applications Circuit




Pin Descriptions

Pin Name	Bump (CSP-16L)	Pin Number (QFN4x4-16L)	Function		
PVCC	A1	16	Audio Amplifier Power Supply		
VOUT	A2	1	Boost Converter Output		
SW	A3	2	Boost Converter Switching Node		
PGND1	A4	4	Boost Converter Power Ground		
OUT+	B1	15	Positive Differential Audio Output		
VSET	B2	3	Boost Converter Output Voltage Setting (8V, 12V, 17.5V)		
COMP	B3	5	Boost Converter Compensation		
AVDD	B4	6	Power Supply		
OUT-	C1	14	Negative Differential Audio Output		
GSET	C2	11	Amplifier Gain Setting (21dB, 26dB, 32.5dB)		
VCM	C3	7	Common Mode Bypass Cap		
AGND	C4	8	Analog Ground		
PGND2	D1	13	Class D Power Ground		
ENA	D2	12	Whole Chip Enable		
INN	D3	10	Negative Differential Audio Input		
INP	D4	9	Positive Differential Audio Input		



Functional Block Diagram



Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

These are stress ratings only and functional operation is not implied. Exposure to absolute maximum ratings for prolonged time periods may affect device reliability. All voltages are with respect to ground.

Parameter	Rating	Unit
Supply Voltage	6.0	N .
Input Voltage	-0.3 to V _{DD} +0.3	V
Storage Temperature	-65 to +150	
Maximum Junction Temperature +150		°C
Soldering Temperature	+250, 10s	

Recommended Operating Conditions (@T_A = +25°C, unless otherwise specified.)

Parameter	Rating	Unit
Supply Voltage Range	2.5 to 5.5	V
Ambient Temperature Range	-40 to +85	*0
Junction Temperature Range	-40 to +125	U U



Thermal Information

Parameter	Symbol	Package	Maximum	Unit
Thermal Resistance (Junction to Ambient)	θ _{JA}	CSP-16L	90	°C/W
		QFN4x4-16L	52	C/W
Thermal Resistance	θυς	CSP-16L	72	°C/W
(Junction to Case)		QFN4x4-16L	30	C/W


Electrical Characteristics (@T_A = +25°C, V_{DD} = 3.6V, C_L = 1µF, V_{SET} Float, unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit	
V _{DD}	Input Voltage	—	2.5		5.5	V	
		V _{EN} > 1.2V, V _{SET} = High		30	48	-	
lq	Quiescent Current	V_{EN} > 1.2V, V_{SET} = Floating			18	mA	
		V _{EN} > 1.2V, V _{SET} = GND		5	12		
I _{SD}	Shutdown Current	V _{EN} = 0V	<u> </u>	0.1	1.0	μA	
twu	Wake-Up Time	V _{EN} From Low to High	—	40	—	ms	
V _{EH}	Chip Enable	-	1.2		- 1	V	
V _{EL}	Chip Disable	_	1		0.4	v	
V _H	GSET/VSET High	-	V _{DD} -0.5	—	V _{DD}		
VF	GSET/VSET Floating	-			V _{DD} -1	V	
VL	GSET/VSET Low	-	0	_	0.5		
UVLO	Under Voltage Lockout Threshold	V _{DD} From High to Low	—	2.2			
UVLO _H	Under Voltage Lockout Hysteresis	V _{DD} From Low to High	—	0.2	_	V	
OTP	Thermal Shutdown Threshold	-	_	+150	_	°C	
OTP _H	Thermal Shutdown Lockout Hysteresis		_	+30	_	°C	
Boost Con	verter		•	•	•		
V ₀ 1		V _{SET} = GND, No Load	7.2	8.0	8.8	V	
V ₀ 2	Output Voltage	V _{SET} = NC, No Load	10.8	12.0	13.2	V	
V _O 3		V _{SET} = AVDD, No Load	16	17.5	19	V	
CL	Current Limit	Average Input Current	_	1.0	_	А	
R _{LS}	Low Side MOSFET RDS(ON)	$I_0 = 50 \text{mA}$	_	0.5	_	Ω	
f _{OSCB}	Boost Switching Frequency		1.1	1.5	1.9	MHz	
Class-D			•	•	•		
f _{OSCD}	Class-D Amplifier Switching Frequency	Input AC-GND	225	375	475	kHz	
CMRR	Common Mode Reject Ratio	V _{IN} = ±100mV, V _{DD} = 3.6V	_	60	_	dB	
Vos	Output Offset Voltage	Output Offset Voltage	_	5	50	mV	
		High Side	—	1.5	_	Ω	
R _P	R _{DS(ON)}	Low Side	_	0.6		Ω	
A _V 1		G_{SET} = AVDD, V_{O} = 1 V_{RMS}	_	32.5	_		
Av2	Closed-Loop Voltage Gain	G _{SET} = AVDD, V _O = 1V _{RMS}	_	26	_	dB	
A _V 3		G _{SET} = AVDD, V _O = 1V _{RMS}	—	21	—		
PSRR	Power Supply Reject Ratio	200m V _{PP} Supply Ripple @ 217Hz	_	70	—	dB	
THD+N	Total Harmonious Distortion Plus Noise	V _O = 5V _{RMS}	—	0.3	—	%	
SNR	Signal to Noise Ratio	Input AC Ground, A-Weighting	_	90	_	dB	




Typical Operating Characteristics

(@T_A = +25°C, V_{DD} = 4.2V, Gain = 26dB, C_{IN} = 1 μ F, C_{LOAD} = 1 μ F, unless otherwise specified.)





Typical Operating Characteristics (continued) (@T_A = +25°C, V_{DD} = 5V, Gain = 18dB, unless otherwise specified.)





Application Information

Select Boost Converter Output Voltage

Customer can use V_{SET} pin to set boost converter output voltage between 8V, 12V and 17.5V. V_{SET} pin configuration table as below:

V _{SET} Pin Configuration	Min	Мах	PVCC Voltage	Audio Amplifier Maximum Output Voltage
Connect to AVDD	AVDD – 0.5V	AVDD	17.5V	11V _{RMS} (V _{PP} = 31.1V)
Floating	1V	AVDD – 1V	12V	5V _{RMS} (V _{PP} = 22.6V)
Connect to GND	GND	0.5V	8V	5V _{RMS} (V _{PP} = 14.1V)

Input Resistance (R_I)

The input resistors (RI = RIN + REX) set the gain of the amplifier according to Equation 1 when anti-saturation is inactive

G _{SET}	R _{IN}	R _F	
G _{SET} = V _{DD}	36.5kΩ	122.6kΩ	
G _{SET} = Floating	59kΩ	100kΩ	
G _{SET} = GND	82kΩ	77.4kΩ	

$G = 20 \text{ Log } [12.8 \text{ }^{*}\text{R}_{F}/(\text{R}_{IN} + \text{REX})] (dB)$

Where R_{IN} is a 77.4k Ω internal resistor, R_{EX} is the external input resistor, R_F is a 122.6k Ω internal resistor. Resistor matching is very important in fully differential amplifiers. The balance of the output on the reference voltage depends on matched ratios of the resistors. CMRR, PSRR, and cancellation of the second harmonic distortion diminish if resistor mismatch occurs. Therefore, it is recommended to use 1% tolerance resistors or better to keep the performance optimized. Matching is more important than overall tolerance. Resistor arrays with 1% matching can be used with a tolerance greater than 1%.

Place the input resistors very close to the PAM8902H to limit noise injection on the high-impedance nodes. For optimal performance the gain should be set to lower. Lower gain allows the PAM8902H to operate at its best, and keeps a high voltage at the input making the inputs less susceptible to noise. In addition to these features, higher value of R₁ minimizes pop noise.

Input Capacitors (C_I)

In the typical application, an input capacitor, C_I , is required to allow the amplifier to bias the input signal to the proper DC level for optimum operation. In this case, C_I and the minimum input impedance R_I form is a high-pass filter with the corner frequency determined in the follow equation:

$$f_{\rm C} = \frac{1}{2\pi R_{\rm I} C_{\rm I}}$$

It is important to consider the value of C_I as it directly affects the low frequency performance of the circuit. For example, when R_I is 150k Ω and the specification calls for a flat bass response are down to 150Hz. Equation is reconfigured as followed:

$$C_{I} = \frac{1}{2\pi R_{IFC}}$$

When input resistance variation is considered, the C_I is 7nF, so one would likely choose a value of 10nF. A further consideration for this capacitor is the leakage path from the input source through the input network (C_I , $R_I + R_F$) to the load. This leakage current creates a DC offset voltage at the input to the amplifier that reduces useful headroom, especially in high gain applications. For this reason, a low-leakage tantalum or ceramic capacitor is the best choice. When polarized capacitors are used, the positive side of the capacitor should face the amplifier input in most applications as the DC level is held at $V_{DD}/2$, which is likely higher than the source DC level. Please note that it is important to confirm the capacitor polarity in the application.



Application Information (continued)

Decoupling Capacitor

The PAM8902H is a high-performance CMOS audio amplifier that requires adequate power supply decoupling to ensure the output Total Harmonic Distortion (THD) as low as possible.

The optimum decoupling is achieved by using two different types of capacitors that target on different types of noise on the power supply leads. For higher frequency transients, spikes or digital hash on the line, a good low Equivalent Series-Resistance (ESR) ceramic capacitor, typically 1μ F, is placed as close as possible to the device AVDD pin for the best operation. For filtering lower frequency noise signals, a large ceramic capacitor of 10μ F or greater placed near the AVDD supply trace is recommended.

External Schottky Diode

Use external Schottky diode can get the best driving capability and efficiency. Since internal power diode has limited driving capability, only in following conditions customer can remove the external Schottky diode to reduce the cost.

- 1. V_{SET} = GND or Floating and C_L less than $1\mu F.$
- 2. The signal frequency less than 4kHz.
- 3. Haptic application (50 to 500Hz)

Shutdown Operation

In order to reduce power consumption while not in use, the PAM8902H contains shutdown circuitry amplifier off when a logic low is placed on the ENA pin. By switching the ENA pin connected to GND, the PAM8902H supply current draw will be minimized in idle mode.

Under Voltage Lock-Out (UVLO)

The PAM8902H incorporates circuitry designed to detect supply voltage. When the supply voltage drops to 2.2V or below, the PAM8902H goes into a state of shutdown, and the device comes out of its shutdown state and restore to normal function only when reset the power supply or ENA pin.

Short Circuit Protection (SCP)

The PAM8902H has short circuit protection circuitry on the outputs to prevent the device from damage when output-to-output shorted or output-to-GND shorted occurs. When a short circuit occurs, the device goes into a latch state and must be reset by cycling the voltage on the ENA pin to a logic low and then back to the logic high state for normal operation. This will clear the short-circuit flag and allow for normal operation if the short was removed. If the short was not removed, the protection circuitry will again activate.


Over Temperature Protection (OTP)

Thermal protection on the PAM8902H prevents the device from damage when the internal die temperature exceeds +150°C. There is a +15°C tolerance on this trip point from device to device. Once the die temperature exceeds the set point, the device will enter the shutdown state and the outputs are disabled, in this condition both OUT+ and OUT- will become high impedance. This is not a latched fault. The thermal fault is cleared once the temperature of the die decreased by +30°C. This large hysteresis will prevent motor boating sound well and the device begins normal operation at this point with no external system interaction.






Ordering Information





Package Outline Dimensions (All dimensions in mm.)


CSP-16L





Package Outline Dimensions (All dimensions in mm.)

QFN4x4-16L





IMPORTANT NOTICE

1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (<u>https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/</u>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com