

具有 7 位点校正 和 3 组，8 位全局亮度控制功能的 24 通道，12 位 PWM LED 驱动器

特性

- 24 通道恒定灌电流输出
- 电流功能
- 使用 PWM 的可选灰度 (GS) 控制：
12 位 (4096 步长)，10 位 (1024 步长)，8 位 (256 步长)
- 针对三色组的三个独立灰度时钟
- 点校正 (DC)：7 位 (128 步长)
- 针对每个颜色组的全局亮度控制 (BC)：8 位 (256 步长)
- 自动重复显示功能
- 针对 GS, BC 和 DC 数据的独立数据端口
- 每个数据端口间的通信路径
- LED 电源电压
- $V_{CC}=3.0V$ 至 $5.5V$
- 恒定电流精度：
 - 通道至通道
 - 器件到器件
- CMOS 逻辑电平 I/O
- 数据传输速率
- 灰度控制时钟
- 持续基座 LED 开路检测 (LOD)
- 持续基座 LED 短路检测 (LSD)
- 带有自动重新启动的热关断 (TSD)
- 成组延迟以防止涌入电流

应用范围

- 全色 LED 显示
- LED 信号板

说明

TLC5951 是一款 24 通道，恒定灌电流驱动器。每个通道具有一个独立可调节，4096 步长，脉宽调制 (PWM) 灰度 (GS) 亮度控制和 128 步长的恒定电流点校正 (DC)。此点校正调节通道和其它 LED 驱动器之间的亮度偏差。输出通道是被分成三组的 8 个通道。每个通道组有一个 256 步长全局亮度控制 (BC) 功能和一个独立的灰度时钟输出。

可通过一个串行接口访问 GS, DC 和 BC 数据。通过一个专用串行端口可对 DC 和 BC 进行编程。

TLC5951 有三个针对 LED 开路检测 (LOD)，LED 短路检测 (LSD) 和热错误标志 (TEF) 的错误检测电路。LOD 检测损坏或者断开的 LED，而 LSD 检测一个短接的 LED。TEF 表示一个过热条件。

ORDERING INFORMATION⁽¹⁾

PRODUCT	PACKAGE DESIGNATOR	PACKAGE	ORDERABLE PART NUMBER	PACKAGE QUANTITY
TLC5951	TD	Bare die in waffle pack ⁽²⁾	TLC5951TDA2	10
			TLC5951TDA3	96

(1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at www.ti.com.

(2) Processing is per the Texas Instruments commercial production baseline and is in compliance with the Texas Instruments Quality Control System in effect at the time of manufacture. Electrical screening consists of DC parametric and functional testing at room temperature only. Unless otherwise specified by Texas Instruments AC performance and performance over temperature is not warranted. Visual Inspection is performed in accordance with MIL-STD-883 Test Method 2010 Condition B at 75X minimum.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

BARE DIE INFORMATION

DIE THICKNESS	BACKSIDE FINISH	BACKSIDE POTENTIAL	BOND PAD METALLIZATION COMPOSITION	BOND PAD THICKNESS
11 mils.	Silicon with backgrind	Floating	TiW-AlCu (0.5%)	900 nm




Table 1. Bond Pad Coordinates in Microns⁽¹⁾

DESCRIPTION	PAD NUMBER	X MIN	Y MIN	X MAX	Y MAX
GSSIN	1	550.35	3842.64	634.41	3926.7
GSSCK	2	396.99	3842.64	481.05	3926.7
GSLAT	3	243.63	3842.64	327.69	3926.7
GSCKG	4	105.3	3704.31	189.36	3788.37
GSCKR	5	105.3	3565.17	189.36	3649.23
GSCKB	6	105.3	3392.55	189.36	3476.61
OUTG0	7	54	2531.43	138.06	2615.49
OUTR0	8	54	2312.91	138.06	2396.97
OUTB0	9	54	2094.39	138.06	2178.45
OUTG1	10	54	1875.87	138.06	1959.93
OUTR1	11	54	1657.35	138.06	1741.41
OUTB1	12	54	1438.83	138.06	1522.89
OUTG2	13	54	1220.31	138.06	1304.37
OUTR2	14	54	1001.79	138.06	1085.85
OUTB2	15	96.03	783.27	180.09	867.33
OUTG3	16	138.06	564.75	222.12	648.81
OUTR3	17	180.09	346.23	264.15	430.29
OUTB3	18	264.15	127.71	348.21	211.77
GSSOUT	19	1016.46	51.3	1100.52	135.36
DCSOUT	20	1509.48	51.3	1593.54	135.36
OUTB4	21	2261.79	127.71	2345.85	211.77
OUTR4	22	2345.85	346.23	2429.91	430.29
OUTG4	23	2387.88	564.75	2471.94	648.81
OUTB5	24	2429.91	783.27	2513.97	867.33
OUTR5	25	2471.94	1001.79	2556	1085.85
OUTG5	26	2471.94	1220.31	2556	1304.37
OUTB6	27	2471.94	1438.83	2556	1522.89
OUTR6	28	2471.94	1657.35	2556	1741.41
OUTG6	29	2471.94	1875.87	2556	1959.93
OUTB7	30	2471.94	2094.39	2556	2178.45
OUTR7	31	2471.94	2312.91	2556	2396.97
OUTG7	32	2471.94	2531.43	2556	2615.49
GND	33	2474.64	3152.43	2558.7	3236.49
GND	34	2474.64	3314.34	2558.7	3398.4
GND	35	2474.64	3510	2558.7	3594.06
IREF	36	2258.37	3842.64	2342.43	3926.7
VCC	37	2055.42	3842.64	2139.48	3926.7
XBLNK	38	1692	3842.64	1776.06	3926.7
DCSCK	39	1499.31	3842.64	1583.37	3926.7
DCSIN	40	1326.69	3842.64	1410.75	3926.7

 (1) Substrate V_{DD} .

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TLC5951TDA2	ACTIVE			0	10	RoHS & Green	Call TI	N / A for Pkg Type			Samples
TLC5951TDA3	ACTIVE			0	96	RoHS & Green	Call TI	N / A for Pkg Type			Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

重要声明和免责声明

TI 提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保或其他要求。这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 TI 的销售条款 (<https://www.ti.com.cn/zh-cn/legal/termsofsale.html>) 或 [ti.com.cn](https://www.ti.com.cn) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

邮寄地址：上海市浦东新区世纪大道 1568 号中建大厦 32 楼，邮政编码：200122

Copyright © 2021 德州仪器半导体技术（上海）有限公司