54ACT16623, 74ACT16623 **16-BIT BUS TRANSCEIVERS** WITH 3-STATE OUTPUTS SCAS152A - JANUARY 1991 - REVISED APRIL 1996

	00A0152	A - JAN	UART 1991 - REVI
<ul> <li>Members of the Texas Instruments Widebus<sup>™</sup> Family</li> </ul>	75ACT166		WD PACKAGE DL PACKAGE IFW)
<ul> <li>Inputs are TTL-Voltage Compatible</li> </ul>		(101 11	
<ul> <li>Flow-Through Architecture Optimizes PCB Layout</li> </ul>	10EAB [ 1B1 [	1 2	48 ] 10EBA 47 ] 1A1
<ul> <li>Distributed V<sub>CC</sub> and GND Pin Configuration Minimizes High-Speed Switching Noise</li> </ul>	1B2 [ GND [	3	46   1A2 45   GND
<ul> <li>EPIC<sup>™</sup> (Enhanced-Performance Implanted CMOS) 1-µm Process</li> </ul>	1B3 [ 1B4 [	5	44 ] 1A3 43 ] 1A4
<ul> <li>Package Options Include Plastic 300-mil Shrink Small-Outline (DL) Packages Using</li> <li>Specific Contex Dia Specific Contex Dia</li></ul>	V <sub>CC</sub> [ 1B5 [ 1B6 [	8	42 V <sub>CC</sub> 41 1A5 40 1A6
25-mil Center-to-Center Pin Spacings and 380-mil Fine-Pitch Ceramic Flat (WD) Packages Using 25-mil Center-to-Center	GND [ 1B7 [	10	39 GND 38 1A7
Pin Spacings	1B8 🛛	12	37 🛛 1A8
	2B1 🛛		36 2A1
description	2B2 🛛		35 2A2
The 'ACT16623 are 16-bit transceivers designed for asynchronous two-way communication between	GND [ 2B3 [	16	34 GND 33 2A3
data buses. The control-function implementation allows for maximum flexibility in timing.		18	32 2A4 31 V <sub>CC</sub>
These devices can be used as two 8-bit	2B5		30 2A5
transceivers or one 16-bit transceiver. They allow	2B6		29 2A6
data transmission from the A bus to the B bus or	GND 2B7		28 GND 27 247
from the B bus to the A bus, depending on the logic	2B7 L 2B8 [		26 2A7

The dual-enable configuration gives the bus transceiver the capability to store data by simultaneously enabling OEBA and OEAB. Each output reinforces its input in this transceiver configuration. When both control inputs are enabled and all other data sources to the two sets of bus lines are at high impedance, the bus lines remain at their last states.

The 74ACT16623 is packaged in TI's shrink small-outline package, which provides twice the functionality of standard small-outline packages in the same printed-circuit-board area.

The 54ACT16623 is characterized for operation over the full military temperature range of -55°C to 125°C. The 74ACT16623 is characterized for operation from -40°C to 85°C.



isolated.

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

EPIC and Widebus are trademarks of Texas Instruments Incorporated.

level at the output-enable (OEBA and OEAB)

inputs. The output-enable inputs can be used to disable the device so that the buses are effectively

UNLESS OTHERWISE NOTED this document contains PRODUCTION DATA information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters



Copyright © 1996, Texas Instruments Incorporated

25 20EBA

24

20EAB


# 54ACT16623, 74ACT16623 **16-BIT BUS TRANSCEIVERS** WITH 3-STATE OUTPUTS

SCAS152A - JANUARY 1991 - REVISED APRIL 1996

#### **FUNCTION TABLE** (each 8-bit section)

	(0000110	Sit Scotion)
INP	UTS	
OEBA	OEAB	OPERATION
L	L	B data to A bus
н	Н	A data to B bus
н	L	Isolation
L	Н	B data to A bus, A data to B bus


# logic symbol<sup>†</sup>




<sup>†</sup> This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.



### logic diagram (positive logic)





#### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

Supply voltage range, V <sub>CC</sub>	–0.5 V to 7 V
Input voltage range, VI (see Note 1)	. –0.5 V to V <sub>CC</sub> + 0.5 V
Output voltage range, V <sub>O</sub> (see Note 1)	-0.5 V to V <sub>CC</sub> + 0.5 V
Input clamp current, I <sub>IK</sub> (V <sub>I</sub> < 0 or V <sub>I</sub> > V <sub>CC</sub> )	±20 mA
Output clamp current, $I_{OK}$ ( $V_O < 0$ or $V_O > V_{CC}$ )	±50 mA
Continuous output current, $I_O (V_O = 0 \text{ to } V_{CC})$	±50 mA
Continuous current through V <sub>CC</sub> or GND	±400 mA
Maximum power package dissipation at $T_A = 55^{\circ}C$ (in still air) (see Note 2): DL package	age 1.2 W
Storage temperature range, T <sub>stg</sub>	–65°C to 150°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

2. The maximum package power dissipation is calculated using a junction temperature of 150°C and a board trace length of 750 mils.

### recommended operating conditions (see Note 3)

		54ACT16623		23	74	ACT1662	23	UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
VCC	Supply voltage (see Note 4)	4.5	5	5.5	4.5	5	5.5	V
VIH	High-level input voltage	2		EN	2			V
VIL	Low-level input voltage		EL	0.8			0.8	V
VI	Input voltage	0	à	VCC	0		VCC	V
Vo	Output voltage	0	5	VCC	0		VCC	V
ЮН	High-level output current	40	2	-24			-24	mA
IOL	Low-level output current	20	/	24			24	mA
$\Delta t/\Delta v$	Input transition rise or fall rate	0		10	0		10	ns/V
ТА	Operating free-air temperature	-55		125	-40		85	°C

NOTES: 3. Unused inputs should be connected to V<sub>CC</sub> through a pullup resistor of approximately 5 k $\Omega$  or greater.

4. All V<sub>CC</sub> and GND pins must be connected to the proper power supply.



# 54ACT16623, 74ACT16623 **16-BIT BUS TRANSCEIVERS** WITH 3-STATE OUTPUTS

SCAS152A - JANUARY 1991 - REVISED APRIL 1996

#### electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

DA	RAMETER	TEST CONDITIONS	Vee	T	<b>Α = 25°C</b>	;	54ACT	16623	74ACT	16623	UNIT	
		TEST CONDITIONS	Vcc	MIN	TYP	MAX	MIN	MAX	MIN	MAX	UNIT	
			4.5 V	4.4			4.4		4.4			
		I <sub>OH</sub> = -50 μA	5.5 V	5.4			5.4		5.4			
VOH		I <sub>OH</sub> = -24 mA	4.5 V	3.94			3.8		3.8		V	
		IOH = -24 INA	5.5 V	4.94			4.8		4.8			
		$I_{OH} = -75 \text{ mA}^{\dagger}$	5.5 V				3.85	2	3.85			
	I <sub>OL</sub> = 50 μA		4.5 V			0.1		0.1		0.1		
		$10L = 30 \mu\text{A}$	5.5 V			0.1		0.1		0.1	V	
VOL		a  = 24  mA	4.5 V			0.36	1	0.44		0.44		
		I <sub>OL</sub> = 24 mA	5.5 V			0.36	on No	0.44		0.44		
		$I_{OL} = 75 \text{ mA}^{\dagger}$	5.5 V				90	1.65		1.65		
Ц	Control inputs	$V_I = V_{CC}$ or GND	5.5 V			±0.1	49	±1		±1	μΑ	
I <sub>OZ</sub>	A or B ports	$V_{O} = V_{CC}$ or GND	5.5 V			±0.5		±5		±5	μA	
ICC	-	$V_{I} = V_{CC} \text{ or } GND, \qquad I_{O} = 0$	5.5 V			8		80		80	μΑ	
$\Delta I_{CC}^{\ddagger}$		One input at 3.4 V, Other inputs at V <sub>CC</sub> or GND	5.5 V			0.9		1		1	mA	
Ci	Control inputs	$V_{I} = V_{CC}$ or GND	5 V		4.5						pF	
Cio	A or B ports	$V_{O} = V_{CC}$ or GND	5 V		16						pF	

<sup>†</sup> Not more than one output should be tested at a time, and the duration of the test should not exceed 10 ms.

<sup>‡</sup> For I/O ports, the parameter IOZ includes the input leakage current.

# switching characteristics over recommended operating free-air temperature range, $V_{CC}$ = 5 V $\pm$ 0.5 V (unless otherwise noted) (see Figure 1)

PARAMETER	FROM	то	T <sub>A</sub> = 25°C			54ACT	16623	74ACT	UNIT	
PARAMETER	(INPUT)	(OUTPUT)	MIN	TYP	MAX	MIN	MAX	MIN	MAX	UNIT
<sup>t</sup> PLH	A or B	BorA	4.2	7.3	9.5	4.2	10.4	4.2	10.4	ns
<sup>t</sup> PHL	AUB	B or A	3.1	7.3	9.5	3.1	10.3	3.1	10.3	115
<sup>t</sup> PZH	OEBA	А	2.7	6.8	8.8	2.7	9.5	2.7	9.5	ns
<sup>t</sup> PZL	OEBA	A	3.5	8.2	10.2	3.5	×11.1	3.5	11.1	115
<sup>t</sup> PHZ	OEBA	٨	6	9.6	11.3	6	12	6	12	ns
<sup>t</sup> PLZ	OEBA	A	5.3	8.6	10.3	5.3	10.7	5.3	10.7	115
<sup>t</sup> PZH	OEAB	В	4.1	6.9	8.7	4.1	9.3	4.1	9.3	ns
<sup>t</sup> PZL	UEAB	В	5.1	7.9	9.7	<b>Q</b> 5.1	10.6	5.1	10.6	115
<sup>t</sup> PHZ	OEAB	В	5.1	8.2	10.2	5.1	10.4	5.1	10.4	ns
<sup>t</sup> PLZ		6	4.4	7.4	9.3	4.4	9.5	4.4	9.5	115


# operating characteristics, V<sub>CC</sub> = 5 V, T<sub>A</sub> = $25^{\circ}$ C

	PARAMETER	TEST CO	TYP	UNIT		
		Outputs enabled	C. 50 pF	f = 1 MHz	56	~ <b>F</b>
C <sub>pd</sub> Power dissipation capacitance per transceiver		Outputs disabled	C <sub>L</sub> = 50 pF,		11	рF

PRODUCT PREVIEW information concerns products in the formative or design phase of development. Characteristic data and other specifications are design goals. Texas Instruments reserves the right to change or discontinue these products without notice.



SCAS152A - JANUARY 1991 - REVISED APRIL 1996



#### PARAMETER MEASUREMENT INFORMATION

- NOTES: A. CL includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
  - C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  1 MHz, Z<sub>O</sub> = 50  $\Omega$ , t<sub>f</sub> = 3 ns, t<sub>f</sub> = 3 ns.
  - D. The outputs are measured one at a time with one input transition per measurement.

#### Figure 1. Load Circuit and Voltage Waveforms





10-Dec-2020

## PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
74ACT16623DL	ACTIVE	SSOP	DL	48	25	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	ACT16623	Samples
74ACT16623DLR	ACTIVE	SSOP	DL	48	1000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	ACT16623	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <= 1000ppm threshold. Antimony trioxide based flame retardants must also meet the <= 1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

# PACKAGE OPTION ADDENDUM

10-Dec-2020

# PACKAGE MATERIALS INFORMATION

Texas Instruments

www.ti.com

### TAPE AND REEL INFORMATION





# QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal	
-----------------------------	--


Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
74ACT16623DLR	SSOP	DL	48	1000	330.0	32.4	11.35	16.2	3.1	16.0	32.0	Q1



www.ti.com

# PACKAGE MATERIALS INFORMATION

5-Jan-2022



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
74ACT16623DLR	SSOP	DL	48	1000	367.0	367.0	55.0



www.ti.com

5-Jan-2022

### TUBE



#### \*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
74ACT16623DL	DL	SSOP	48	25	473.7	14.24	5110	7.87

### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated