SCAS332B - DECEMBER 1992 - REVISED MAY 1997

- Low Output Skew, Low Pulse Skew for Clock-Distribution and Clock-Generation Applications
- TTL-Compatible Inputs and Outputs
- Distributes One Clock Input to Eight Outputs
- Distributed V<sub>CC</sub> and Ground Pins Reduce Switching Noise
- High-Drive Outputs (-48-mA I<sub>OH</sub>, 48-mA I<sub>OI</sub> )
- State-of-the-Art EPIC-IIB™ BiCMOS Design Significantly Reduces Power Dissipation
- Package Options Include Plastic Small-Outline (DW) and Shrink

#### **DW PACKAGE** (TOP VIEW) 20 VCC Vcc [ 1G [ 19 1Y1 2 2G [] 3 18 ¶ 1Y2 17 GND ΑП Р0 П 16 1Y3 Р1 Г 15 1Y4 6 14 GND $v_{cc}$ 2Y4 **1** 8 13 2Y1 12 2Y2 2Y3 $\Pi$ 9 GND **1** 10 11 | GND

### description

The CDC340 is a high-performance clock-driver circuit that distributes one (A) input signal to eight (Y) outputs with minimum skew for clock distribution. Through the use of the control pins (1G and 2G), the outputs can be placed in a high state regardless of the A input.

The propagation delays are adjusted at the factory using the P0 and P1 pins. These pins are not intended for customer use and should be strapped to GND.

The CDC340 is characterized for operation from 0°C to 70°C.

**FUNCTION TABLE** 

	INPUTS		OUTPUTS				
1G	2G	Α	1Y1-1Y4	2Y1-2Y4			
Х	Х	L	Н	Н			
L	L	Н	Н	Н			
L	Н	Н	Н	L			
Н	L	Н	L	Н			
Н	Н	Н	L	L			




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

EPIC-IIB is a trademark of Texas Instruments Incorporated.




## logic symbol†



<sup>&</sup>lt;sup>†</sup> This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

## logic diagram (positive logic)





SCAS332B - DECEMBER 1992 - REVISED MAY 1997

### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

NOTES: 1. The input and output negative-voltage ratings may be exceeded if the input and output clamp-current ratings are observed.

### recommended operating conditions (see Note 3)

			MIN	MAX	UNIT
Vcc	Supply voltage	4.75	5.25	V	
VIH	High-level input voltage				V
VIL	Low-level input voltage				V
VI	Input voltage				V
ІОН	High-level output current				mA
l <sub>OL</sub>	Low-level output current				mA
4	Input alogk fraguency	One output back loaded		80	MHz
<sup>†</sup> clock	Input clock frequency  Both output banks loaded				IVITIZ
TA	Operating free-air temperature				°C

NOTE 3: Unused inputs must be held high or low to prevent them from floating.

# electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS					MIN	MAX	UNIT
PARAMETER	'	MIN	TYP‡	MAX	IVIIIN	IVIAA	UNIT		
VIK	$V_{CC} = 4.75 V$ ,	I <sub>I</sub> = -18 mA				-1.2		-1.2	V
	$V_{CC} = 4.75 V$ ,	$I_{OH} = -3 \text{ mA}$		2.5			2.5		
VOH	$V_{CC} = 5 V$ ,	$I_{OH} = -3 \text{ mA}$		3			3		V
	$V_{CC} = 4.75 V$ ,	$I_{OH} = -48 \text{ mA}$		2			2		
V <sub>OL</sub>	$V_{CC} = 4.75 V$ ,	$I_{OL} = 48 \text{ mA}$						0.5	V
lį	$V_{CC} = 5.25 \text{ V},$	$V_I = V_{CC}$ or GND				±1		±1	μΑ
ΙΟ <sup>§</sup>	$V_{CC} = 5.25 \text{ V},$	V <sub>O</sub> = 2.5 V		-50	-100	-200	-50	-200	mA
laa	V <sub>CC</sub> = 5.25 V,	l <sub>O</sub> = 0,	Outputs high		2			3.5	mA
lcc	$V_I = V_{CC}$ or GND		Outputs low		24			33	ША
Ci	V <sub>I</sub> = 2.5 V or 0.5 V				3				pF

<sup>‡</sup> All typical values are at  $V_{CC} = 5 \text{ V}$ .



<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

The maximum package power dissipation is calculated using a junction temperature of 150°C and a board trace length of 750 mils.
 For more information, refer to the Package Thermal Considerations Application Note in the ABT Advanced BiCMOS Technology Data Book, literature number SCBD002.

<sup>§</sup> No more than one output should be tested at a time, and the duration of the test should not exceed one second.

SCAS332B - DECEMBER 1992 - REVISED MAY 1997

# switching characteristics, $C_L = 50 \text{ pF}$ (see Figure 1 and Figure 2)

PARAMETER		FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub> = 5 V, T <sub>A</sub> = 25°C			V <sub>CC</sub> = 4.75 T <sub>A</sub> = 0°	UNIT	
		(INPUT)	(001701)	MIN	TYP	MAX	MIN	MAX	
tPLH	Propagation delay time, low-to-high level	Α	V	3.4		4.5	3	4.8	ns
t <sub>PHL</sub>	Propagation delay time, high-to-low level	^	'	3.2		4.3	2.8	4.7	115
<sup>t</sup> PLH	Propagation delay time, low-to-high level	G	V	2		3.8	2	4	no
t <sub>PHL</sub>	Propagation delay time, high-to-low level	G	ī	2		3.8	2	4	ns
tsk(o)	Skew time, output				0.3	0.5		0.6	
tsk(p)	Skew time, pulse	Α	Υ		0.6	0.8		0.9	ns
tsk(pr)	Skew time, process					1.1		1.1	
t <sub>r</sub>	Rise time	А	Υ					1.5	ns
tf	Fall time	А	Y					1.5	ns

# $t_{\mbox{\scriptsize pd}}$ performance information relative to $V_{\mbox{\scriptsize CC}}$ and temperature variation (see Note 4)


	PARAMETER	∆ change
∆t <sub>PLH(TA)</sub> †	Temperature drift of t <sub>PLH</sub> from 0°C to 70°C	−53 ps/10°C
∆t <sub>PHL(TA)</sub> †	Temperature drift of t <sub>PHL</sub> from 0°C to 70°C	−58 ps/10°C
∆tPLH(VCC) <sup>‡</sup>	V <sub>CC</sub> drift of t <sub>PLH</sub> from 4.75 V to 5.25 V	43 ps/100 mV
∆tPHL(VCC) <sup>‡</sup>	V <sub>CC</sub> drift of t <sub>PHL</sub> from 4.75 V to 5.25 V	-33 ps/100 mV

<sup>†</sup> Virtually independent of V<sub>CC</sub>


NOTE 4: The data extracted is from a wide range of characterization material.

<sup>‡</sup> Virtually independent of temperature

### PARAMETER MEASUREMENT INFORMATION




**LOAD CIRCUIT** 



NOTES: A.  $C_L$  includes probe and jig capacitance.

B. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_O = 50 \Omega$ ,  $t_f \leq$  2.5 ns,  $t_f \leq$  2.5 ns.

Figure 1. Load Circuit and Voltage Waveforms



NOTES: A. Output skew,  $t_{Sk(0)}$ , is calculated as the greater of:

- The difference between the fastest and slowest of tp<sub>LHn</sub> (n = 1, 2)
   The difference between the fastest and slowest of tp<sub>HLn</sub> (n = 1, 2)
- B. Pulse skew,  $t_{Sk(p)}$ , is calculated as the greater of  $|t_{PLHn} t_{PHLn}|$  (n = 1, 2).
- C. Process skew,  $t_{sk(pr)}$ , is calculated as the greater of:
  - The difference bétween the fastest and slowest of tpLHn (n = 1, 2) across multiple devices under identical operating conditions
  - The difference between the fastest and slowest of tpHLn (n = 1, 2) across multiple devices under identical operating conditions

Figure 2. Waveforms for Calculation of  $t_{sk(o)}$ ,  $t_{sk(p)}$ ,  $t_{sk(pr)}$ 





### PACKAGE OPTION ADDENDUM

10-Dec-2020

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
CDC340DW	ACTIVE	SOIC	DW	20	25	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	CDC340	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## PACKAGE MATERIALS INFORMATION

www.ti.com 5-Jan-2022

### **TUBE**



#### \*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
CDC340DW	DW	SOIC	20	25	507	12.83	5080	6.6

### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated