
www.vishay.com

MSE1PB, MSE1PD, MSE1PG, MSE1PJ

Vishay General Semiconductor

Surface-Mount ESD Capability Rectifier



MicroSMP (DO-219AD)



LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS					
I _{F(AV)}	1.0 A				
V _{RRM}	100 V, 200 V, 400 V, 600 V				
I _{FSM}	20 A				
V_F at $I_F = 1.0$ A	0.925 V				
I _R	1 µA				
T _J max.	175 °C				
Package	MicroSMP (DO-219AD)				
Circuit configuration	Single				

FEATURES

- Very low profile typical height of 0.65 mm
- Ideal for automated placement
- Oxide planar chip junction
- Low forward voltage drop, low leakage current
- ESD capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
 Automotive ordering code: base P/NHM3
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

General purpose, polarity protection, and rail-to-rail protection in both consumer and automotive applications.

MECHANICAL DATA

Case: MicroSMP (DO-219AD)

Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Base P/NHM3 - halogen-free, RoHS-compliant, and AEC-Q101 qualified

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 and HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes the cathode end

MAXIMUM RATINGS (T _A = 25 °C, unless otherwise noted)							
PARAMETER	SYMBOL	MSE1PB	MSE1PD	MSE1PG	MSE1PJ	UNIT	
Device marking code		SB	SD	SG	SJ		
Max. repetitive peak reverse voltage V _{RRM} 100 200 400		600	V				
Max. average forward rectified current (fig. 1)	I _{F(AV)}	1.0				А	
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	I _{FSM}	20			А		
Operating junction and storage temperature range	T _J , T _{STG}	-55 to +175				°C	





RoHS

COMPLIANT

HALOGEN

FREE





Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C, unless otherwise noted)							
PARAMETER	TEST C	TEST CONDITIONS		TYP.	MAX.	UNIT	
Max. instantaneous forward voltage	I _F = 0.5 A	- T _A = 25 °C	V _F (1)	0.940	-		
	I _F = 1.0 A	$I_{A} = 25 \text{ C}$		1.016	1.1	V	
	I _F = 0.5 A	T _A = 125 °C		0.834	-		
	I _F = 1.0 A	$I_{A} = 125 \text{ C}$		0.925	0.98		
Max. reverse current	Rated V _B	T _A = 25 °C	I _R ⁽²⁾	-	1.0	μA	
Max. reverse current	naleu v _R	T _A = 125 °C		3.7	50		
Typical reverse recovery time	I _F = 0.5 A, I _R	$I_F = 0.5 \text{ A}, I_R = 1.0 \text{ A}, I_{rr} = 0.25 \text{ A}$		780	-	ns	
Typical junction capacitance	4.0 V, 1 MHz	4.0 V, 1 MHz		5	-	pF	

Notes

⁽¹⁾ Pulse test: 300 µs pulse width, 1 % duty cycle

⁽²⁾ Pulse test: Pulse width \leq 40 ms

THERMAL CHARACTERISTICS ($T_A = 25 \text{ °C}$, unless otherwise noted)							
PARAMETER SYMBOL MSE1PB MSE1PD MSE1PG MSE1PJ				UNIT			
	R _{0JA} ⁽¹⁾	110				°C/W	
Typical thermal resistance	R _{0JL} ⁽¹⁾						
	R _{0JC} ⁽¹⁾	40					

Note

⁽¹⁾ Thermal resistance from junction to ambient and junction to lead mounted on PCB with 6.0 mm x 6.0 mm copper pad areas. R_{0,JL} is measured at the terminal of cathode band.

IMMUNITY TO ELECTRICAL STATIC DISCHARGE TO THE FOLLOWING STANDARDS ($T_A = 25$ °C, unless otherwise noted)							
STANDARD	TEST TYPE	TEST CONDITIONS	SYMBOL	CLASS	VALUE		
AEC-Q101-001	Human body model (contact mode)	C = 100 pF, R = 1.5 k Ω		H3B	> 8 kV		
AEC-Q101-002	Machine model (contact mode)	C = 200 pF, R = 0 Ω		M4	> 400 V		
JESD22-A114	Human body model (contact mode)	C = 100 pF, R = 1.5 k Ω	V	3B	> 8 kV		
JESD22-A115	Machine model (contact mode)	C = 200 pF, R = 0 Ω	V _C	С	> 400 V		
IEC 61000-4-2 ⁽²⁾	Human body model (contact mode)	C = 150 pF, R = 330 Ω		4	> 8 kV		
IEC 01000-4-2 (=)	Human body model (air-discharge mode) ⁽¹⁾	C = 150 pF, R = 330 Ω		4	> 15 kV		

Notes

(1) Immunity to IEC 61000-4-2 air discharge mode has a typical performance > 30 kV

⁽²⁾ System ESD standard

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
MSE1PJ-M3/89A	0.006	89A	4500	7" diameter plastic tape and reel		
MSE1PJHM3/89A (1)	0.006	89A	4500	7" diameter plastic tape and reel		
MSE1PGHM3/I ⁽¹⁾	0.006	I	16 000	13" diameter plastic tape and reel		

Note

(1) AEC-Q101 qualified



MSE1PB, MSE1PD, MSE1PG, MSE1PJ

Vishay General Semiconductor

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve






Fig. 2 - Forward Power Loss Characteristics








Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 5 - Typical Junction Capacitance




Fig. 6 - Typical Transient Thermal Impedance

Revision: 06-Aug-2020

3

Document Number: 89067


For technical questions within your region: DiodesAmericas@vishay.com, Diode sia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



MSE1PB, MSE1PD, MSE1PG, MSE1PJ

Vishay General Semiconductor

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



Revision: 06-Aug-2020 Document Number: 89067 4 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.