











OPA846-DIE

ZHCSBV4A - DECEMBER 2013 - REVISED MARCH 2017

OPA846-DIE 宽带、低噪声、电压反馈运算放大器

1 特性

- 高帯宽
- 低输入电压噪声
- 极低失真
- 高转换率
- 高直流精度
- 低电源电流
- 高增益带宽积

2 应用

- 高动态范围 ADC 前置放大器
- 低噪声、宽带、互阻抗放大器
- 宽带、高增益放大器
- 低噪声差动接收器
- VDSL 线路接收器
- 超声通道放大器
- 安全传感器前端

3 说明

OPA846-DIE 兼具极高增益带宽和大信号性能以及极低输入电压噪声,且耗散较低的电源电流。经典的差分输入级以及两个正向增益级和一个高功率输出级相结合,使得 OPA846-DIE 成为具有出色直流精度和输出驱动能力的优质低失真放大器。借助电压反馈架构,所有标准运算放大器 应用 应用都能实现非常高的性能。

低输入电压和电流噪声以及增益带宽相结合,使得 OPA846 成为适合宽带互阻抗级的理想放大器。

可使用一项全新的外部补偿技术来为 OPA846-DIE 提供一个低于最小稳定增益的十分平坦的频率响应,从而进一步改进其已经十分出色的失真性能。

订购信息(1)

产品	封装 标识符	封装	可订购部件号	封装数量	
OPA846	TD	TD 裸片采用叠片封装 ⁽²⁾ OPA846TDB1	300		
	טו	株月木用堂月到表 **/	OPA846TDB2	10	

1) 要获得最新的封装和订购信息,请参阅本文档末尾的封装选项附录,或者浏览 TI 网站 www.ti.com。

4 修订历史记录

Changes from Original (December 2013) to Revision A Page • Added designator to diagram in Bare Die Information section 2 • Added note after diagram in Bare Die Information section regarding added designator 2 • Changed description for pad number 5 and 6 in the Bond Pad Coordinates in Microns table 2

⁽²⁾ 加工过程遵循德州仪器 (TI) 商业生产基本规范,制造过程符合德州仪器 (TI) 质量控制系统的实际要求。电气筛选仅包括室温下的直流参数和功能测试。除非德州仪器 (TI) 另有说明,否则不对交流性能和过热性能进行保证。在最少 75 倍的放大倍数下,按照 MIL-STD-883 测试方法 2010 条件 B 执行目视检查。






This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

5 Bare Die Information

DIE THICKNESS BACKSIDE FINISH		BACKSIDE POTENTIAL	BOND PAD METALLIZATION COMPOSITION	BOND PAD THICKNESS	
10.5 mils.	Silicon with backgrind	Floating	Ti/Alcu (0.5%)/TiW	1010 nm	



(1) Designator "CIC60140" may appear on die.

Table 1. Bond Pad Coordinates in Microns

DESCRIPTION	PAD NUMBER	X MIN	Y MIN	X MAX	Y MAX
N/C	1	27	477	103	553
Inverting Input	2	27	251	105	329
Noninverting Input	3	27	27	103	103
Output	4	949	27	1025	103
-Vs	5	947	251	1025	329
+Vs	6	949	477	1025	553



PACKAGE OPTION ADDENDUM

14-Feb-2021

PACKAGING INFORMATION

www.ti.com

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
OPA846TDB1	ACTIVE			0	300	RoHS & Green	Call TI	N / A for Pkg Type	25 to 25		Samples
OPA846TDB2	ACTIVE			0	10	RoHS & Green	Call TI	N / A for Pkg Type	25 to 25		Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.





14-Feb-2021

重要声明和免责声明

TI 提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他安全、安保或其他要求。这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务,TI 对此概不负责。

TI 提供的产品受 TI 的销售条款 (https://www.ti.com.cn/zh-cn/legal/termsofsale.html) 或 ti.com.cn 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

邮寄地址:上海市浦东新区世纪大道 1568 号中建大厦 32 楼,邮政编码:200122 Copyright © 2021 德州仪器半导体技术(上海)有限公司