

# 74LVC2T45 2-Bit Dual-Supply Bus Transceiver with Configurable Voltage Translation

#### **GENERAL DESCRIPTION**

The 74LVC2T45 is a 2-bit, dual-supply bus transceiver with configurable voltage translation. The device has two separate configurable power-supply rails. The A and B ports track the  $V_{CCA}$  supply and  $V_{CCB}$  supply respectively. The supply voltage pins accept any voltage from 1.65V to 5.5V. This makes the device suitable for low voltage bidirectional translation voltage nodes of 1.8V, 2.5V, 3.3V, and 5V.

The 74LVC2T45 features that allows two data buses asynchronously communicated. Either the A port outputs or the B port outputs can be activated by DIR logic levels. The DIR input circuit is supplied by  $V_{CCA}$ . When B port outputs are activated, the device allows the data to transmit from A bus to B bus. On the contrary, when A port outputs are activated, the device allows the data to transmit from B bus to A bus. The input circuit is always active on the two ports. A logic high or low must be set to avoid excessive supply current.

# FEATURES

- V<sub>CCA</sub> Supply Voltage Range: 1.65V to 5.5V
- V<sub>CCB</sub> Supply Voltage Range: 1.65V to 5.5V
- DIR Input Circuit Referenced to V<sub>CCA</sub>
- +32mA/-32mA Output Current
- Data Rates
  - 420Mbps (3.3V to 5V Translation)
  - 210Mbps (Translate to 3.3V)
  - 140Mbps (Translate to 2.5V)
  - 75Mbps (Translate to 1.8V)
- Outputs in High-Impedance State when V<sub>CCA</sub> or V<sub>CCB</sub> = 0V
- -40°C to +125°C Operating Temperature Range
- Available in Green MSOP-8 and XTDFN-1.35×1-8L Packages

## **APPLICATIONS**

Personal Electronic Devices Industrial and Enterprise Devices Telecommunications



#### **PACKAGE/ORDERING INFORMATION**

| MODEL     | PACKAGE<br>DESCRIPTION | SPECIFIED<br>TEMPERATURE<br>RANGE | ORDERING<br>NUMBER | PACKAGE<br>MARKING   | PACKING<br>OPTION   |
|-----------|------------------------|-----------------------------------|--------------------|----------------------|---------------------|
| 74LVC2T45 | MSOP-8                 | -40°C to +125°C                   | 74LVC2T45XMS8G/TR  | GJX<br>XMS8<br>XXXXX | Tape and Reel, 4000 |
|           | XTDFN-1.35×1-8L        | -40°C to +125°C                   | 74LVC2T45XXET8G/TR | 4PX                  | Tape and Reel, 5000 |

#### MARKING INFORMATION

NOTE: XXXXX = Date Code, Trace Code and Vendor Code. X = Date Code.







Green (RoHS & HSF): SG Micro Corp defines "Green" to mean Pb-Free (RoHS compatible) and free of halogen substances. If you have additional comments or questions, please contact your SGMICRO representative directly.

#### ABSOLUTE MAXIMUM RATINGS (1)

| Supply Voltage Range, V <sub>CCA</sub>                     | 0.5V to 6.5V                    |
|--|---------------------------------|
| Supply Voltage Range, V <sub>CCB</sub>                     | 0.5V to 6.5V                    |
| Input Voltage Range, VI (2)                                | 0.5V to 6.5V                    |
| Output Voltage Range, Vo <sup>(2)</sup>                    |                                 |
| High-Impedance State                                       | 0.5V to 6.5V                    |
| High-State or Low-State                                    |                                 |
| A Ports0.5V to MIN   | (6.5V, V <sub>CCA</sub> + 0.5V) |
| B Ports0.5V to MIN   | (6.5V, V <sub>CCB</sub> + 0.5V) |
| Input Clamp Current, I <sub>IK</sub> (V <sub>I</sub> < 0)  | 50mA                            |
| Output Clamp Current, I <sub>OK</sub> (V <sub>O</sub> < 0) | 50mA                            |
| Output Current, Io   |                                 |
| High-State or Low-State                                    | ±50mA                           |
| Supply Current, I <sub>CCA</sub> or I <sub>CCB</sub>       | 100mA                           |
| Ground Current, I <sub>GND</sub>                           | 100mA                           |
| Junction Temperature <sup>(3)</sup>                        | +150°C                          |
| Storage Temperature Range                                  | 65°C to +150°C                  |
| Lead Temperature (Soldering, 10s)                          | +260°C                          |
| ESD Susceptibility   |                                 |
| НВМ  | 4000V                           |
| CDM  | 1000V                           |
|  |                                 |

#### **OVERSTRESS CAUTION**

1. Stresses beyond those listed in Absolute Maximum Ratings may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect reliability. Functional operation of the device at any conditions beyond those indicated in the Recommended Operating Conditions section is not implied.

2. The input negative-voltage and output voltage ratings may be exceeded if the input and output current ratings are observed.

3. The performance capability of a high-performance integrated circuit in conjunction with its thermal environment can create junction temperatures which are detrimental to reliability.

#### **ESD SENSITIVITY CAUTION**

This integrated circuit can be damaged if ESD protections are not considered carefully. SGMICRO recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage. ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because even small parametric changes could cause the device not to meet the published specifications.

#### DISCLAIMER

SG Micro Corp reserves the right to make any change in circuit design, or specifications without prior notice.



# 2-Bit Dual-Supply Bus Transceiver with Configurable Voltage Translation

#### **RECOMMENDED OPERATING CONDITIONS**

| Supply Voltage Range, V <sub>CCA</sub> | 1.65V to 5.5V          |
|--|------------------------|
| Supply Voltage Range, V <sub>CCB</sub> | 1.65V to 5.5V          |
| Input Voltage Range, V <sub>1</sub>    | 0V to 5.5V             |
| Output Voltage Range, Vo               |                        |
| High-Impedance State                   | 0V to 5.5V             |
| High-State or Low-State                |                        |
| A Ports                                | 0V to $V_{CCA}$        |
| B Ports                                | 0V to V <sub>CCB</sub> |
| High-Level Output Current, IOH         | 32mA                   |

| Low-Level Output Current, IoL                             | 32mA           |
|---|----------------|
| Input Transition Rise or Fall Rate, $\Delta t / \Delta V$ |                |
| Data Inputs   |                |
| V <sub>CCI</sub> = 1.65V to 1.95V                         | 20ns/V (MAX)   |
| V <sub>CCI</sub> = 2.3V to 2.7V                           | 20ns/V (MAX)   |
| V <sub>CCI</sub> = 3V to 3.6V                             | 10ns/V (MAX)   |
| V <sub>CCI</sub> = 4.5V to 5.5V                           | 5ns/V (MAX)    |
| Control Input   |                |
| V <sub>CCI</sub> = 1.65V to 5.5V                          | 5ns/V (MAX)    |
| Operating Temperature Range                               | 40°C to +125°C |

# LOGIC DIAGRAM



## **FUNCTION TABLE**

| SUPPLY VOLTAGE     | CONTROL INPUT      | INPUT/O | JTPUT <sup>(1)</sup> |  |  |
|--------------------|--------------------|---------|----------------------|--|--|
| $V_{CCA}, V_{CCB}$ | DIR <sup>(2)</sup> | An      | Bn                   |  |  |
| 1.65V to 5.5V      | L                  | An = Bn | Input                |  |  |
| 1.65V to 5.5V      | Н                  | Input   | Bn = An              |  |  |
| GND <sup>(3)</sup> | X                  | Z       | Z                    |  |  |

H = High Voltage Level

L = Low Voltage Level

X = Don't Care

Z = High-Impedance State

#### NOTES:

1. The input circuit of the data I/O is always active.

2. The DIR input circuit is referenced to  $V_{\mbox{\tiny CCA.}}$ 

3. If at least one of  $V_{\text{CCA}}$  or  $V_{\text{CCB}}$  is at GND level, the outputs in High-Impedance State.



## **PIN CONFIGURATIONS**



### **PIN DESCRIPTION**

| Р      | IN              | NAME  | FUNCTION   |  |  |  |
|--------|-----------------|---|--|--|--|--|
| MSOP-8 | XTDFN-1.35×1-8L | NAME  |  |  |  |  |
| 1      | 1               | V <sub>CCA</sub>  | Supply Voltage on A Ports.                           |  |  |  |
| 2      | 2               | A1 Input/Output. It tracks the V <sub>CCA</sub> supply. |  |  |  |  |
| 3      | 3               | A2  | Input/Output. It tracks the V <sub>CCA</sub> supply. |  |  |  |
| 4      | 4               | GND   | Ground.  |  |  |  |
| 5      | 5               | DIR   | Direction Control Signal.                            |  |  |  |
| 6      | 6               | B2  | Input/Output. It tracks the $V_{CCB}$ supply.        |  |  |  |
| 7      | 7               | B1  | Input/Output. It tracks the $V_{CCB}$ supply.        |  |  |  |
| 8      | 8               | V <sub>CCB</sub>  | Supply Voltage on B Ports.                           |  |  |  |



## **ELECTRICAL CHARACTERISTICS**

(Full = -40°C to +125°C, typical values are at  $T_A$  = +25°C.  $V_{CCI}$  is the supply voltage associated with the data input port,  $V_{CCO}$  is the supply voltage associated with the output port, unless otherwise noted.)

| PARAMETER   | SYMBOL              | С  | ONDITIONS  | TEMP  | MIN                     | TYP | MAX                     | UNITS |  |
|---|---------------------|--|--|-------|-------------------------|-----|-------------------------|-------|--|
| Cumulu Valtana  | V <sub>CCA</sub>    |  |  | Full  | 1.65                    |     | 5.5                     | V     |  |
| Supply voltage  | V <sub>CCB</sub>    |  |  | Full  | 1.65                    |     | 5.5                     | v     |  |
|   |                     |  | V <sub>CCI</sub> = 1.65V to 1.95V                                  | Full  | $0.65 \times V_{CCI}$   |     |                         |       |  |
|   | .,                  |  | V <sub>CCI</sub> = 2.3V to 2.7V                                    | Full  | 1.7                     |     |                         |       |  |
| PARAMETER         Supply Voltage         High-Level Input Voltage         Low-Level Input Voltage         High-Level Output Voltage         Low-Level Output Voltage         Input Leakage Current         Power-Off Leakage         Off-State Output Current <sup>(1)</sup> Supply Current | VIH                 | $ V_{CCA} = V_{CCA} = V_{CCB} = V_{$ | V <sub>CCI</sub> = 3V to 3.6V                                      | Full  | 2                       |     |                         | v     |  |
|   |                     |  |  |       |                         |     |                         |       |  |
|   |                     |  | V <sub>CCI</sub> = 1.65V to 1.95V                                  | Full  |                         |     | 0.35 × V <sub>CCI</sub> |       |  |
| 1   |                     |  | V <sub>CCI</sub> = 2.3V to 2.7V                                    | Full  |                         |     | 0.7                     |       |  |
| Low-Level input voltage   | VIL                 | Data and DIR inputs  | V <sub>CCI</sub> = 3V to 3.6V                                      | Full  |                         |     | 0.8                     | v     |  |
|   |                     |  | V <sub>CCI</sub> = 4.5V to 5.5V                                    | Full  |                         |     | 0.3 × V <sub>CCI</sub>  |       |  |
|   |                     |  | V <sub>CCO</sub> = 1.65V to 4.5V,<br>I <sub>OH</sub> = -100µA      | Full  | V <sub>cco</sub> - 0.03 |     |                         |       |  |
|   |                     |  | V <sub>CCO</sub> = 1.65V, I <sub>OH</sub> = -4mA                   | Full  | 1.37                    |     |                         | -     |  |
| High-Level Output Voltage   | Vau                 | $V_{i} = V_{i}$  | V <sub>CCO</sub> = 2.3V, I <sub>OH</sub> = -8mA                    | Full  | 2.00                    |     |                         | V     |  |
|   | V OH                | VI – VIH   | V <sub>CCO</sub> = 3V, I <sub>OH</sub> = -24mA                     | Full  | 2.44                    |     |                         | Ň     |  |
|   |                     |  | V <sub>CCO</sub> = 4.5V, I <sub>OH</sub> = -32mA                   | Full  | 3.98                    |     |                         |       |  |
|   |                     |  | V <sub>CCO</sub> = 5.5V, I <sub>OH</sub> = -32mA                   | Full  | 5.04                    |     |                         |       |  |
|   |                     |  | V <sub>CCO</sub> = 1.65V to 4.5V,<br>I <sub>OL</sub> = 100µA       | Full  |                         |     | 0.03                    |       |  |
|   |                     |  | V <sub>CCO</sub> = 1.65V, I <sub>OL</sub> = 4mA                    | Full  |                         |     | 0.24                    | -     |  |
| Low-Level Output Voltage  | Vai                 | $V_{i} = V_{i}$  | V <sub>CCO</sub> = 2.3V, I <sub>OL</sub> = 8mA                     | Full  |                         |     | 0.25                    | V     |  |
|   | V OL                |  | $V_{CCO} = 3V$ , $I_{OL} = 24mA$                                   | Full  |                         |     | 0.45                    | 1     |  |
|   |                     |  | V <sub>CCO</sub> = 4.5V, I <sub>OL</sub> = 32mA                    | Full  |                         |     | 0.50                    |       |  |
| High-Level Output Voltage Low-Level Output Voltage Input Leakage Current Power-Off Leakage Current Off-State Output Current <sup>(1)</sup> Supply Current Icc   |                     |  | V <sub>CCO</sub> = 5.5V, I <sub>OL</sub> = 32mA                    | Full  |                         |     | 0.47                    | -     |  |
| Input Leakage Current   | l <sub>i</sub>      | $V_I = V_{CCA}$ or GND, $V_{CA}$   | <sub>CA</sub> = V <sub>CCB</sub> = 1.65V to 5.5V                   | Full  |                         |     | ±1                      | μA    |  |
| Power-Off Leakage   |                     | $V_{0} = 0 V_{10} = 5 V_{10}$  | A port, $V_{CCA} = 0V$ ,<br>$V_{CCB} = 0V$ to 5.5V                 | Full  |                         |     | ±1                      | -μA   |  |
| Current   | OFF                 | $v_1$ or $v_0 = 0$ to 5.5 v  | B port, $V_{CCB} = 0V$ ,<br>$V_{CCA} = 0V$ to 5.5V                 | Full  |                         |     | ±1                      |       |  |
| Off-State Output Current (1)  | l <sub>oz</sub>     | $V_{CCA} = V_{CCB} = 1.65V t$  | to 5.5V, $V_0 = V_{CC0}$ or GND                                    | Full  |                         |     | ±1                      | μA    |  |
|   |                     |  | $V_{CCA} = V_{CCB} = 1.65V$ to 5.5V                                | Full  |                         |     | 2                       |       |  |
|   | I <sub>CCA</sub>    |  | $V_{CCA} = 5V, V_{CCB} = 0V$                                       | Full  |                         |     | 2                       |       |  |
|   |                     | $V_I = V_{CCI}$ or GND,  | $V_{CCA} = 0V, V_{CCB} = 5V$                                       | Full  | -2                      |     |                         |       |  |
| Supply Current  |                     | $I_{\rm O} = 0$  | $V_{CCA} = V_{CCB} = 1.65V$ to 5.5V                                | Full  |                         |     | 2                       | μA    |  |
|   | I <sub>CCB</sub>    |  | $V_{CCA} = 5V, V_{CCB} = 0V$                                       | Full  | -2                      |     |                         |       |  |
|   |                     |  | $V_{CCA} = 0V, V_{CCB} = 5V$                                       | Full  |                         |     | 2                       |       |  |
|   | $I_{CCA} + I_{CCB}$ | $V_1 = V_{CC1}$ or GND,<br>$I_0 = 0$   | $V_{CCA} = V_{CCB} = 1.65V$ to 5.5V                                | Full  |                         |     | 4                       |       |  |
|   | Alaas               | One A port at $V_{CCA}$ - C<br>B port = open, $V_{CCA}$ =  | 0.6V, DIR at V <sub>CCA</sub> ,<br>= V <sub>CCB</sub> = 3V to 5.5V | Full  |                         |     | 10                      |       |  |
| Additional Supply Current   |                     | DIR at $V_{CCA}$ - 0.6V, A<br>B port = open, $V_{CCA}$ =   | port at $V_{CCA}$ or GND,<br>$V_{CCB} = 3V$ to 5.5V                | Full  |                         |     | 10                      | μA    |  |
|   | $\Delta I_{CCB}$    | One B port at $V_{CCB}$ - (<br>A port = open, $V_{CCA}$ =  | Full   |       |                         | 10  |                         |       |  |
| Input Capacitance   | Cı                  | $V_{CCA} = V_{CCB} = 3.3V, D$  | DIR input, $V_1 = V_{CCA}$ or GND                                  | +25°C |                         | 4   | 1                       | pF    |  |
| Input/Output Capacitance  | C <sub>IO</sub>     | $V_{CCA} = V_{CCB} = 3.3V, A$  | and B ports, $V_0 = V_{CCA/B}$ or GND                              | +25°C |                         | 5   |                         | pF    |  |

#### NOTE:

1. For I/O ports, the parameter I<sub>OZ</sub> includes the input leakage current.

# 2-Bit Dual-Supply Bus Transceiver with Configurable Voltage Translation

## **DYNAMIC CHARACTERISTICS**

(For test circuit see Figure 1. Minimum and maximum values are at  $T_A = -40^{\circ}$ C to  $+125^{\circ}$ C, typical values are at  $T_A = +25^{\circ}$ C, unless otherwise noted.)

|                          |                  |            |                    |          |                    |                    |          | Va                 | св                 |         |                    |                    |         |                    |       |
|--------------------------|------------------|------------|--------------------|----------|--------------------|--------------------|----------|--------------------|--------------------|---------|--------------------|--------------------|---------|--------------------|-------|
| PARAMETER                | SYMBOL           | CONDITIONS | 1.8                | SV ± 0.1 | 15V                | 2.                 | 5V ± 0.: | 2V                 | 3.                 | 3V ± 0. | 3V                 | 5                  | V ± 0.5 | V                  | UNITS |
|                          |                  |            | MIN <sup>(1)</sup> | TYP      | MAX <sup>(1)</sup> | MIN <sup>(1)</sup> | TYP      | MAX <sup>(1)</sup> | MIN <sup>(1)</sup> | TYP     | MAX <sup>(1)</sup> | MIN <sup>(1)</sup> | TYP     | MAX <sup>(1)</sup> |       |
| $V_{CCA} = 1.8V \pm 0.$  | 15V              |            |                    |          |                    |                    |          |                    |                    |         |                    |                    |         |                    |       |
|                          | t <sub>PLH</sub> | A to B     | 1.5                | 6        | 13                 | 1                  | 4.5      | 9                  | 1                  | 4       | 7.5                | 1                  | 4       | 7                  |       |
| Propagation              | t <sub>PHL</sub> | A to D     | 1.5                | 6        | 13                 | 1                  | 4.5      | 8.5                | 1                  | 4       | 7.5                | 1                  | 4       | 7                  | ne    |
| Delay                    | t <sub>PLH</sub> | R to A     | 1.5                | 6        | 13                 | 1                  | 5        | 12                 | 1                  | 5       | 11.5               | 1                  | 5       | 11                 | 115   |
|                          | t <sub>PHL</sub> | DIOA       | 1.5                | 6        | 13                 | 1                  | 5        | 12                 | 1                  | 5       | 11.5               | 1                  | 5       | 11.5               |       |
|                          | t <sub>PHZ</sub> |            | 3                  | 10.5     | 16                 | 3                  | 10.5     | 16                 | 3                  | 10.5    | 16                 | 3                  | 10.5    | 16                 |       |
| Disable Time             | t <sub>PLZ</sub> | DIR to A   | 2.5                | 7        | 11.5               | 2.5                | 7.5      | 11.5               | 2.5                | 7       | 12                 | 2.5                | 8.5     | 13                 |       |
|                          | t <sub>PHZ</sub> |            | 3                  | 14       | 22                 | 2.5                | 9        | 14                 | 2.5                | 6       | 11                 | 2.5                | 5.5     | 9                  | 115   |
|                          | t <sub>PLZ</sub> |            | 3                  | 10       | 17                 | 2                  | 6        | 11                 | 2.5                | 6.5     | 10                 | 2                  | 5       | 8                  |       |
|                          | t <sub>PZH</sub> | DIR to A   |                    | 16       | 30                 |                    | 11       | 23                 |                    | 11.5    | 21.5               |                    | 10      | 19                 |       |
|                          | t <sub>PZL</sub> | DIR IO A   |                    | 20       | 35                 |                    | 14       | 26                 |                    | 11      | 22.5               |                    | 10.5    | 20.5               |       |
| Enable Time V            | t <sub>PZH</sub> | DIR to B   |                    | 13       | 24.5               |                    | 12       | 20.5               |                    | 11      | 19.5               |                    | 12.5    | 20                 |       |
|                          | t <sub>PZL</sub> |            |                    | 16.5     | 29                 |                    | 15       | 24.5               |                    | 14.5    | 23.5               |                    | 14.5    | 23                 |       |
| $V_{CCA} = 2.5V \pm 0.2$ | 2V               |            |                    |          |                    |                    |          |                    | •                  |         |                    |                    |         |                    |       |
|                          | t <sub>PLH</sub> |            | 1                  | 5        | 12                 | 1                  | 3.5      | 7.5                | 1                  | 3       | 6                  | 0.7                | 3       | 5.5                |       |
| Propagation              | t <sub>PHL</sub> | ALOB       | 1                  | 5        | 12                 | 1                  | 3.5      | 7.5                | 1                  | 3       | 6                  | 0.7                | 3       | 5.5                |       |
| Delay                    | t <sub>PLH</sub> | R to A     | 1                  | 4.5      | 9                  | 1                  | 3.5      | 7.5                | 1                  | 3.5     | 7                  | 1                  | 3.5     | 7                  | 115   |
|                          | t <sub>PHL</sub> | BIOA       | 1                  | 4.5      | 8.5                | 1                  | 3.5      | 7.5                | 1                  | 3.5     | 7                  | 0.9                | 3.5     | 7                  |       |
|                          | t <sub>PHZ</sub> |            | 2                  | 7        | 10                 | 2                  | 7        | 10                 | 2                  | 7       | 10                 | 2                  | 7.5     | 11                 |       |
| Dischle Time             | t <sub>PLZ</sub> | DIR IO A   | 1.5                | 3.5      | 8                  | 1.5                | 3.5      | 8                  | 1.5                | 3.5     | 8                  | 1.5                | 4       | 8                  |       |
| Disable Time             | t <sub>PHZ</sub> |            | 3.5                | 12.5     | 20.5               | 2.5                | 7.5      | 12                 | 2.5                | 5       | 10                 | 2                  | 4       | 7.5                | ns    |
|                          | t <sub>PLZ</sub> |            | 3                  | 9        | 16                 | 2                  | 5        | 10                 | 2.5                | 5.5     | 9                  | 2                  | 4       | 7                  |       |
|                          | t <sub>PZH</sub> |            |                    | 13.5     | 25                 |                    | 8.5      | 17.5               |                    | 9       | 16                 |                    | 7.5     | 14                 |       |
|                          | t <sub>PZL</sub> | DIR IO A   |                    | 17       | 29                 |                    | 11       | 19.5               |                    | 8.5     | 17                 |                    | 7.5     | 14.5               | 1     |
|                          | t <sub>PZH</sub> |            |                    | 8.5      | 20                 |                    | 7        | 15.5               |                    | 6.5     | 14                 |                    | 7       | 13.5               | ns    |
|                          | t <sub>PZL</sub> | אוע וט א   |                    | 12       | 22                 |                    | 10.5     | 17.5               |                    | 10      | 16                 |                    | 10.5    | 16.5               |       |

# **DYNAMIC CHARACTERISTICS (continued)**

(For test circuit see Figure 1. Minimum and maximum values are at  $T_A = -40^{\circ}$ C to  $+125^{\circ}$ C, typical values are at  $T_A = +25^{\circ}$ C, unless otherwise noted.)

|                             |                  |            |                    |          |                    |                    |         | Va                 | СВ                 |         |                    |                    |         |                    |            |
|-----------------------------|------------------|------------|--------------------|----------|--------------------|--------------------|---------|--------------------|--------------------|---------|--------------------|--------------------|---------|--------------------|------------|
| PARAMETER                   | SYMBOL           | CONDITIONS | 1.8                | BV ± 0.1 | 15V                | 2.                 | 5V ± 0. | 2V                 | 3.                 | 3V ± 0. | 3V                 | 5                  | V ± 0.5 | V                  | UNITS      |
|                             |                  |            | MIN <sup>(1)</sup> | TYP      | MAX <sup>(1)</sup> | MIN <sup>(1)</sup> | TYP     | MAX <sup>(1)</sup> | MIN <sup>(1)</sup> | TYP     | MAX <sup>(1)</sup> | MIN <sup>(1)</sup> | TYP     | MAX <sup>(1)</sup> |            |
| $V_{CCA} = 3.3V \pm 0.$     | 3V               |            |                    |          |                    |                    |         |                    |                    |         |                    |                    |         |                    |            |
|                             | t <sub>PLH</sub> | A to B     | 1                  | 5        | 11.5               | 1                  | 3.5     | 7                  | 0.7                | 3       | 5.5                | 0.7                | 2.5     | 5                  |            |
| Propagation                 | t <sub>PHL</sub> |            | 1                  | 5        | 11.5               | 1                  | 3.5     | 7                  | 0.8                | 3       | 5.5                | 0.7                | 2.5     | 5                  | ne         |
| Delay                       | t <sub>PLH</sub> | B to A     | 1                  | 4        | 7.5                | 1                  | 3       | 6                  | 0.7                | 3       | 5.5                | 0.6                | 3       | 5.5                | 115        |
|                             | t <sub>PHL</sub> | DIOA       | 1                  | 4        | 7.5                | 1                  | 3       | 6                  | 0.8                | 3       | 5.5                | 0.7                | 3       | 5.5                |            |
|                             | t <sub>PHZ</sub> |            | 2                  | 4        | 8.5                | 2                  | 4       | 8.5                | 2                  | 4       | 8.5                | 2                  | 4       | 8.5                |            |
| Disable Time                | t <sub>PLZ</sub> | DIR IO A   | 1.5                | 3.5      | 8                  | 1.5                | 3.5     | 8                  | 1.5                | 4       | 8                  | 1.5                | 4       | 8                  | ne         |
| Disable Time                | t <sub>PHZ</sub> |            | 3.5                | 12.5     | 20                 | 2.5                | 8       | 12                 | 2.5                | 5       | 10                 | 2                  | 4       | 7.5                | 115        |
|                             | t <sub>PLZ</sub> |            | 3                  | 8        | 15.5               | 2                  | 4.5     | 10                 | 2                  | 5.5     | 8.5                | 1.5                | 3.5     | 7.5                |            |
|                             | t <sub>PZH</sub> |            |                    | 12       | 23                 |                    | 7.5     | 16                 |                    | 8.5     | 14                 |                    | 6.5     | 13                 |            |
|                             | t <sub>PZL</sub> |            |                    | 16.5     | 27.5               |                    | 11      | 18                 |                    | 8       | 15.5               |                    | 7       | 13                 | ns         |
|                             | t <sub>PZH</sub> | DIR to B   |                    | 8.5      | 19.5               |                    | 7       | 15                 |                    | 7       | 13.5               |                    | 6.5     | 13                 |            |
|                             | t <sub>PZL</sub> |            |                    | 9        | 20                 |                    | 7.5     | 15.5               |                    | 7       | 14                 |                    | 6.5     | 13.5               |            |
| $V_{\rm CCA} = 5V \pm 0.5V$ | /                |            |                    |          |                    |                    |         |                    |                    |         |                    |                    |         |                    |            |
|                             | t <sub>PLH</sub> | A to B     | 1                  | 5        | 11                 | 1                  | 3.5     | 7                  | 0.6                | 3       | 5.5                | 0.5                | 2.5     | 5                  |            |
| Propagation                 | t <sub>PHL</sub> | AIUB       | 1                  | 5        | 11.5               | 0.9                | 3.5     | 7                  | 0.7                | 3       | 5.5                | 0.5                | 2.5     | 4.5                | <b>n</b> 0 |
| Delay                       | t <sub>PLH</sub> | R to A     | 1                  | 4        | 7                  | 0.7                | 3       | 5.5                | 0.7                | 2.5     | 5                  | 0.5                | 2.5     | 5                  | 115        |
|                             | t <sub>PHL</sub> | DIUA       | 1                  | 4        | 7                  | 0.7                | 3       | 5.5                | 0.7                | 2.5     | 5                  | 0.5                | 2.5     | 4.5                |            |
|                             | t <sub>PHZ</sub> |            | 1.5                | 4        | 6.5                | 1.5                | 4       | 6.5                | 1.5                | 4       | 6.5                | 1.5                | 4       | 7                  |            |
| Dischla Time                | t <sub>PLZ</sub> | DIR IO A   | 1                  | 3        | 5.5                | 1                  | 3       | 5.5                | 1                  | 3       | 5.5                | 1                  | 3       | 5.5                |            |
| Disable Time                | t <sub>PHZ</sub> |            | 3.5                | 12       | 19.5               | 2.5                | 8       | 12.5               | 2.5                | 5       | 10                 | 2                  | 4       | 7.5                | ns         |
|                             | t <sub>PLZ</sub> |            | 3                  | 9.5      | 16                 | 2                  | 5.5     | 9                  | 2                  | 5.5     | 8.5                | 1.5                | 3.5     | 6                  |            |
|                             | t <sub>PZH</sub> |            |                    | 13.5     | 23                 |                    | 8.5     | 14.5               |                    | 8       | 13.5               |                    | 6       | 11                 | -          |
| Enchlo Time <sup>(2)</sup>  | t <sub>PZL</sub> |            |                    | 16       | 26.5               |                    | 11      | 18                 |                    | 7.5     | 15                 |                    | 6.5     | 12                 |            |
|                             | t <sub>PZH</sub> |            |                    | 8        | 16.5               |                    | 6.5     | 12.5               |                    | 6       | 11                 |                    | 5.5     | 10.5               | ns         |
|                             | t <sub>PZL</sub> | אוט א      |                    | 9        | 18                 |                    | 7.5     | 13.5               |                    | 7       | 12                 |                    | 6.5     | 11.5               |            |

NOTE:

1. Specified by design and characterization; not production tested.

2. The enable time value is calculated. Calculate the enable times for the 74LVC2T45 using the following formulas:

•  $t_{PZH}$  (DIR to A) =  $t_{PLZ}$  (DIR to B) +  $t_{PLH}$  (B to A)

•  $t_{PZL}$  (DIR to A) =  $t_{PHZ}$  (DIR to B) +  $t_{PHL}$  (B to A)

•  $t_{PZH}$  (DIR to B) =  $t_{PLZ}$  (DIR to A) +  $t_{PLH}$  (A to B)

•  $t_{PZL}$  (DIR to B) =  $t_{PHZ}$  (DIR to A) +  $t_{PHL}$  (A to B)



## **DYNAMIC CHARACTERISTICS (continued)**

(For test circuit, see Figure 1, typical values are at  $T_A = +25^{\circ}C$ , unless otherwise noted.)

| DADAMETED  | SYMPOL           | CONDITIONS             |                                | $V_{CCA} = V_{CCB} = 1.8V$ | $V_{CCA} = V_{CCB} = 2.5V$ | $V_{CCA} = V_{CCB} = 3.3V$ | $_{A} = V_{CCB} = 3.3V$ $V_{CCA} = V_{CCB} = 5V$ |       |
|--|------------------|------------------------|--------------------------------|----------------------------|----------------------------|----------------------------|--|-------|
| PARAMETER  | STWIDOL          |                        |                                | ТҮР                        | TYP                        | TYP                        | TYP  | UNITS |
|  | C                | $C_L = 0 pF$ ,         | A Port Input,<br>B Port Output | 3                          | 3                          | 4                          | 5  | рE    |
| Power<br>Dissipation<br>Capacitance <sup>(1)</sup> | OPDA             | $t_{R} = t_{F} = 1$ ns | B Port Input,<br>A Port Output | 19                         | 20                         | 21                         | 22   | ρr    |
|  | C <sub>PDB</sub> | $C_L = 0 p F,$         | A Port Input,<br>B Port Output | 19                         | 20                         | 21                         | 22   | ۶Ē    |
|  |                  | $t_R = t_F = 1$ ns     | B Port Input,<br>A Port Output | 3                          | 3                          | 4                          | 5  | μL    |

NOTE:

1. Power dissipation capacitance per transceiver.  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu W$ ).

 $P_{D} = C_{PD} \times V_{CC}^{2} \times f_{i} \times N + \Sigma (C_{L} \times V_{CC}^{2} \times f_{o})$ 

where:

 $f_i$  = input frequency in MHz.

 $f_o$  = output frequency in MHz.

 $C_L$  = output load capacitance in pF.

V<sub>CC</sub> = supply voltage in Volts.

N = number of inputs switching.

 $\Sigma(C_L \times V_{CC}^2 \times f_o)$  = sum of the outputs.



# 2-Bit Dual-Supply Bus Transceiver with Configurable Voltage Translation

## **TEST CIRCUIT**



Test conditions are given in Table 1.

Definitions for test circuit:

RL: Load resistance.

CL: Load capacitance (includes jig and probe).

 $R_T$ : Termination resistance (equals to output impedance  $Z_0$  of the pulse generator).

V<sub>EXT</sub>: External voltage used to measure switching time.

#### Figure 1. Test Circuit for Measuring Switching Times

#### **Table 1. Test Conditions**

| SUPPLY VOLTAGE                      | IN                | PUT                             | LC   | AD  | V <sub>EXT</sub>                    |                                   |                                     |  |
|-------------------------------------|-------------------|---------------------------------|------|-----|-------------------------------------|-----------------------------------|-------------------------------------|--|
| V <sub>CCA</sub> , V <sub>CCB</sub> | VI <sup>(1)</sup> | t <sub>R</sub> , t <sub>F</sub> | C∟   | R∟  | t <sub>PHZ</sub> , t <sub>PZH</sub> | $t_{PLZ}, t_{PZL}$ <sup>(2)</sup> | t <sub>PLH</sub> , t <sub>PHL</sub> |  |
| 1.65V to 5.5V                       | V <sub>CCI</sub>  | ≤ 2.5ns                         | 15pF | 2kΩ | GND                                 | 2 × V <sub>CCO</sub>              | Open                                |  |

NOTES:

1.  $V_{\text{CCI}}$  is the supply voltage related to the input port.

2.  $V_{\text{CCO}}$  is the supply voltage related to the output port.



## WAVEFORMS



Test conditions are given in Table 1.

Measurement points are given in Table 2.

Logic levels:  $V_{OL}$  and  $V_{OH}$  are typical output voltage levels that occur with the output load.

#### Figure 2. Input (An, Bn) to Output (Bn, An) Propagation Delay Times



Test conditions are given in Table 1.

Measurement points are given in Table 2.

Logic levels:  $V_{OL}$  and  $V_{OH}$  are typical output voltage levels that occur with the output load.

#### Figure 3. Enable and Disable Times

#### Table 2. Measurement Points

| SUPPLY VOLTAGE     | INF                           | TU                            | OUTPUT                        |                         |                         |  |  |  |
|--------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------|-------------------------|--|--|--|
| $V_{CCA}, V_{CCB}$ | V <sub>1</sub> <sup>(1)</sup> | V <sub>M</sub> <sup>(2)</sup> | V <sub>M</sub> <sup>(3)</sup> | Vx                      | V <sub>Y</sub>          |  |  |  |
| 1.65V to 2.7V      | V <sub>CCI</sub>              | $0.5 \times V_{CCI}$          | $0.5 \times V_{CCO}$          | V <sub>OL</sub> + 0.15V | V <sub>OH</sub> - 0.15V |  |  |  |
| 3V to 5.5V         | V <sub>CCI</sub>              | 0.5 × V <sub>CCI</sub>        | $0.5 \times V_{CCO}$          | V <sub>OL</sub> + 0.3V  | V <sub>OH</sub> - 0.3V  |  |  |  |

#### NOTES:

1. V<sub>CCI</sub> is the supply voltage related to the input port.

2. The measurement points should be  $V_{IH}$  or  $V_{IL}$  when the input rising or falling time exceeds 2.5ns.

3.  $V_{\text{CCO}}$  is the supply voltage related to the output port.

Page

### **REVISION HISTORY**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

#### Changes from Original (JUNE 2022) to REV.A

| Changed from product provide to production data | 11  |
|---|-----|
| changed from product preview to production data | 111 |



# PACKAGE OUTLINE DIMENSIONS

## **MSOP-8**





RECOMMENDED LAND PATTERN (Unit: mm)





| Symbol | Dimer<br>In Milli | nsions<br>meters | Dimensions<br>In Inches |       |  |
|--------|-------------------|------------------|-------------------------|-------|--|
|        | MIN               | MAX              | MIN                     | MAX   |  |
| A      | 0.820             | 1.100            | 0.032                   | 0.043 |  |
| A1     | 0.020             | 0.150            | 0.001                   | 0.006 |  |
| A2     | 0.750             | 0.950            | 0.030                   | 0.037 |  |
| b      | 0.250             | 0.380            | 0.010                   | 0.015 |  |
| с      | 0.090             | 0.230            | 0.004                   | 0.009 |  |
| D      | 2.900             | 3.100            | 0.114                   | 0.122 |  |
| E      | 2.900             | 3.100            | 0.114                   | 0.122 |  |
| E1     | 4.750             | 5.050            | 0.187                   | 0.199 |  |
| е      | 0.650             | ) BSC            | 0.026                   | BSC   |  |
| L      | 0.400             | 0.800            | 0.016                   | 0.031 |  |
| θ      | 0°                | 6°               | 0°                      | 6°    |  |

NOTES:

Body dimensions do not include mode flash or protrusion.
 This drawing is subject to change without notice.



# PACKAGE OUTLINE DIMENSIONS

# XTDFN-1.35×1-8L





RECOMMENDED LAND PATTERN (Unit: mm)

| Symbol | Dimensions In Millimeters |       |       |  |  |  |
|--------|---------------------------|-------|-------|--|--|--|
|        | MIN                       | MOD   | MAX   |  |  |  |
| A      | -                         | 0.310 | 0.330 |  |  |  |
| A1     | 0.000                     | -     | 0.050 |  |  |  |
| A2     | 0.100 REF                 |       |       |  |  |  |
| D      | 1.250                     | 1.350 | 1.450 |  |  |  |
| E      | 0.900                     | 1.000 | 1.100 |  |  |  |
| b      | 0.110                     | 0.160 | 0.210 |  |  |  |
| е      | 0.350 BSC                 |       |       |  |  |  |
| L      | 0.250                     | 0.300 | 0.350 |  |  |  |
| L1     | 0.300                     | 0.350 | 0.400 |  |  |  |
| L2     | 0.075 REF                 |       |       |  |  |  |
| eee    | - 0.050 -                 |       |       |  |  |  |

NOTE: This drawing is subject to change without notice.



## TAPE AND REEL INFORMATION

#### **REEL DIMENSIONS**



NOTE: The picture is only for reference. Please make the object as the standard.

#### KEY PARAMETER LIST OF TAPE AND REEL

| Package Type    | Reel<br>Diameter | Reel Width<br>W1<br>(mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P0<br>(mm) | P1<br>(mm) | P2<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
|-----------------|------------------|--------------------------|------------|------------|------------|------------|------------|------------|-----------|------------------|
| MSOP-8          | 13″              | 12.4                     | 5.20       | 3.30       | 1.50       | 4.0        | 8.0        | 2.0        | 12.0      | Q1               |
| XTDFN-1.35×1-8L | 7"               | 9.5                      | 1.21       | 1.51       | 0.39       | 4.0        | 4.0        | 2.0        | 8.0       | Q1               |

#### **CARTON BOX DIMENSIONS**



NOTE: The picture is only for reference. Please make the object as the standard.

#### **KEY PARAMETER LIST OF CARTON BOX**

| Reel Type   | Length<br>(mm) | Width<br>(mm) | Height<br>(mm) | Pizza/Carton |  |
|-------------|----------------|---------------|----------------|--------------|--|
| 7" (Option) | 368            | 227           | 224            | 8            |  |
| 7″          | 442            | 410           | 224            | 18           |  |
| 13″         | 386            | 280           | 370            | 5            |  |

