

# 74LVC74 Dual D-Type Positive Edge-Triggered Flip-Flop with Set and Reset

## **GENERAL DESCRIPTION**

The 74LVC74 is a dual D-type flip-flop positive edge-triggered with set and reset. This device accepts a wide supply voltage range from 1.2V to 3.6V. nD are individual data inputs, nCP are clock inputs, n $\overline{S}D$  and  $n\overline{R}D$  are set inputs, nQ and  $n\overline{Q}$  are complementary outputs.

The set and reset are non-synchronous inputs (active low) and clock inputs can be operated independently. When clock pulse is in the transition of low-to-high, data at the nD inputs will be transmitted to the nQ outputs. For predictable outputs performance, prior set-up time must be required necessarily by nD inputs to the low-to-high clock transition.

Schmitt trigger action features the high tolerance of over-voltage for inputs/outputs data and control inputs and slower input rise and fall times. This device is suitable for down-translation in a mixed-voltage environment.

## **FUNCTION TABLE**

CONTROL INPUT			INPUT	OUTPUT	
nSD	nRD	nCP	nD	nQ	nQ
L	н	X	X	Н	L
Н	L	X	X	L	Н
L	L	X	X	Н	Н

H = High Voltage Level


L = Low Voltage Level

X = Don't Care

## **FEATURES**

- Wide Supply Voltage Range: 1.2V to 3.6V
- Inputs Accept Voltages up to 5V
- CMOS Low Power Consumption
- Direct Interface with TTL Levels
- -40°C to +125°C Operating Temperature Range
- Available in a Green TSSOP-14 Package

# LOGIC SYMBOL



CONTROL INPUT			INPUT	OUTPUT		
nSD	nRD	nCP	nD	nQ <sub>n+1</sub>	nQn+1	
Н	Н	<b>↑</b>	L	L	Н	
Н	Н	Ť	Н	Н	L	

H = High Voltage Level

L = Low Voltage Level

↑ = Low-to-High Clock Transition

Q<sub>n+1</sub> = State after the Next Low-to-High CP Transition

## PACKAGE/ORDERING INFORMATION

MODEL	PACKAGE DESCRIPTION	SPECIFIED TEMPERATURE RANGE	ORDERING NUMBER	PACKAGE MARKING	PACKING OPTION
74LVC74	TSSOP-14	-40°C to +125°C	74LVC74XTS14G/TR	74LVC74 XTS14 XXXXX	Tape and Reel, 4000

### MARKING INFORMATION

NOTE: XXXXX = Date Code, Trace Code and Vendor Code.

XXXXX

- Vendor Code
- Trace Code
  - Date Code Year

Green (RoHS & HSF): SG Micro Corp defines "Green" to mean Pb-Free (RoHS compatible) and free of halogen substances. If yo ave additional comments or questions, please contact your SGMICRO representative directly.

### ABSOLUTE MAXIMUM RATINGS (1)

Supply Voltage, V <sub>CC</sub>	0.5V to 6.5V
Input Voltage, V <sub>I</sub> <sup>(2)</sup>	0.5V to 6.5V
Output Voltage, Vo <sup>(2)</sup>	0.5V to V <sub>CC</sub> + 0.5V
Input Clamping Current, I <sub>IK</sub> (V <sub>I</sub> < 0V)	
Output Clamping Current, $I_{OK}$ (V <sub>O</sub> > V <sub>CC</sub> or	V <sub>0</sub> < 0V)
	±50mA
Output Current, $I_0$ (V <sub>0</sub> = 0V to V <sub>CC</sub> )	±50mA
Supply Current, I <sub>CC</sub>	100mA
Ground Current, I <sub>GND</sub>	
Junction Temperature <sup>(3)</sup>	+150°C
Storage Temperature Range	65°C to +150°C
Lead Temperature (Soldering, 10s)	+260°C
ESD Susceptibility	
НВМ	6000V
CDM	1000V

### **RECOMMENDED OPERATING CONDITIONS**

Supply Voltage, V <sub>CC</sub>	1.65V to 3.6V
Data Retention Only, Vcc	1.2V to 3.6V
Input Voltage, V <sub>I</sub>	0V to 5.5V
Output Voltage, Vo	$0V$ to $V_{CC}$
Input Transition Rise and Fall Rate, $\Delta t / \Delta V$	
V <sub>CC</sub> = 1.65V to 2.7V	20ns/V (MAX)
V <sub>CC</sub> = 2.7V to 3.6V	10ns/V (MAX)
Operating Temperature Range	40°C to +125°C

### **OVERSTRESS CAUTION**

1. Stresses beyond those listed in Absolute Maximum Ratings may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect reliability. Functional operation of the device at any conditions beyond those indicated in the Recommended Operating Conditions section is not implied.

2. The input and output voltage ratings may be exceeded if the input and output clamp current ratings are observed.

3. The performance capability of a high-performance integrated circuit in conjunction with its thermal environment can create junction temperatures which are detrimental to reliability.

### **ESD SENSITIVITY CAUTION**

This integrated circuit can be damaged if ESD protections are not considered carefully. SGMICRO recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage. ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because even small parametric changes could cause the device not to meet the published specifications.


#### DISCLAIMER

SG Micro Corp reserves the right to make any change in circuit design, or specifications without prior notice.



## 74LVC74

# **PIN CONFIGURATION**



### **PIN DESCRIPTION**

PIN	NAME	FUNCTION
1, 13	1RD, 2RD	Non-synchronous Reset-Direct Inputs (Active Low).
2, 12	1D, 2D	Data Inputs.
3, 11	1CP, 2CP	Clock Inputs (Low-to-High, Edge-Triggered).
4, 10	1SD, 2SD	Non-synchronous Set-Direct Inputs (Active Low).
5, 9	1Q, 2Q	True Outputs.
6, 8	1Q, 2Q	Complement Outputs.
7	GND	Ground.
14	Vcc	Power Supply.

# **ELECTRICAL CHARACTERISTICS**

(Full = -40°C to +125°C, all typical values are measured at  $V_{CC}$  = 3.3V and  $T_A$  = +25°C, unless otherwise noted.)

PARAMETER	SYMBOL		CONDITIONS	TEMP	MIN	TYP	MAX	UNITS			
High Lovel Input Veltage	VIH	V <sub>CC</sub> = 1.2V		Full	1.2			V			
High-Level Input Voltage	VIH	$V_{\rm CC}$ = 2.7V to 3	3.6V	Full	2			v			
	VIL	V <sub>CC</sub> = 1.2V		Full			0.1	V			
Low-Level Input Voltage	VIL	$V_{CC}$ = 2.7V to 3	3.6V	Full			0.8	v			
			$V_{CC}$ = 2.7V to 3.6V, $I_0$ = -100 $\mu$ A	Full	V <sub>CC</sub> - 0.05	$V_{\rm CC}$ - 0.005					
Lligh Lough Output Valtage	V <sub>он</sub>	V <sub>он</sub>	$V_{I} = V_{IH} \text{ or } V_{IL}$	V <sub>CC</sub> = 2.7V, I <sub>O</sub> = -12mA	Full	2.35	2.57		v		
High-Level Output Voltage				V <sub>CC</sub> = 3.0V, I <sub>O</sub> = -18mA	Full	2.55	2.82		v		
			$V_{CC} = 3.0V, I_0 = -24mA$	Full	2.45	2.75					
						$V_{CC}$ = 2.7V to 3.6V, $I_0$ = 100 $\mu$ A	Full		0.005	0.05	
Low-Level Output Voltage	V <sub>OL</sub>	$V_{I} = V_{IH} \text{ or } V_{IL}$	V <sub>CC</sub> = 2.7V, I <sub>O</sub> = 12mA	Full		0.12	0.30	V			
			V <sub>CC</sub> = 3.0V, I <sub>O</sub> = 24mA	Full		0.23	0.55				
Input Leakage Current	lı –	V <sub>CC</sub> = 3.6V, V <sub>I</sub>	V <sub>CC</sub> = 3.6V, V <sub>I</sub> = 5.5V or GND			±0.05	±10	μA			
Supply Current	Icc	$V_{CC}$ = 3.6V, $V_I$ = $V_{CC}$ or GND, $I_O$ = 0A		Full		0.05	20	μA			
Additional Supply Current	ΔI <sub>CC</sub>	Per input pin, $V_{CC}$ = 2.7V to 3.6V, V <sub>I</sub> = V <sub>CC</sub> - 0.6V, I <sub>O</sub> = 0A		Full		0.1	4000	μA			
Input Capacitance	Cı	$V_{\rm CC}$ = 0V to 3.6	SV, $V_I = GND$ to $V_{CC}$	+25°C		6		pF			



## **DYNAMIC CHARACTERISTICS**

(For test circuit, see Figure 1. All typical values are measured at  $T_A = +25^{\circ}$ C. For  $V_{CC} = 3.0$ V to 3.6V range, typical values are measured at 3.3V, unless otherwise noted.)

PARAMETER	SYMBOL	C	ONDITIONS	TEMP	MIN	TYP	MAX	UNITS
		_	V <sub>CC</sub> = 1.2V	+25°C		15		
		nCP to nQ, n $\overline{Q}$ , see Figure 2	V <sub>CC</sub> = 2.7V	+25°C		5		]
		soo niguro 2	V <sub>CC</sub> = 3.0V to 3.6V	+25℃		4		
			V <sub>CC</sub> = 1.2V	+25℃		16		
Propagation Delay <sup>(1)</sup>	t <sub>PD</sub>	nSD to nQ, nQ, see Figure 3	V <sub>CC</sub> = 2.7V	+25℃		4		ns
		See Figure 0	V <sub>CC</sub> = 3.0V to 3.6V	+25℃		3.5		
			V <sub>CC</sub> = 1.2V	+25°C		17		
		nRD to nQ, nQ, see Figure 3	V <sub>CC</sub> = 2.7V	+25°C		4		
	See Figure 0	V <sub>CC</sub> = 3.0V to 3.6V	+25°C		3.5		1	
		Clock high or low, see Figure 2	V <sub>CC</sub> = 2.7V	+25℃	5			- ns
			V <sub>CC</sub> = 3.0V to 3.6V	+25℃		2.5		
Pulse Width	t <sub>w</sub>	Set or reset low, see Figure 3	V <sub>CC</sub> = 2.7V	+25℃	5			
			V <sub>CC</sub> = 3.0V to 3.6V	+25℃		2.5		
Description		Set or reset,	V <sub>CC</sub> = 2.7V	+25℃	2.5			
Recovery Time	t <sub>REC</sub>	see Figure 3	V <sub>CC</sub> = 3.0V to 3.6V	+25℃	2			ns
		nD to nCP,	V <sub>CC</sub> = 2.7V	+25℃	3			
Set-Up Time	t <sub>s∪</sub>	see Figure 2	V <sub>CC</sub> = 3.0V to 3.6V	+25°C	2.5			ns
I I a I d Time a		nD to nCP,	V <sub>CC</sub> = 2.7V	+25°C	2			ns
Hold Time	t <sub>H</sub>	see Figure 2	V <sub>CC</sub> = 3.0V to 3.6V	+25℃	2			
Maria Francis	6	nCP,	V <sub>CC</sub> = 2.7V	+25°C		170		N 41 I-
Maximum Frequency f <sub>MAX</sub>	see Figure 2	V <sub>CC</sub> = 3.0V to 3.6V	+25°C		250		MHz	
Output Skew Time	t <sub>SK(O)</sub>	$V_{CC}$ = 3.0V to 3.6V	•	+25°C		0.5		ns
Power Dissipation Capacitance <sup>(2)</sup>	C <sub>PD</sub>	Per flip-flop, V <sub>I</sub> = G	ND to $V_{CC}$ , $V_{CC}$ = 3.0V to 3.6V	+25°C		15		pF

NOTES:

1.  $t_{\text{PD}}$  is the same as  $t_{\text{PLH}}$  and  $t_{\text{PHL}}.$ 

2.  $C_{PD}$  is used to determine the dynamic power dissipation (P<sub>D</sub> in  $\mu$ W).

 $P_{D} = C_{PD} \times V_{CC}^{2} \times f_{i} \times N + \Sigma (C_{L} \times V_{CC}^{2} \times f_{o})$ where:

 $f_i$  = input frequency in MHz.

 $f_o$  = output frequency in MHz.

 $C_L$  = output load capacitance in pF.

 $V_{CC}$  = supply voltage in Volts.


N = number of inputs switching.

 $\Sigma(C_L \times V_{CC}^2 \times f_o)$  = sum of the outputs.



### 74LVC74

## **TEST CIRCUIT**



Test conditions are given in Table 1.

Definitions for test circuit:

R<sub>L</sub>: Load resistance.

C<sub>L</sub>: Load capacitance (including jig and probe).

 $R_T$ : Termination resistance (equal to output impedance  $Z_0$  of the pulse generator).

#### Figure 1. Test Circuit for Measuring Switching Times


#### **Table 1. Test Conditions**

SUPPLY VOLTAGE	INF	TUT	LOAD		
Vcc	VI	t <sub>R</sub> , t <sub>F</sub>	CL	RL	
2.7V	2.7V	≤ 2.5ns	50pF	500Ω	
3.0V to 3.6V	2.7V	≤ 2.5ns	50pF	500Ω	



### 74LVC74

### WAVEFORMS




Test conditions are given in Table 1.

Test conditions are given in Table 2.

Logic levels:  $V_{OL}$  and  $V_{OH}$  are typical voltage output levels that occur with the output load.

The shaded areas indicate when the input is permitted to change for predictable output performance.

# Figure 2. The Clock Input (nCP) to Output (nQ, nQ) Propagation Delays, the Clock Pulse Width, the nD to nCP Set-Up, the nCP to nD Hold Times, and the Maximum Frequency



Test conditions are given in Table 1.

Test conditions are given in Table 2.

Logic levels:  $V_{OL}$  and  $V_{OH}$  are typical voltage output levels that occur with the output load.

# Figure 3. The Set (nSD) and Reset (nRD) Input to Output (nQ, nQ) Propagation Delays, the Set and Reset Pulse Widths, and the nRD to nCP Recovery Time



# WAVEFORMS (continued)

#### Table 2. Measurement Points

SUPPLY VOLTAGE	INPUT	OUTPUT
Vcc	V <sub>M</sub> <sup>(1)</sup>	V <sub>M</sub>
V <sub>CC</sub> ≥ 2.7V	1.5V	1.5V
V <sub>CC</sub> < 2.7V	$0.5 \times V_{CC}$	$0.5 \times V_{CC}$

NOTE:

1. The measurement points should be  $V_{IH}$  or  $V_{IL}$  when the input rising or falling time exceeds 2.5ns.

### **REVISION HISTORY**


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.


Changes from Original (APRIL 2021) to REV.A	Page
Changed from product preview to production data	All




# PACKAGE OUTLINE DIMENSIONS

## **TSSOP-14**





RECOMMENDED LAND PATTERN (Unit: mm)



0h.e.l	Dimensions In Millimeters					
Symbol	MIN	MOD	MAX			
A	-	-	1.200			
A1	0.050	-	0.150			
A2	0.800	-	1.050			
b	0.190	-	0.300			
С	0.090	-	0.200			
D	4.860	-	5.100			
E	4.300	-	4.500			
E1	6.200	-	6.600			
е		0.650 BSC				
L	0.450	-	0.750			
Н	0.250 TYP					
θ	0°	-	8°			
ccc		0.100				

#### NOTES:

1. This drawing is subject to change without notice.


2. The dimensions do not include mold flashes, protrusions or gate burrs.

3. Reference JEDEC MO-153.



# TAPE AND REEL INFORMATION

### **REEL DIMENSIONS**




NOTE: The picture is only for reference. Please make the object as the standard.

### KEY PARAMETER LIST OF TAPE AND REEL

Package Type	Reel Diameter	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P0 (mm)	P1 (mm)	P2 (mm)	W (mm)	Pin1 Quadrant
TSSOP-14	13″	12.4	6.95	5.60	1.20	4.0	8.0	2.0	12.0	Q1

### **CARTON BOX DIMENSIONS**



NOTE: The picture is only for reference. Please make the object as the standard.

### **KEY PARAMETER LIST OF CARTON BOX**

Reel Type	Length (mm)	Width (mm)	Height (mm)	Pizza/Carton	
13″	386	280	370	5	DD0002

