



SGM4590

GOA Panel 15-Channel Level Shifter

GENERAL DESCRIPTION

The SGM4590 is a 15-channel high-voltage level shifter for GOA TFT-LCD panel application. It features adjustable gate pattern function.

The SGM4590 is used for transferring the logic signals that are generated by the TCON system. Different outputs of CKO_1~8 will be generated by the different settings which are outside the device. The low-impedance transistors that are located at the outputs of the device will generate fast transit, even driving the LCD panel (a capacitive load).

The SGM4590 has the input under-voltage lockout (UVLO) and the over-temperature protection (OTP) functions.

The SGM4590 is available in a Green TQFN-4×4-32L package and it operates over the temperature range of -40°C to +85°C.

TYPICAL APPLICATION




Figure 1. Typical Application Circuit

FEATURES

- 15-Channel Level Shifter
- Input Supply Range: 2.5V to 5.5V
- Input Under-Voltage Lockout (UVLO)
- Over-Temperature Protection (OTP)
- Highest Voltage Level: +30V
- Lowest Voltage Level: -10V
- Peak Current: 800mA
- Continuous Current: 30mA
- Available in a Green TQFN-4×4-32L Package

APPLICATIONS

GOA TFT-LCD Panel

PACKAGE/ORDERING INFORMATION

| MODEL | PACKAGE DESCRIPTION | SPECIFIED TEMPERATURE RANGE | ORDERING NUMBER | PACKAGE MARKING | PACKING OPTION |
|---------|---------------------|-----------------------------|-------------------|----------------------------|---------------------|
| SGM4590 | TQFN-4x4-32L | -40°C to +85°C | SGM4590YTQU32G/TR | SGM4590 YTQU32 XXXXX | Tape and Reel, 3000 |

MARKING INFORMATION

NOTE: XXXXX = Date Code, Trace Code and Vendor Code.



Green (RoHS & HSF): SG Micro Corp defines "Green" to mean Pb-Free (RoHS compatible) and free of halogen substances. If you have additional comments or questions, please contact your SGMICRO representative directly.

ABSOLUTE MAXIMUM RATINGS

Voltage Range (with Respect to AGND)

| | |
|---|---------------------------------|
| VIN | -0.3V to 6V |
| STI_1~2, LCI, CKI_1~3..... | -0.3V to V _{IN} + 0.3V |
| SET, Mode, GPM..... | -0.3V to V _{IN} + 0.3V |
| Templ..... | -0.3V to V _{IN} + 0.3V |
| Terminate..... | -0.3V to V _{IN} + 0.3V |
| VGH | -0.3V to +30V |
| VGL, VSQ | -10V to +0.3V |
| LCO_1~2, UTP_DC, VSQO to VSQ | -0.3V to V _{GH} + 0.3V |
| CKO_1~8, STO_1~2, VGLO to VGL | -0.3V to V _{GH} + 0.3V |
| VGH to VGL, VSQ | -0.3V to +40V |
| Junction Temperature..... | +150°C |
| Storage Temperature Range | -65°C to +150°C |
| Lead Temperature (Soldering, 10s) | +260°C |

RECOMMENDED OPERATING CONDITIONS

Operating Temperature Range

-40°C to +85°C

OVERSTRESS CAUTION

Stresses beyond those listed in Absolute Maximum Ratings may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect reliability. Functional operation of the device at any conditions beyond those indicated in the Recommended Operating Conditions section is not implied.


ESD SENSITIVITY CAUTION

This integrated circuit can be damaged if ESD protections are not considered carefully. SGMICRO recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage. ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because even small parametric changes could cause the device not to meet the published specifications.

DISCLAIMER

SG Micro Corp reserves the right to make any change in circuit design, or specifications without prior notice.

PIN CONFIGURATION



PIN DESCRIPTION

| PIN | NAME | FUNCTION |
|----------------------------------|----------------|--|
| 1 | LCI | Input Signal for Level Shifter (Low Frequency Clock). The LCI is the high-/low-level trigger. |
| 2 | STI_2 | Input Signal for Level Shifter (Start Pulse when Mode = High Level and Stop Pulse when Mode = Low Level). The STO_2 is the output of the specific level shifter. |
| 3 | AGND | Analog Ground for Logic Block. |
| 4 | UTP_DCO | Output Signal. Default output is VSQ, output VGH when Templ = High. |
| 5 | VGLO | Output Signal, Discharge Function for Liquid Crystal Capacitor. Low output = VGL. |
| 6 | VSQO | Output Signal, Discharge Function for Liquid Crystal Capacitor. Low output = VSQ. |
| 7 | VSQ | Negative Power Supply (LCO_1, LCO_2 and UTP_DCO). |
| 8 | VGL | Negative Power Supply (CKO_1 to CKO_8, STO_1 and STO_2). |
| 9, 10, 11, 12, 13, 14, 15, 16 | CKO_8 to CKO_1 | Output Signal for Level Shifter. |
| 17, 18 | STO_2, STO_1 | Output Signal for Level Shifter. |
| 19 | LCO_2 | Output Signal for Level Shifter (Low Frequency Clock 2). |
| 20 | LCO_1 | Output Signal for Level Shifter (Low Frequency Clock 1). |
| 21 | VGH | Positive Power Supply (STO_1, STO_2, LCO_1, LCO_2, CKO_1 to CKO_8 and XON). |
| 22 | Templ | Input Signal for UTP Function. |
| 23 | RE | Resistor Connection Input for GPM Function. |
| 24 | GPM | Setting Pin for GPM Function. High-level: shave falling edge. |

PIN DESCRIPTION (continued)

| PIN | NAME | FUNCTION |
|-------------|-------|--|
| 25 | SET | Phase Selection Setting Pin. VIN: 8 phase. AGND: 6 phase. Floating: 4 phase. Change the setting at every START rising edge. |
| 26 | Mode | CKOs Output Sequence Selection Setting Pin. High-level (1.5V to 5.5V): CKO_8 output first. Low-level (0V to 0.8V): CKO_1 output first. Change the setting at every STOP falling edge. |
| 27 | CKI_3 | Input Signal for GPM Function. |
| 28 | CKI_2 | Input Signal (Duty Cycle Adjust). The CKI_2 is the high-/low-level trigger. |
| 29 | VIN | Supply Voltage Input. |
| 30 | STI_1 | Input Signal for Level Shifter (Start Pulse when Mode = Low Level and Stop Pulse when Mode = High Level). The STO_1 is the output of the specific level shifter. |
| 31 | CKI_1 | Input Signal for Level Shifter (Condensed Clock) The CKI_1 is the high-/low-level trigger. |
| 32 | XON | Input Signal for XON Function. |
| Exposed Pad | EP | Thermal Pad. No connection. |

ELECTRICAL CHARACTERISTICS(V_{IN} = 3.3V, V_{GH} = 22V, V_{GL} = V_{SQ} = -7V, AGND = 0V, T_A = +25°C, unless otherwise noted.)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS |
|---|--|---|--|-----------------------|-----------------------|-------|
| General | | | | | | |
| Supply Voltage | V _{IN} | Operating | 2.5 | | 5.5 | V |
| V _{IN} Under-Voltage Lockout Threshold | V _{UVLO} | V _{IN} rising, hysteresis 200mV | | 2 | | V |
| XON Voltage External Setting | V _{XON} | V _{IN} falling, reference voltage | | 0.5 | | V |
| V _{GH} Under-Voltage Lockout Threshold | V _{UVLOGH} | V _{GH} rising | | 6.5 | | V |
| | | V _{GH} falling | | 3.5 | | V |
| Thermal Overload Shutdown | t _{SD} | Junction temperature rising | | 155 | | °C |
| Level Shifter | | | | | | |
| V _{GH} to AGND | | | 7 | | 30 | V |
| V _{GL} , V _{SQ} to AGND | | | -10 | | 0 | V |
| V _{GH} - (V _{GL} or V _{SQ}) | | | | | 40 | V |
| LCO_1~2, VSQO, UTP_DCO | V _{OUT} | | 0.1 + V _{SQ} | | V _{GH} - 0.2 | V |
| CKO_1~CKO_8, STO_1~2, VGLO | | | 0.1 + V _{GL} | | V _{GH} - 0.1 | V |
| Input High-Level (CKI, Templ, GPM_1/2, STI_1, STI_2, LCI) | V _{IH} | V _{IN} = 2.6V to 5.5V | | 1.2 | | V |
| Input Low-Level (CKI, Templ, GPM_1/2, STI_1, STI_2, LCI) | V _{IL} | V _{IN} = 2.6V to 5.5V | | 0.75 | | V |
| Input High-Level | SET_3/4 | V _{IH} | V _{IN} = 2.6V to 5.5V | 4.8 | | V |
| | SET_1/4 | | | 0.95 | | |
| Input Low-Level | SET_3/4 | V _{IL} | V _{IN} = 2.6V to 5.5V | 1.85 | | V |
| | SET_1/4 | | | 0.65 | | |
| Positive Output Swing | CKO_1~CKO_8, STO_1~2, LCO_1~2, VSQO, VGLO, UTP_DCO | V _{CK+} | All inputs high, I _O = 10mA | | V _{GH} - 0.2 | V |
| Negative Output Swing | LCO_1~2, UTP_DCO, VSQO | V _{CK-} | All inputs low, I _O = -10mA | V _{SQ} + 0.1 | | V |
| | CKO_1~CKO_8, STO_1~2, VGLO | | | V _{GL} + 0.1 | | |
| High-side Switch-On Resistance | STO_1~2, LCO_1~2, VSQO, VGLO, UTP_DCO | R _{HIGH-SIDE} | I _O = 10mA | | 12 | Ω |
| | CKO_1~CKO_8 | | | | 7 | |
| Low-side Switch-On Resistance | CKO_1~CKO_8 | R _{LOW-SIDE} | I _O = -10mA | | 3.4 | Ω |
| | STO_1~2, LCO_1~2 | | | | 5.2 | |
| | VSQO, VGLO, UTP_DCO | | | | 9 | |
| CKOs to RE Switch On-Resistance | R _{RE} | V _{GH} = 22V, V _{GL1~2} = -7V | | | 126 | Ω |

ELECTRICAL CHARACTERISTICS (continued)(V_{IN} = 3.3V, V_{GH} = 22V, V_{GL} = V_{SQ} = -7V, AGND = 0V, T_A = +25°C, unless otherwise noted.)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNITS |
|-------------------------|-------------|-----------------|---|-----|-----|-------|
| Level Shifter | | | | | | |
| Rising Time | CKO_1~CKO_8 | t _R | V _{GH} = 22V, V _{GL1~2} = -7V, C _L = 4.7nF, 10% ~ 90% | 160 | | ns |
| | STO_1~2 | | | 160 | | |
| | LCO_1~2 | | | 300 | | |
| | XON | | | 2 | | μs |
| Falling Time | CKO_1~CKO_8 | t _F | V _{GH} = 22V, V _{GL1~2} = -7V, C _L = 4.7nF, 90% ~ 10% | 80 | | ns |
| | STO_1~2 | | | 80 | | |
| | LCO_1~2 | | | 80 | | |
| | XON | | | 400 | | |
| Rising Edge Delay Time | CKO_1~CKO_8 | t _{RD} | V _{GH} = 22V, V _{GL1~2} = -7V, C _L = 4.7nF, 50% of input to 10% of output | 82 | | ns |
| | STO_1~2 | | | 154 | | |
| | LCO_1~2 | | | 149 | | |
| | XON | | | 490 | | |
| Falling Edge Delay Time | CKO_1~CKO_8 | t _{FD} | V _{GH} = 22V, V _{GL1~2} = -7V, C _L = 4.7nF, 50% of input to 90% of output | 91 | | ns |
| | STO_1~2 | | | 114 | | |
| | LCO_1~2 | | | 120 | | |
| | XON | | | 278 | | |

FUNCTIONAL BLOCK DIAGRAM




Figure 2. Block Diagram

DETAILED DESCRIPTION

Power-On Sequence

The internal signal ENA for condensed GOA logic goes high if the VIN exceeds VIN_UVLO. The level shifter outputs CKO_1~8 and STO_1~2 track the VGL supply, and LCO_1~2 track the VSQ supply, it is called default mode. After VGH exceeds VGH_UVLO, the default

mode continues until receiving the first START rising edge. Input signals STI_1~2 will provide START and STOP command, LCO_1~2 only refreshes in the period after STOP and before the next START. Refer to Figure 3.




Figure 3. Power-On Waveform Diagram




Figure 4. Power-Off Waveform Diagram

DETAILED DESCRIPTION (continued)

Power-Off Sequence (XON MODE)

The falling VIN_UVLO reference voltage at the XON pin is 0.5V. The user selects a resistor divider to obtain the falling threshold for the specific application. The thresholds can be determined as follows:




Figure 5. XON Function Structure

Once the level of VIN is below the V_{REF} , the output of the SGM4590 will be pulled at the same level as VGH. Refer to Figure 4.

Level Shift Function

The SGM4590 contains 15-channel level shifter. The corresponding tech is Gate-On-Array (GOA). Four signals are used to generate signals of STO_1~2, LCO_1~2, and CKO_1~8. VGL is the low-level for CKO_1~8 and STO_1~2 while VSQ is the low-level for LCO_1~2. The settings for the output of the SGM4590 are shown below.

Terminate

The CKO_1~8 can be pulled low by terminating input pin and no CKI edges can launch them before the coming start. However, if the stimulation of the terminal pin is not be triggered, the CKO_1~8 can also be terminated by the next START.

LC

The complementary signal and the two low frequency components should be taken into consideration. As a result, the LCI should be followed by LCO_1 and the inverting of the LCO_1 should be followed by LCO_2.

SET

The phase number of the CKOs is set by the SET pin of the SGM4590. For the rising edge of each START condition, the SET will be latched and triggered. However, if there is noise interference, the state real time will be changed. Table 1 lists the settings.

Table 1. The Setting Table

| Pin | Status | Level Shifter Output |
|--------------------|-------------------|--|
| SET ⁽¹⁾ | VIN | 8 phases. CKO_1~8 output. |
| | AGND | 6 phases. CKO_1~6 output. CKO_7 and CKO_8 keep in VGL. |
| | Floating | 4 phases. CKO_1~4 output. CKO_5~8 keep in VGL. |
| Mode | Logic signal high | CKO_8 output first. |
| | Logic signal low | CKO_1 output first. |
| GPM | Logic signal high | CKOs' falling edge shaved. |
| | Logic signal low | Falling edge shave function disable. |

NOTE: 1. For a tri-state setting pin, it is connected 400kΩ resistor to VIN and 400kΩ to AGND inside the SGM4590.

Mode

Mode pin is to set the CKOs output sequence. CKO_1 outputs first when Mode pin = "Low", when Mode pin = "high", CKO_8 outputs first. The first type of the output for CKO_1 is shown as below (see Figure 6).




Figure 6. CKO_1 Output First Type

The first type of the output for CKO_8 is shown in Figure 7.




Figure 7. CKO_8 Output First Type

DETAILED DESCRIPTION (continued)

OTP

The over-temperature protection will cause the external power dissipation to the SGM4590 since the device is overheated. If the junction temperature is over 155°C, the thermal sensor that is at the internal of the SGM4590 will be triggered so that the OTP is launched. Only cycle the VIN to clear the OTP latch and reactivate the device.

UTP

The SGM4590 has an external UTP (Under-Temperature Protection) function through the input Tempi pin. Tempi pin supports both high-/low-level trigger and NTC mode.




Figure 8. UTP Function Structure

CKOs Duty Cycle Adjustable

The CKOs output duty cycle can be adjusted through CKI_2. The first CKO output rising edge follows CKI_2.

GPM Function

The eight clock channels of CLK_1~8 outputs support the GPM function, which shave the corner of the scan-driver outputs' falling edge. Depending on GPM pin, the corner of the falling edge shaving is achieved by turning off the scan-driver switches, and turn on the GPM switches to let the panel load capacitance discharge through the resistor at the RE pin. The start point of shaving activity is adjusted by CKI_3.




Figure 9. GPM Function Timing Sequence




Figure 10. GPM Function Structure

DETAILED DESCRIPTION (continued)





Figure 11. Timing Sequence of CKOs

PACKAGE INFORMATION

PACKAGE OUTLINE DIMENSIONS

TQFN-4x4-32L




| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|------------------------------|-------|-------------------------|-------|
| | MIN | MAX | MIN | MAX |
| A | 0.700 | 0.800 | 0.028 | 0.031 |
| A1 | 0.000 | 0.050 | 0.000 | 0.002 |
| A2 | 0.203 REF | | 0.008 REF | |
| D | 3.900 | 4.100 | 0.154 | 0.161 |
| D1 | 2.500 | 2.700 | 0.098 | 0.106 |
| E | 3.900 | 4.100 | 0.154 | 0.161 |
| E1 | 2.500 | 2.700 | 0.098 | 0.106 |
| k | 0.300 REF | | 0.012 REF | |
| b | 0.150 | 0.250 | 0.006 | 0.010 |
| L | 0.300 | 0.500 | 0.012 | 0.020 |
| e | 0.400 BSC | | 0.016 BSC | |

NOTE: This drawing is subject to change without notice.


PACKAGE INFORMATION

TAPE AND REEL INFORMATION

REEL DIMENSIONS



TAPE DIMENSIONS




NOTE: The picture is only for reference. Please make the object as the standard.

KEY PARAMETER LIST OF TAPE AND REEL

| Package Type | Reel Diameter | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P0 (mm) | P1 (mm) | P2 (mm) | W (mm) | Pin1 Quadrant |
|--------------|---------------|--------------------|---------|---------|---------|---------|---------|---------|--------|---------------|
| TQFN-4x4-32L | 13" | 12.4 | 4.30 | 4.30 | 1.10 | 4.0 | 8.0 | 2.0 | 12.0 | Q2 |

PACKAGE INFORMATION

CARTON BOX DIMENSIONS



NOTE: The picture is only for reference. Please make the object as the standard.

KEY PARAMETER LIST OF CARTON BOX

| Reel Type | Length (mm) | Width (mm) | Height (mm) | Pizza/Carton |
|-----------|-------------|------------|-------------|--------------|
| 13" | 386 | 280 | 370 | 5 |