


PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DATO	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)




Specification:

- Electrical Characteristics:
 - Contact Current Rating:0.5 Amperes.
 - Dielectric Withstanding Voltage:Ac500V r.m.s.
 - InsulationResistance.1000 MΩ Minimum.
 - Contact Resistance:40 mΩ Maximum.
- Environmental:
 - Operating Temperature:-25°c~+90°c,
- Environmental:
 - Mating Cycles:5,000 Insertions.
- Mechanical Characteristics:
 - Card Push Insertion/Out Force:0.2~1.40kgf.
 - Contact Separation Force:0.20kgf Minimum.
- Material:
 - Insulator:HI-Temp Plastic UL 94V-0 Rated.
 - Contact:Copper Alloy(t=0.15mm).
 - Shell:Stainless Steel(t=0.15mm).
 - Spring:SWP.



TF-N02-X

G=GOLD 1u"
N=NICKEL 80u"



④	Spring	1	SWP	
③	Shell	1	SUS	
②	Terminal	9	COPPER ALLOY	
①	Housing	1	HI-TEMP.PLASIC UL 94V-0	BLACK
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

ECN BO.		DESCRIPTION.		DATE.	REV.	SCALE: 3:1	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER		SCALT: 1/2		
Mikey	Tom	Jerry	PART NAME	TF-N02-X	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25
			MODEL NAME	TF-N02-X		X.x	±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	±0.15
						ANGULAIR	±3
						FILE.NO.	

瀚源