



SSL12F THRU SSL16F

Surface Mount Low VF Schottky Rectifiers


Reverse Voltage - 20 to 60 V
Forward Current - 1.0 A

FEATURES

- Metal silicon junction, majority carrier conduction
- For surface mounted applications
- Low power loss, high efficiency
- High forward surge current capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



MECHANICAL DATA

- Case: SMAF
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 27mg 0.00086oz

Absolute Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz resistive or inductive load, for capacitive load, derate by 20 %

Parameter	Symbols	SSL12F	SSL14F	SSL16F	Units
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	20	40	60	V
Maximum RMS voltage	V_{RMS}	14	28	42	V
Maximum DC Blocking Voltage	V_{DC}	20	40	60	V
Maximum Average Forward Rectified Current	$I_{F(AV)}$	1.0			A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}	40			A
Max Instantaneous Forward Voltage at 1 A	V_F	0.45		0.55	V
Maximum DC Reverse Current $T_a = 25^{\circ}C$ at Rated DC Reverse Voltage $T_a = 100^{\circ}C$	I_R	0.3 10	0.2 5		mA
Typical Junction Capacitance ¹⁾	C_j	180		80	pF
Typical Thermal Resistance ²⁾	$R_{\theta JA}$	115			°C/W
Operating Junction Temperature Range	T_j	-55 ~ +125			°C
Storage Temperature Range	T_{stg}	-55 ~ +150			°C

1) Measured at 1MHz and applied reverse voltage of 4 V D.C.

2) P.C.B. mounted with 0.2 X 0.2" (5 X 5 mm) copper pad areas.



SSL12F THRU SSL16F

Surface Mount Low VF Schottky Rectifiers

Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current





Fig.6- Typical Transient Thermal Impedance






SSL12F THRU SSL16F

Surface Mount Low VF Schottky Rectifiers


PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SMAF



The recommended mounting pad size



Marking

Type number	Marking code
SSL12F	SSL12
SSL14F	SSL14
SSL16F	SSL16