




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2017.04.20	馮國東

Dim.C	NOTE
4.00mm	02PIN
5.00mm	03~08PIN
8.16mm	09~40PIN


Specifications

Current Rating:2.0Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:500VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials

Contact Material:Brass
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon (Halogen Free) or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.



Recommended P.C.Board Layout
 (Tolerance: ±0.05)



Ordering Information

G PFC206 - XX XX A 115 R 1 W X

No. of Pins per Row 02~40
 Standard Plating 02=Gold Flash
 Selective Plating 01=Tin 05=Gold Flash/Tin
 Color 1=Black
 Standard Packing C=Tube(03~40PIN)
 Selective Packing D=Tape&Reel E=CAP+Tube(04~40PIN) F=CAP+Tape&Reel

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X. ±5.0°	X. ±0.30
.X ±3.0°	.X ±0.25
.XX ±2.0°	.XX ±0.15
.XXX ±1.0°	.XXX ±0.10

DESIGNED: 馮國東	DATE: 2017.04.20
CHECKED: 曹熙	DATE: 2017.04.20
CO SIGNED: 蘭文禮	DATE: 2017.04.20
APPROVED: 李輝	DATE: 2017.04.20

DWG. NO.	GPFC206-CA115RW
PART NO.	GPFC206-XXXX A115R1WX

TITLE:
 2.00 PIN HEADER
 DUAL ROWS SMT TYPE
 CONNECTOR

REV.	UNIT.	SCALE.	PAGE.
01	mm	4:1	1/1